



Type B Liquidtight Conduit Tubing & Fittings

T&B Catalog Number:

UPC Number:

LT9200P

Status:

78621045080

Description:

Active

2 in. 90 degree non-metallic liquidtight Bullet.

Features

Outside surface has friction reducing ridges.

Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.

Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.

Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

Application

T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.

Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

General

Trade Size (inches)

2

Material

Thermoplastic

Dimension Information

Dimension A (inches) 0.794

Dimension B (inches) 3.432

Dimension C (inches) 3.362

Dimension D-Minimum Throat (inches) 1.883

Dimension F (inches) 3.675

A (mm) 20.17

B (mm) 87.17

C (mm) 85.39

D (mm) 47.83

F Approx. (mm) 93.34

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

1

Package in Units

5

T&B Sold in UOM

Each

T&B Weight Per UOM

93 lbs. per 100

Application Support

T&B Instruction Sheets

ta00998-tb2

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications

Available on Website

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com