


# Amphenol® MIL-DTL-5015 and MIL-5015 Type Standard Cylindrical Connectors

12-020-18



# Amphenol

# MS/Standard

## how to order

### MIL-DTL-5015 and MIL-5015 Type (Solder Contacts)

MS   3102   A   18-3   P   W   (SR)  
**1**   **2**   **3**   **4**   **5**   **6**   **7**   **8**

1. Connector Type  
 MS designates Military Standard  
 CS\* designates service class A and C with proprietary special contact arrangements  
 SG\* designates service class E with proprietary special contact arrangements  
 SM\* designates service class F and R with proprietary special contact arrangements
2. Connector Style  
 3100 wall mounting receptacle  
 3101 cable connecting plug  
 3102 box mounting receptacle  
 3106 straight plug  
 3108 90° plug
3. Service Class  
 A solid shell for general, non-environmental applications  
 C solid shell for pressurized applications  
 E environmental resisting  
 F environmental resisting with strain relief (MS part number only)  
 R lightweight environmental resisting
- 4., 5. Shell size and insert arrangement - see tables, pages 22-24.
6. Contact Types  
 P designates pin contact  
 S designates socket contact
7. Insert Rotation  
 "W", "X", "Y", or "Z" designate that insert is rotated in its shell from normal position. No letter required for normal (no rotation) position.
8. (SR) strain relief for non-military connectors (For MS use "F" class)

\* For insert arrangements over 50 and shell size 40 and above.  
 Exceptions: 36-52, 40-1, 40-9 and 40-56 are MS approved.

Consult Amphenol, Sidney, NY for availability of alternate finishes, including black and olive drab zinc alloys.

### Proprietary (Crimp Contacts)

75 - 68   0   12-3   H  
**1**   **2**   **3**   **4**   **5**   **6**

1. Connector Type  
 75 - connector utilizing silver plated contacts  
 80 - less contacts  
 85 - contacts utilizing 50 micro-inches gold over silver plating
2. Service Class  
 68 service class A, general duty  
 474 service class F, environmental resisting  
 190 service class R, lightweight environmental resisting
3. Connector Style  
 0 wall mounting receptacle  
 1 cable connecting plug  
 2 box mounting receptacle  
 6 straight plug  
 8 90° plug
4. Shell Size Designator


|                  |    |     |      |     |    |     |    |     |    |    |
|------------------|----|-----|------|-----|----|-----|----|-----|----|----|
| Shell Size       | 8S | 10S | 10SL | 12S | 12 | 14S | 14 | 16S | 16 | 18 |
| Shell Designator | 8  | 10  | 11   | 12  | 13 | 14  | 15 | 16  | 17 | 18 |

|                  |    |    |    |    |    |    |    |    |    |  |
|------------------|----|----|----|----|----|----|----|----|----|--|
| Shell Size       | 20 | 22 | 24 | 28 | 32 | 36 | 40 | 44 | 48 |  |
| Shell Designator | 20 | 22 | 24 | 28 | 32 | 36 | 40 | 44 | 48 |  |

5. Insert Arrangements  
 See page 22-24.
6. Contact Type/Alternate Insert Rotation  
 P designates pin, S designates socket for normal positioning of inserts. When an alternate position of the connector insert is required to prevent cross-mating, a different letter (other than P or S) is used. See page 25 for description of alternate positions, then convert to Amphenol® proprietary coding by the following charts:

| Pin Contacts |                 | Socket Contacts |                 |
|--------------|-----------------|-----------------|-----------------|
| MS Letter    | Amphenol Letter | MS Letter       | Amphenol Letter |
| PW           | G               | SW              | H               |
| PX           | I               | SX              | J               |
| PY           | K               | SY              | L               |
| PZ           | M               | SZ              | N               |

# Amphenol® MIL-DTL-5015 and MIL-5015 Type Standard Cylindrical Connectors



MS-A, MS-C



MS-E/F



MS-R

## DESIGN CHARACTERISTICS

- Medium to heavy weight cylindrical
- Durable, field-proven design
- Environmental resistant
- Resilient inserts
- Operating voltage to 3000 VAC (RMS) at sea level
- Threaded couplings
- Single key/keyway shell polarization
- Cost effective

## CUSTOMER OPTIONS

- Five shell styles
- Nineteen shell sizes
- 305 contact arrangements from 1 to 104 circuits
- Solder or crimp contacts, sizes 16-0 accepting 22-0 AWG.
- Coaxial and thermocouple contact options
- Five class designations
- Alternate insert positioning
- Hermetic configurations available
- Zinc alloy plating (cadmium-free) available

MS connectors meet the latest performance requirements of MIL-DTL-5015. These connectors represent well-proven electrical capability at an acceptable cost for most equipment where durability is important.

MIL-DTL-5015 features threaded couplings and single key/keyway polarization, representing maximum simplicity in design. Applications include military ground support equipment, ordnance and shipboard installations.

Amphenol Industrial Operations manufactures five classes of connectors to meet different requirements. Class designations and brief descriptions are listed below.

A – Solid Shell – for general, non-environmental applications.

C – Pressurized – for use on pressurized bulkheads or pressure barriers; limits air leakage regardless of type and class of plug mated with them.

E/F – Environmental Resisting with Strain Relief – designed for applications where the connector will be exposed to moisture, vibration, and rapid changes in pressure and temperature.

R – Lightweight Environmental Resisting – shorter in length and lighter in weight than the E and F classes, the MS-R offers a high degree of reliability under adverse conditions: recommended for new design applications.

# MS/Standard


## MS-A and MS-C



**wall mounting receptacle**




**cable connecting plug**



**box mounting receptacle**



**straight plug**



**90 degree plug**

### **MS-A and MS-C**

MS-A and MS-C class connectors perform many of the vital functions in powering, testing and ground support systems. Class A applications include communications equipment, computers and shipboard installations where mechanical forces and physical parameters are not subject to extreme or rapid environmental changes.

Class C connectors are most frequently used on pressurized bulkheads or pressure barriers at elevated altitudes or maritime applications. Air leakage is limited to one cubic inch per hour at a pressure differential of 30 lbs. per square inch.

#### **Shells:**

Shell components are fabricated from high grade aluminum alloy. Electrically conductive cadmium plate finish with an olive drab chromate after-treat offers corrosion resistance.

#### **Contacts:**

Contacts are available in both solder and crimp versions. Pins and sockets are machined from copper alloy with a silver plated finish. Size 16 and 12 socket contacts incorporate a closed entry design. Refer to pages 49, 67 and 68 for additional contact information.


#### **Inserts:**

Inserts are resilient neoprene, offering high dielectric strength, high arc resistance and resistance to vibration. Proprietary design permits pressurization of either pin or socket insert.

# MS/Standard

## MS3100A or C

### wall mounting receptacle



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.


| Shell Size | A Thread Class 2A | B Min Full Thread | K $+0.020$ $-0.010$ | L $\pm 0.030$ | M $+0.010$ $-0.000$ | R $\pm 0.005$ | S $\pm 0.031$ | T Dia. $+0.004$ $-0.002$ | V Thread Class 2A | Z $+0.050$ $-0.060$ |
|------------|-------------------|-------------------|---------------------|---------------|---------------------|---------------|---------------|--------------------------|-------------------|---------------------|
| 8S         | .5000-28UNEF      | .391              | .672                | 1.391         | .562                | .594          | .875          | .120                     | .5000-28UNEF      | .422                |
| 10S        | .6250-24 UNF      | .391              | .672                | 1.468         | .562                | .719          | 1.000         | .120                     | .5000-28UNEF      | .422                |
| 10SL       | .6250-24 UNF      | .391              | .672                | 1.468         | .562                | .719          | 1.000         | .120                     | .6250-24NEF       | .422                |
| 12S        | .7500-20UNEF      | .450              | .672                | 1.468         | .562                | .812          | 1.094         | .120                     | .6250-24NEF       | .422                |
| 12         | .7500-20UNEF      | .625              | .860                | 1.843         | .750                | .812          | 1.094         | .120                     | .6250-24NEF       | .672                |
| 14S        | .8750-20UNEF      | .450              | .672                | 1.468         | .562                | .906          | 1.188         | .120                     | .7500-20UNEF      | .422                |
| 14         | .8750-20UNEF      | .625              | .860                | 1.843         | .750                | .906          | 1.188         | .120                     | .7500-20UNEF      | .672                |
| 16S        | 1.0000-20UNEF     | .450              | .672                | 1.468         | .562                | .969          | 1.281         | .120                     | .8750-20UNEF      | .422                |
| 16         | 1.0000-20UNEF     | .625              | .860                | 1.843         | .750                | .969          | 1.281         | .120                     | .8750-20UNEF      | .672                |
| 18         | 1.1250-18NEF      | .625              | .891                | 1.938         | .750                | 1.063         | 1.375         | .120                     | 1.0000-20UNEF     | .641*               |
| 20         | 1.2500-18NEF      | .625              | .891                | 1.844         | .750                | 1.156         | 1.500         | .120                     | 1.1875-18NEF      | .641*               |
| 22         | 1.3750-18NEF      | .625              | .891                | 1.938         | .750                | 1.250         | 1.625         | .120                     | 1.1875-18NEF      | .641*               |
| 24         | 1.5000-18NEF      | .625              | .953                | 1.969         | .812                | 1.375         | 1.750         | .147                     | 1.4375-18NEF      | .578*               |
| 28         | 1.7500-18NS       | .625              | .953                | 2.188         | .812                | 1.562         | 2.000         | .147                     | 1.4375-18NEF      | .578*               |
| 32         | 2.0000-18NS       | .625              | 1.031               | 2.157         | .875                | 1.750         | 2.250         | .173                     | 1.7500-18NS       | .500*               |
| 36         | 2.2500-16UN       | .625              | 1.031               | 2.219         | .875                | 1.938         | 2.500         | .173                     | 2.0000-18NS       | .500*               |
| 40         | 2.5000-16UN       | .625              | 1.031               | 2.188         | .875                | 2.188         | 2.750         | .173                     | 2.2500-16UN       | .500*               |
| 44***      | 2.7500-16UN       | .625              | 1.031†              | 2.547         | .875                | 2.375         | 3.000††       | .173                     | 2.5000-16UN       | .751**              |
| 48***      | 3.0000-16UN       | .625              | 1.031†              | 2.547         | .875                | 2.625         | 3.000††       | .173                     | 3.0000-16UN       | .751**              |

\* Increase Z dimension by .312 for size "0" contact only.  
 \*\* Increase Z dimension by .062 for size "0" contact only.  
 \*\*\* Available in proprietary version only.  
 †  $+0.020$   $-0.030$   
 ††  $\pm 0.020$

# MS/Standard

## MS3101A

### cable connecting plug



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.


| Shell Size | A Thread Class 2A | B Min. Full Thread | L $\pm .030$ | N Dia. Max. | V Thread Class 2A | Z $\pm .040$ |
|------------|-------------------|--------------------|--------------|-------------|-------------------|--------------|
| 8S         | .5000-28UNEF      | .406               | 1.390        | .532        | .5000-28UNEF      | 1.094        |
| 10S        | .6250-24NEF       | .406               | 1.468        | .628        | .5000-28UNEF      | 1.094        |
| 10SL       | .6250-24NEF       | .406               | 1.468        | .755        | .6250-24NEF       | 1.094        |
| 12S        | .7500-20UNEF      | .422               | 1.468        | .755        | .6250-24NEF       | 1.094        |
| 12         | .7500-20UNEF      | .656               | 1.843        | .755        | .6250-24NEF       | 1.532        |
| 14S        | .8750-20UNEF      | .391               | 1.468        | .882        | .7500-20UNEF      | 1.094        |
| 14         | .8750-20UNEF      | .625               | 1.843        | .882        | .7500-20UNEF      | 1.532        |
| 16S        | 1.0000-20UNEF     | .391               | 1.468        | 1.010       | .8750-20UNEF      | 1.094        |
| 16         | 1.0000-20UNEF     | .625               | 1.843        | 1.010       | .8750-20UNEF      | 1.532        |
| 18         | 1.1250-18NEF      | .625               | 1.938        | 1.137       | 1.0000-20UNEF     | 1.532*       |
| 20         | 1.2500-18NEF      | .625               | 1.844        | 1.264       | 1.1875-18NEF      | 1.532*       |
| 22         | 1.3750-18NEF      | .625               | 1.938        | 1.392       | 1.1875-18NEF      | 1.532*       |
| 24         | 1.5000-18NEF      | .625               | 1.969        | 1.519       | 1.4375-18NEF      | 1.532*       |
| 28         | 1.7500-18NS       | .625               | 2.188        | 1.774       | 1.4375-18NEF      | 1.532*       |
| 32         | 2.0000-18NS       | .625               | 2.157        | 1.996       | 1.7500-18NS       | 1.532*       |
| 36         | 2.2500-16UN       | .625               | 2.219        | 2.251       | 2.0000-18NS       | 1.532*       |
| 40         | 2.5000-16UN       | .625               | 2.188        | 2.506       | 2.2500-16UN       | 1.532*       |
| 44***      | 2.7500-16UN       | .625               | 2.521        | 3.135       | 2.5000-16UN       | 1.782**      |

\* Increase Z dimension by .312 for size "0" contact only.

\*\* Increase Z dimension by .062 for size "0" contact only.

\*\*\* Available in proprietary version only.

# MS/Standard MS3102A or C box mounting receptacle



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.

| Shell Size | A Thread Class 2A | B Min Full Thread | K $+.020$ $-.010$ | L $+.000$ $-.010$ | M $+.010$ $-.000$ | N Dia. $+.010$ $-.000$ | R $\pm.005$ | S $\pm.031$ | T Dia. $+.004$ $-.002$ | Z $+.050$ $-.060$ |
|------------|-------------------|-------------------|-------------------|-------------------|-------------------|------------------------|-------------|-------------|------------------------|-------------------|
| 8S         | .5000-28UNEF      | .391              | .672              | .297              | .562              | .375                   | .594        | .875        | .120                   | .422              |
| 10S        | .6250-24NEF       | .391              | .672              | .297              | .562              | .500                   | .719        | 1.000       | .120                   | .422              |
| 10SL       | .6250-24NEF       | .391              | .672              | .297              | .562              | .625                   | .719        | 1.000       | .120                   | .422              |
| 12S        | .7500-20UNEF      | .450              | .672              | .297              | .562              | .625                   | .812        | 1.094       | .120                   | .422              |
| 12         | .7500-20UNEF      | .625              | .860              | .484              | .750              | .625                   | .812        | 1.094       | .120                   | .672              |
| 14S        | .8750-20UNEF      | .450              | .672              | .297              | .562              | .750                   | .906        | 1.188       | .120                   | .422              |
| 14         | .8750-20UNEF      | .625              | .860              | .484              | .750              | .750                   | .906        | 1.188       | .120                   | .672              |
| 16S        | 1.0000-20UNEF     | .450              | .672              | .297              | .562              | .875                   | .969        | 1.281       | .120                   | .422              |
| 16         | 1.0000-20UNEF     | .625              | .860              | .484              | .750              | .875                   | .969        | 1.281       | .120                   | .672              |
| 18         | 1.1250-18NEF      | .625              | .891              | .453              | .750              | 1.000                  | 1.062       | 1.375       | .120                   | .641*             |
| 20         | 1.2500-18NEF      | .625              | .891              | .453              | .750              | 1.125                  | 1.156       | 1.500       | .120                   | .641*             |
| 22         | 1.3750-18NEF      | .625              | .891              | .453              | .750              | 1.250                  | 1.250       | 1.625       | .120                   | .641*             |
| 24         | 1.5000-18NEF      | .625              | .953              | .453              | .812              | 1.375                  | 1.375       | 1.750       | .147                   | .578              |
| 28         | 1.7500-18NS       | .625              | .953              | .453              | .812              | 1.625                  | 1.562       | 2.000       | .147                   | .578*             |
| 32         | 2.0000-18NS       | .625              | 1.031             | .438              | .875              | 1.875                  | 1.750       | 2.250       | .173                   | .500*             |
| 36         | 2.2500-16UN       | .625              | 1.031             | .438              | .875              | 2.062                  | 1.938       | 2.500       | .173                   | .500*             |
| 40         | 2.5000-16UN       | .625              | 1.031             | .438              | .875              | 2.312                  | 2.188       | 2.750       | .173                   | .500*             |
| 44***      | 2.7500-16UN       | .625              | 1.063             | .543†             | .875              | 2.594                  | 2.375       | 3.000††     | .173                   | .768**            |
| 48***      | 3.0000-16UN       | .625              | 1.063             | .543†             | .875              | 2.812                  | 2.625       | 3.250††     | .209                   | .769**            |

\* Increase Z dimension by .312 for size "0" contact only.

\*\* Increase Z dimension by .062 for size "0" contact only.

\*\*\* Available in proprietary version only.


†  $+.020$   $-.030$

††  $\pm.020$

# MS/Standard

## MS3106A

### straight plug



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.  
All lockwire holes are .045 dia. min.

| Shell Size | A Thread Class 2B | J $\pm .005$ | L $\pm .030$ | Q Dia. Max. | V Thread Class 2A | Z $\pm .045$ |
|------------|-------------------|--------------|--------------|-------------|-------------------|--------------|
| 8S         | .5000-28UNEF      | .531         | .859         | .741        | .5000-28UNEF      | .562         |
| 10S        | .6250-24NEF       | .531         | .937         | .869        | .5000-28UNEF      | .562         |
| 10SL       | .6250-24NEF       | .531         | .937         | .946        | .6250-24NEF       | .562         |
| 12S        | .7500-20UNEF      | .531         | .937         | .995        | .6250-24NEF       | .562         |
| 12         | .7500-20UNEF      | .719         | 1.124        | .995        | .6250-24NEF       | .812         |
| 14S        | .8750-20UNEF      | .531         | .937         | 1.123       | .7500-20UNEF      | .562         |
| 14         | .8750-20UNEF      | .719         | 1.124        | 1.123       | .7500-20UNEF      | .812         |
| 16S        | 1.0000-20UNEF     | .531         | .937         | 1.250       | .8750-20UNEF      | .562         |
| 16         | 1.0000-20UNEF     | .719         | 1.124        | 1.250       | .8750-20UNEF      | .812         |
| 18         | 1.1250-18NEF      | .719         | 1.219        | 1.333       | 1.0000-20UNEF     | .812*        |
| 20         | 1.2500-18NEF      | .719         | 1.125        | 1.461       | 1.1875-18NEF      | .812*        |
| 22         | 1.3750-18NEF      | .719         | 1.219        | 1.588       | 1.1875-18NEF      | .812*        |
| 24         | 1.5000-18NEF      | .719         | 1.251        | 1.715       | 1.4375-18NEF      | .812*        |
| 28         | 1.7500-18NS       | .719         | 1.470        | 1.968       | 1.4375-18NEF      | .812*        |
| 32         | 2.0000-18NS       | .719         | 1.439        | 2.209       | 1.7500-18NS       | .812*        |
| 36         | 2.2500-16UN       | .719         | 1.500        | 2.463       | 2.0000-18NS       | .812*        |
| 40         | 2.5000-16UN       | .719         | 1.469        | 2.719       | 2.2500-16UN       | .812*        |
| 44***      | 2.7500-16UN       | .719         | 1.818†       | 3.084       | 2.5000-16UN       | 1.063**      |
| 48***      | 3.3000-16UN       | .719         | 1.818†       | 3.354       | 3.0000-16UN       | 1.063**      |

\* Increase Z dimension by .312 for size "0" contact only.

\*\* Increase Z dimension by .062 for size "0" contact only.


\*\*\* Available in proprietary version only.

† +.020 –.030

# MS/Standard

## MS3108A

### 90 degree plug



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.  
All lockwire holes are .045 dia. min.

| Shell Size | A Thread Class 2B | J $\pm.005$ | L Max. | Q Dia. Max. | U Max. | V Thread Class 2A | W    | Z $\pm.045$ |
|------------|-------------------|-------------|--------|-------------|--------|-------------------|------|-------------|
| 8S         | .5000-28UNEF      | .531        | .896   | .741        | .750   | .5000-28UNEF      | .375 | .562        |
| 10S        | .6250-24NEF       | .531        | .927   | .869        | .750   | .5000-28UNEF      | .375 | .562        |
| 10SL       | .6250-24NEF       | .531        | .951   | .946        | .875   | .6250-24NEF       | .375 | .562        |
| 12S        | .7500-20UNEF      | .531        | .956   | .995        | .875   | .6250-24NEF       | .375 | .562        |
| 12         | .7500-20UNEF      | .719        | 1.143  | .995        | .875   | .6250-24NEF       | .375 | .812        |
| 14S        | .8750-20UNEF      | .531        | 1.120  | 1.123       | 1.000  | .7500-20UNEF      | .375 | .562        |
| 14         | .8750-20UNEF      | .719        | 1.207  | 1.123       | 1.000  | .7500-20UNEF      | .375 | .812        |
| 16S        | 1.0000-20UNEF     | .531        | 1.146  | 1.250       | 1.062  | .8750-20UNEF      | .375 | .562        |
| 16         | 1.0000-20UNEF     | .719        | 1.332  | 1.250       | 1.062  | .8750-20UNEF      | .375 | .812        |
| 18         | 1.1250-18NEF      | .719        | 1.395  | 1.333       | 1.188  | 1.0000-20UNEF     | .375 | .812*       |
| 20         | 1.2500-18NEF      | .719        | 1.645  | 1.461       | 1.250  | 1.1875-18NEF      | .375 | .812*       |
| 22         | 1.3750-18NEF      | .719        | 1.645  | 1.588       | 1.312  | 1.1875-18NEF      | .375 | .812*       |
| 24         | 1.5000-18NEF      | .719        | 1.896  | 1.715       | 1.438  | 1.4375-18NEF      | .375 | .812*       |
| 28         | 1.7500-18NS       | .719        | 1.896  | 1.968       | 1.500  | 1.4375-18NEF      | .375 | .812*       |
| 32         | 2.0000-18NS       | .719        | 2.118  | 2.209       | 1.750  | 1.7500-18NS       | .438 | .812*       |
| 36         | 2.2500-16UN       | .719        | 2.176  | 2.463       | 1.875  | 2.0000-18NS       | .500 | .812*       |
| 40         | 2.5000-16UN       | .719        | 2.301  | 2.719       | 2.031  | 2.2500-16UN       | .500 | .812*       |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS-E/F



wall mounting receptacle



cable connecting plug



box mounting receptacle



straight plug



90 degree plug

### MS-E & F

MS Class F connectors satisfy all the performance requirements of MIL-DTL-5015. Class E, environmental is also produced, but is no longer listed on the qualified products listing (QPL). These connectors are recommended for conditions where vibration, moisture, pressure and/or temperature are extreme. Strain relief is supplied on most shell sizes.

#### Shells:

Shell components are fabricated from high grade aluminum alloy. The standard hardware plating is electrically conductive cadmium plated finish with an olive drab chromate after-treatment for corrosion resistance. Consult Amphenol, Sidney, NY for other plating options.

#### Contacts:

Contacts are silver plated copper alloy for maximum corrosion resistance, maximum current carrying capacity and low millivolt drop. Size 16 and 12 socket contacts incorporate a closed entry design. Crimp and solder versions are available. Refer to pages 49, 67 and 68 for additional contact information.

#### Inserts:

Resilient neoprene inserts provide an outstanding moisture barrier, high dielectric strength, and resistance to vibration. Either pin or socket insert can be pressurized.


#### Strain Relief Clamp:

Strain relief clamps minimize tension at the solder well connection and provide a positive mechanical moisture seal. Complete field serviceability is possible with the strain relief clamp.

# MS/Standard

## MS3100E/F

### wall mounting receptacle




To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.

| Shell Size | A Thread Class 2A | B Min. Full Thread | K $+0.020$ $-0.010$ | L Max. | M $+0.010$ $-0.000$ | P Max. | R $\pm 0.005$ | S $\pm 0.010$ | T Dia. $+0.004$ $-0.002$ | Z* Max. | XX Min. Cable Clearance |
|------------|-------------------|--------------------|---------------------|--------|---------------------|--------|---------------|---------------|--------------------------|---------|-------------------------|
| 10SL       | .6250-24UNEF      | .391               | .672                | 2.129  | .562                | .896   | .719          | 1.000         | .120                     | .472    | .281                    |
| 12S        | .7500-20UNEF      | .450               | .672                | 2.129  | .562                | .896   | .812          | 1.094         | .120                     | .472    | .281                    |
| 12         | .7500-20UNEF      | .625               | .860                | 2.129  | .750                | .896   | .812          | 1.094         | .120                     | .722    | .281                    |
| 14S        | .8750-20UNEF      | .450               | .672                | 2.201  | .562                | 1.021  | .906          | 1.188         | .120                     | .472    | .406                    |
| 14         | .8750-20UNEF      | .625               | .860                | 2.524  | .750                | 1.021  | .906          | 1.188         | .120                     | .722    | .406                    |
| 16S        | 1.0000-20UNEF     | .450               | .672                | 2.201  | .562                | 1.151  | .969          | 1.281         | .120                     | .472    | .500                    |
| 16         | 1.0000-20UNEF     | .625               | .860                | 2.524  | .750                | 1.151  | .969          | 1.281         | .120                     | .722    | .500                    |
| 18         | 1.1250-18UNEF     | .625               | .891                | 2.596  | .750                | 1.242  | 1.063         | 1.375         | .120                     | .691    | .531                    |
| 20         | 1.2500-18UNEF     | .625               | .891                | 2.654  | .750                | 1.499  | 1.156         | 1.500         | .120                     | .691    | .656                    |
| 22         | 1.3750-18UNEF     | .625               | .891                | 2.654  | .750                | 1.499  | 1.250         | 1.625         | .120                     | .691    | .740                    |
| 24         | 1.5000-18UNEF     | .625               | .953                | 2.885  | .812                | 1.781  | 1.375         | 1.750         | .147                     | .628    | .781                    |
| 28         | 1.7500-18UNS      | .625               | .953                | 2.885  | .812                | 1.781  | 1.562         | 2.000         | .147                     | .628    | .922                    |
| 32         | 2.0000-18UNS      | .625               | 1.031               | 2.943  | .875                | 2.087  | 1.750         | 2.250         | .173                     | .550    | 1.156                   |
| 36         | 2.2500-16UN       | .625               | 1.031               | 2.943  | .875                | 2.281  | 1.938         | 2.500         | .173                     | .550    | 1.250                   |
| 40         | 2.5000-16UN       | .625               | 1.031               | 3.068  | .875                | 2.581  | 2.188         | 2.750         | .173                     | .550    | 1.562                   |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard MS3101E/F cable connecting plug



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.


| Shell Size | A Thread Class 2A | B Min. Full Thread | J Max. | L Max. | Z* Max. | XX Min. Cable Clearance |
|------------|-------------------|--------------------|--------|--------|---------|-------------------------|
| 10SL       | .6250-24UNEF      | .406               | .896   | 2.129  | 1.134   | .281                    |
| 12S        | .7500-20UNEF      | .422               | .896   | 2.129  | 1.134   | .281                    |
| 12         | .7500-20UNEF      | .656               | .896   | 2.129  | 1.572   | .281                    |
| 14S        | .8750-20UNEF      | .391               | 1.021  | 2.201  | 1.134   | .406                    |
| 14         | .8750-20UNEF      | .625               | 1.021  | 2.524  | 1.572   | .406                    |
| 16S        | 1.0000-20UNEF     | .391               | 1.151  | 2.201  | 1.134   | .500                    |
| 16         | 1.0000-20UNEF     | .625               | 1.151  | 2.524  | 1.572   | .500                    |
| 18         | 1.1250-18UNEF     | .625               | 1.242  | 2.596  | 1.572   | .531                    |
| 20         | 1.2500-18UNEF     | .625               | 1.499  | 2.654  | 1.572   | .656                    |
| 22         | 1.3750-18UNEF     | .625               | 1.499  | 2.654  | 1.572   | .740                    |
| 24         | 1.5000-18UNEF     | .625               | 1.781  | 2.885  | 1.572   | .781                    |
| 28         | 1.7500-18UNS      | .625               | 1.781  | 2.885  | 1.572   | .922                    |
| 32         | 2.0000-18UNS      | .625               | 2.087  | 2.943  | 1.572   | 1.156                   |
| 36         | 2.2500-16UN       | .625               | 2.281  | 2.943  | 1.572   | 1.250                   |
| 40         | 2.5000-16UN       | .625               | 2.581  | 3.068  | 1.572   | 1.562                   |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS3102E

### box mounting receptacle



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.


| Shell Size | A Thread Class 2A | B Min. Full Thread | K $+0.020$ $-0.010$ | L $+0.000$ $-0.010$ | M $+0.010$ $-0.000$ | N Dia. $+0.010$ $-0.000$ | R $\pm 0.005$ | S $\pm 0.031$ | T Dia. $+0.004$ $-0.002$ | Z $+0.050$ $-0.060$ |
|------------|-------------------|--------------------|---------------------|---------------------|---------------------|--------------------------|---------------|---------------|--------------------------|---------------------|
| 8S         | .5000-28UNEF      | .391               | .672                | .297                | .562                | .375                     | .594          | .875          | .120                     | .422                |
| 10S        | .6250-24NEF       | .391               | .672                | .297                | .562                | .500                     | .719          | 1.000         | .120                     | .422                |
| 10SL       | .6250-24NEF       | .391               | .672                | .297                | .562                | .625                     | .719          | 1.000         | .120                     | .422                |
| 12S        | .7500-20UNEF      | .450               | .672                | .297                | .562                | .625                     | .812          | 1.094         | .120                     | .422                |
| 12         | .7500-20UNEF      | .625               | .860                | .484                | .750                | .625                     | .812          | 1.094         | .120                     | .672                |
| 14S        | .8750-20UNEF      | .450               | .672                | .297                | .562                | .750                     | .906          | 1.188         | .120                     | .422                |
| 14         | .8750-20UNEF      | .625               | .860                | .484                | .750                | .750                     | .906          | 1.188         | .120                     | .672                |
| 16S        | 1.0000-20UNEF     | .450               | .672                | .297                | .562                | .875                     | .969          | 1.281         | .120                     | .422                |
| 16         | 1.0000-20UNEF     | .625               | .860                | .484                | .750                | .875                     | .969          | 1.281         | .120                     | .672                |
| 18         | 1.1250-18NEF      | .625               | .891                | .453                | .750                | 1.000                    | 1.062         | 1.375         | .120                     | .641*               |
| 20         | 1.2500-18NEF      | .625               | .891                | .453                | .750                | 1.125                    | 1.156         | 1.500         | .120                     | .641*               |
| 22         | 1.3750-18NEF      | .625               | .891                | .453                | .750                | 1.250                    | 1.250         | 1.625         | .120                     | .641*               |
| 24         | 1.5000-18NEF      | .625               | .953                | .453                | .812                | 1.375                    | 1.375         | 1.750         | .147                     | .578*               |
| 28         | 1.7500-18NS       | .625               | .953                | .453                | .812                | 1.625                    | 1.562         | 2.000         | .147                     | .578*               |
| 32         | 2.0000-18NS       | .625               | 1.031               | .438                | .875                | 1.875                    | 1.750         | 2.250         | .173                     | .500*               |
| 36         | 2.2500-16UN       | .625               | 1.031               | .438                | .875                | 2.062                    | 1.938         | 2.500         | .173                     | .500*               |
| 40         | 2.5000-16UN       | .625               | 1.031               | .438                | .875                | 2.312                    | 2.188         | 2.750         | .173                     | .500*               |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS3106E/F

### straight plug



To complete order number, see "how to order" pg. 70.  
 For solder well data, see page 67.  
 All lockwire holes are .045 dia. min.


| Shell Size | A Thread Class 2A | B ±.005 | J Max. | L Max. | Q Max. | Z* ±.045 | XX Min. Cable Clearance |
|------------|-------------------|---------|--------|--------|--------|----------|-------------------------|
| 10SL       | .6250-24UNEF      | .531    | .896   | 2.129  | .946   | .607     | .281                    |
| 12S        | .7500-20UNEF      | .531    | .896   | 2.129  | .995   | .607     | .281                    |
| 12         | .7500-20UNEF      | .719    | .896   | 2.129  | .995   | .857     | .281                    |
| 14S        | .8750-20UNEF      | .531    | 1.021  | 2.201  | 1.123  | .607     | .406                    |
| 14         | .8750-20UNEF      | .719    | 1.021  | 2.524  | 1.123  | .857     | .406                    |
| 16S        | 1.0000-20UNEF     | .531    | 1.151  | 2.201  | 1.250  | .607     | .500                    |
| 16         | 1.0000-20UNEF     | .719    | 1.151  | 2.524  | 1.250  | .857     | .500                    |
| 18         | 1.1250-18UNEF     | .719    | 1.242  | 2.596  | 1.333  | .857     | .531                    |
| 20         | 1.2500-18UNEF     | .719    | 1.499  | 2.654  | 1.461  | .857     | .656                    |
| 22         | 1.3750-18UNEF     | .719    | 1.499  | 2.654  | 1.588  | .857     | .740                    |
| 24         | 1.5000-18UNEF     | .719    | 1.781  | 2.885  | 1.715  | .857     | .781                    |
| 28         | 1.7500-18UNS      | .719    | 1.781  | 2.885  | 1.968  | .857     | .922                    |
| 32         | 2.0000-18UNS      | .719    | 2.087  | 2.943  | 2.209  | .857     | 1.156                   |
| 36         | 2.2500-16UN       | .719    | 2.281  | 2.943  | 2.463  | .857     | 1.250                   |
| 40         | 2.5000-16UN       | .719    | 2.581  | 3.068  | 2.718  | .857     | 1.562                   |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS3108E

### 90 degree plug



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.  
All lockwire holes are .045 dia. min.

| Shell Size | A Thread Class 2B | J $\pm .005$ | L Max. | N Max. | Q Dia. Max. | U Max. | Y Thread Class 2B | Z $\pm .045$ |
|------------|-------------------|--------------|--------|--------|-------------|--------|-------------------|--------------|
| 8S         | .5000-28UNEF      | .531         | .927   | .807   | .741        | 1.445  | 6-32NC            | .562         |
| 10S        | .6250-24NEF       | .531         | .927   | .807   | .869        | 1.445  | 6-32NC            | .562         |
| 10SL       | .6250-24NEF       | .531         | .951   | .901   | .946        | 1.508  | 6-32NC            | .562         |
| 12S        | .7500-20UNEF      | .531         | .956   | .901   | .995        | 1.508  | 6-32NC            | .562         |
| 12         | .7500-20UNEF      | .719         | 1.143  | .901   | .995        | 1.508  | 6-32NC            | .812         |
| 14S        | .8750-20UNEF      | .531         | 1.020  | 1.026  | 1.123       | 1.570  | 6-32NC            | .562         |
| 14         | .8750-20UNEF      | .719         | 1.207  | 1.026  | 1.123       | 1.570  | 6-32NC            | .812         |
| 16S        | 1.0000-20UNEF     | .531         | 1.146  | 1.119  | 1.250       | 1.633  | 6-32NC            | .562         |
| 16         | 1.1000-20UNEF     | .719         | 1.333  | 1.119  | 1.250       | 1.633  | 6-32NC            | .812         |
| 18         | 1.1250-18NEF      | .719         | 1.395  | 1.229  | 1.333       | 1.759  | 6-32NC            | .812*        |
| 20         | 1.2500-18NEF      | .719         | 1.598  | 1.479  | 1.461       | 1.931  | 8-32NC            | .812*        |
| 22         | 1.3750-18NEF      | .719         | 1.598  | 1.479  | 1.588       | 1.993  | 8-32NC            | .812*        |
| 24         | 1.5000-18NEF      | .719         | 1.786  | 1.666  | 1.729       | 2.119  | 8-32NC            | .812*        |
| 28         | 1.7500-18NS       | .719         | 1.786  | 1.666  | 1.968       | 2.181  | 8-32NC            | .812*        |
| 32         | 2.0000-18NS       | .719         | 2.020  | 2.135  | 2.209       | 2.570  | 10-32NF           | .812*        |
| 36         | 2.2500-16UN       | .719         | 2.145  | 2.260  | 2.463       | 2.695  | 10-32NF           | .812*        |
| 40         | 2.5000-16UN       | .719         | 2.270  | 2.510  | 2.719       | 2.851  | 10-32NF           | .812*        |


\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS-R



**wall mounting receptacle**



**cable connecting plug**



**box mounting receptacle**



**straight plug**

### MS-R

Specification requirements for greater reliability in a shorter, lighter weight environmental resistant connector led to the design of the MS-R. MS Class R connectors satisfy all the performance requirements of MIL-DTL-5015.

This low profile assembly was attained by moving the axial compression nut and grommet assembly forward and flush with the rear of the insert. The neoprene grommet, with its low coefficient of friction, assures easier threading of wire bundles and quicker assembly and serviceability of the unit. Molded webs in each wire hole insure a moisture barrier around each wire.

The addition of an "O" ring at the main joint of all MS3106R plugs provide a main joint seal supplementary to the interfacial seal, thus insuring a higher degree of reliability when connector halves from different sources are employed. MS-R types are recommended for new design applications.

#### Shells:

Shell components are fabricated from high grade aluminum alloy. All components have the standard electrically conductive cadmium plated finish with an olive drab chromate after-treatment for corrosion resistance. Consult Amphenol, Sidney, NY for other plating options.

#### Contacts:

Contacts are machined from copper alloy for maximum corrosion resistance, maximum current carrying capacity and low millivolt drop. Both crimp and solder versions are available. Refer to pages 49, 67 and 68 for additional contact information.


#### Inserts:

Resilient neoprene inserts provide an outstanding moisture barrier, maximum vibration resistance and high dielectric strength. Either pin or socket insert can be pressurized.

# MS/Standard

## MS3100R

### wall mounting receptacle



To complete order number, see "how to order" pg. 70.  
 For solder well data, see page 67.  
 All lockwire holes are .045 dia. min.


| Shell Size | A Thread Class 2A | B Min. Full Thread | H Dia. Max. | K $+0.020$ $-0.010$ | L Max. | M $+0.010$ $-0.000$ | P Dia. Max. | R $\pm 0.005$ | S $\pm 0.031$ | Y Thread Class 2 | T Dia. $+0.004$ $-0.002$ | Z $+0.050$ $-0.060$ |
|------------|-------------------|--------------------|-------------|---------------------|--------|---------------------|-------------|---------------|---------------|------------------|--------------------------|---------------------|
| 8S         | .5000-28UNEF      | .391               | .959        | .672                | 1.588  | .562                | .557        | .594          | .875          | 6-32NC           | .120                     | .422                |
| 10S        | .6250-24NEF       | .391               | 1.026       | .672                | 1.588  | .562                | .682        | .719          | 1.000         | 6-32NC           | .120                     | .422                |
| 10SL       | .6250-24NEF       | .391               | 1.120       | .672                | 1.588  | .562                | .807        | .719          | 1.000         | 6-32NC           | .120                     | .422                |
| 12S        | .7500-20UNEF      | .450               | 1.120       | .672                | 1.588  | .562                | .807        | .812          | 1.094         | 6-32NC           | .120                     | .422                |
| 12         | .7500-20UNEF      | .625               | 1.120       | .860                | 1.931  | .750                | .807        | .812          | 1.094         | 6-32NC           | .120                     | .672                |
| 14S        | .8750-20UNEF      | .450               | 1.307       | .672                | 1.588  | .562                | .932        | .906          | 1.188         | 6-32NC           | .120                     | .422                |
| 14         | .8750-20UNEF      | .625               | 1.307       | .860                | 1.931  | .750                | .932        | .906          | 1.188         | 6-32NC           | .120                     | .672                |
| 16S        | 1.0000-20UNEF     | .450               | 1.432       | .672                | 1.588  | .562                | 1.057       | .969          | 1.281         | 6-32NC           | .120                     | .422                |
| 16         | 1.0000-20UNEF     | .625               | 1.432       | .860                | 1.931  | .750                | 1.057       | .969          | 1.281         | 6-32NC           | .120                     | .672                |
| 18         | 1.1250-18NEF      | .625               | 1.557       | .891                | 1.931  | .750                | 1.182       | 1.063         | 1.375         | 6-32NC           | .120                     | .641*               |
| 20         | 1.2500-18NEF      | .625               | 1.744       | .891                | 1.931  | .750                | 1.291       | 1.156         | 1.500         | 8-32NC           | .120                     | .641*               |
| 22         | 1.3750-18NEF      | .625               | 1.869       | .891                | 1.931  | .750                | 1.432       | 1.250         | 1.625         | 8-32NC           | .120                     | .641*               |
| 24         | 1.5000-18NEF      | .625               | 1.994       | .953                | 2.009  | .812                | 1.557       | 1.375         | 1.750         | 8-32NC           | .147                     | .578*               |
| 28         | 1.7500-18NS       | .625               | 2.166       | .953                | 2.009  | .812                | 1.807       | 1.562         | 2.000         | 8-32NC           | .147                     | .578*               |
| 32         | 2.0000-18NS       | .625               | 2.541       | 1.031               | 2.072  | .875                | 2.057       | 1.750         | 2.250         | 10-32NF          | .173                     | .500*               |
| 36         | 2.2500-16UN       | .625               | 2.729       | 1.031               | 2.072  | .875                | 2.260       | 1.938         | 2.500         | 10-32NF          | .173                     | .500*               |
| 40         | 2.5000-16UN       | .625               | 2.979       | 1.031               | 2.072  | .875                | 2.260       | 2.510         | 2.750         | 10-32NF          | .173                     | .500*               |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS3101R

### cable connecting plug



To complete order number, see “how to order” pg. 70.  
 For solder well data, see page 67.  
 All lockwire holes are .045 dia. min.


| Shell Size | A Thread Class 2A | B Min. Full Thread | F Dia. Max. | J Dia. Max. | L Max. | Y Thread Class 2 | Z ±.040 |
|------------|-------------------|--------------------|-------------|-------------|--------|------------------|---------|
| 8S         | .5000-28UNEF      | .406               | .959        | .557        | 1.588  | 6-32NC           | 1.094   |
| 10S        | .6250-24NEF       | .406               | 1.026       | .682        | 1.588  | 6-32NC           | 1.094   |
| 10SL       | .6250-24NEF       | .406               | 1.120       | .807        | 1.588  | 6-32NC           | 1.094   |
| 12S        | .7500-20UNEF      | .422               | 1.120       | .807        | 1.588  | 6-32NC           | 1.094   |
| 12         | .7500-20UNEF      | .656               | 1.120       | .807        | 1.931  | 6-32NC           | 1.532   |
| 14S        | .8750-20UNEF      | .391               | 1.307       | .932        | 1.588  | 6-32NC           | 1.094   |
| 14         | .8750-20UNEF      | .625               | 1.307       | .932        | 1.931  | 6-32NC           | 1.532   |
| 16S        | 1.0000-20UNEF     | .391               | 1.432       | 1.057       | 1.588  | 6-32NC           | 1.094   |
| 16         | 1.0000-20UNEF     | .625               | 1.432       | 1.057       | 1.931  | 6-32NC           | 1.532   |
| 18         | 1.1250-18NEF      | .625               | 1.557       | 1.182       | 1.931  | 6-32NC           | 1.532*  |
| 20         | 1.2500-18NEF      | .625               | 1.744       | 1.291       | 1.931  | 8-32NC           | 1.532*  |
| 22         | 1.3750-18NEF      | .625               | 1.869       | 1.432       | 1.931  | 8-32NC           | 1.532*  |
| 24         | 1.5000-18NEF      | .625               | 1.994       | 1.557       | 2.009  | 8-32NC           | 1.532*  |
| 28         | 1.7500-18NS       | .625               | 2.166       | 1.807       | 2.009  | 8-32NC           | 1.532*  |
| 32         | 2.0000-18NS       | .625               | 2.541       | 2.057       | 2.072  | 10-32NF          | 1.532*  |
| 36         | 2.2500-16UN       | .625               | 2.729       | 2.260       | 2.072  | 10-32NF          | 1.532*  |
| 40         | 2.5000-16UN       | .625               | 2.979       | 2.510       | 2.072  | 10-32NF          | 1.532*  |

\* Increase Z dimension by .312 for size “0” contact only.

# MS/Standard

## MS3102R

### box mounting receptacle



To complete order number, see "how to order" pg. 70.  
For solder well data, see page 67.


| Shell Size | A Thread Class 2A | B Min. Full Thread | K $+0.020$ $-0.010$ | L $+0.000$ $-0.010$ | M $+0.010$ $-0.000$ | N Dia. $+0.010$ $-0.000$ | R $\pm 0.005$ | S $\pm 0.031$ | T Dia. $+0.004$ $-0.002$ | Z $+0.050$ $-0.060$ |
|------------|-------------------|--------------------|---------------------|---------------------|---------------------|--------------------------|---------------|---------------|--------------------------|---------------------|
| 8S         | .5000-28UNEF      | .391               | .672                | .297                | .562                | .375                     | .594          | .875          | .120                     | .422                |
| 10S        | .6250-24NEF       | .391               | .672                | .297                | .562                | .500                     | .719          | 1.000         | .120                     | .422                |
| 10SL       | .6250-24NEF       | .391               | .672                | .297                | .562                | .625                     | .719          | 1.000         | .120                     | .422                |
| 12S        | .7500-20UNEF      | .450               | .672                | .297                | .562                | .625                     | .812          | 1.094         | .120                     | .422                |
| 12         | .7500-20UNEF      | .625               | .860                | .484                | .750                | .625                     | .812          | 1.094         | .120                     | .672                |
| 14S        | .8750-20UNEF      | .450               | .672                | .297                | .562                | .750                     | .906          | 1.188         | .120                     | .422                |
| 14         | .8750-20UNEF      | .625               | .860                | .484                | .750                | .750                     | .906          | 1.188         | .120                     | .672                |
| 16S        | 1.0000-20UNEF     | .450               | .672                | .297                | .562                | .875                     | .969          | 1.281         | .120                     | .422                |
| 16         | 1.0000-20UNEF     | .625               | .860                | .484                | .750                | .875                     | .969          | 1.281         | .120                     | .672                |
| 18         | 1.1250-18NEF      | .625               | .891                | .453                | .750                | 1.000                    | 1.062         | 1.375         | .120                     | .641*               |
| 20         | 1.2500-18NEF      | .625               | .891                | .453                | .750                | 1.125                    | 1.156         | 1.500         | .120                     | .641*               |
| 22         | 1.3750-18NEF      | .625               | .891                | .453                | .750                | 1.250                    | 1.250         | 1.625         | .120                     | .641*               |
| 24         | 1.5000-18NEF      | .625               | .953                | .453                | .812                | 1.375                    | 1.375         | 1.750         | .147                     | .578*               |
| 28         | 1.7500-18NS       | .625               | .953                | .453                | .812                | 1.625                    | 1.562         | 2.000         | .147                     | .578*               |
| 32         | 2.0000-18NS       | .625               | 1.031               | .438                | .875                | 1.875                    | 1.750         | 2.250         | .173                     | .500*               |
| 36         | 2.2500-16UN       | .625               | 1.031               | .438                | .875                | 2.062                    | 1.938         | 2.500         | .173                     | .500*               |
| 40         | 2.5000-16UN       | .625               | 1.031               | .438                | .875                | 2.312                    | 2.188         | 2.750         | .173                     | .500*               |

\* Increase Z dimension by .312 for size "0" contact only.

# MS/Standard

## MS3106R

### straight plug



To complete order number, see “how to order” pg. 70.  
 For solder well data, see page 67.  
 All lockwire holes are .045 dia. min.

| Shell Size | A Thread Class 2B | F Dia. Max. | J ±.005 | L Max. | N Dia. Max. | Q Dia. Max. | Y Thread Class 2 | Z ±.045 |
|------------|-------------------|-------------|---------|--------|-------------|-------------|------------------|---------|
| 8S         | .5000-28UNEF      | .959        | .531    | 1.057  | .557        | .741        | 6-32NC           | .562    |
| 10S        | .6250-24NEF       | 1.026       | .531    | 1.057  | .682        | .869        | 6-32NC           | .562    |
| 10SL       | .6250-24NEF       | 1.120       | .531    | 1.057  | .807        | .946        | 6-32NC           | .562    |
| 12S        | .7500-20UNEF      | 1.120       | .531    | 1.057  | .807        | .995        | 6-32NC           | .562    |
| 12         | .7500-20UNEF      | 1.120       | .719    | 1.212  | .807        | .995        | 6-32NC           | .812    |
| 14S        | .8750-20UNEF      | 1.307       | .531    | 1.057  | .932        | 1.123       | 6-32NC           | .562    |
| 14         | .8750-20UNEF      | 1.307       | .719    | 1.212  | .932        | 1.123       | 6-32NC           | .812    |
| 16S        | 1.0000-20UNEF     | 1.432       | .531    | 1.057  | 1.057       | 1.250       | 6-32NC           | .562    |
| 16         | 1.0000-20UNEF     | 1.432       | .719    | 1.212  | 1.057       | 1.250       | 6-32NC           | .812    |
| 18         | 1.1250-18NEF      | 1.557       | .719    | 1.212  | 1.182       | 1.333       | 6-32NC           | .812*   |
| 20         | 1.2500-18NEF      | 1.744       | .719    | 1.212  | 1.291       | 1.461       | 8-32NC           | .812*   |
| 22         | 1.3750-18NEF      | 1.869       | .719    | 1.212  | 1.432       | 1.588       | 8-32NC           | .812*   |
| 24         | 1.5000-18NEF      | 1.994       | .719    | 1.291  | 1.557       | 1.715       | 8-32NC           | .812*   |
| 28         | 1.7500-18NS       | 2.166       | .719    | 1.291  | 1.807       | 1.968       | 8-32NC           | .812*   |
| 32         | 2.0000-18NS       | 2.541       | .719    | 1.353  | 2.057       | 2.209       | 10-32NF          | .812*   |
| 36         | 2.2500-16UN       | 2.729       | .719    | 1.353  | 2.260       | 2.463       | 10-32NF          | .812*   |
| 40         | 2.5000-16UN       | 2.979       | .719    | 1.353  | 2.510       | 2.719       | 10-32NF          | .812*   |

\* Increase Z dimension by .312 for size "0" contact only.

**MS/Standard**  
contact and  
insert arrangements

# MS/Standard

## insert arrangements

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 8S-1               | A              | 1              |              |   |   |    | 1  |
| 10S-2              | A              | 1              |              |   |   |    | 1  |
| 10SL-3             | A              | 3              |              |   |   |    | 3  |
| 10SL-4†            | A              | 2              |              |   |   |    | 2  |
| 12S-3              | A              | 2              |              |   |   |    | 2  |
| 12S-4              | D              | 1              |              |   |   |    | 1  |
| 12-5               | D              | 1              |              |   |   | 1  |    |
| 14S-1              | A              | 3              |              |   |   |    | 3  |
| 14S-2              | Inst.          | 4              |              |   |   |    | 4  |
| 14S-4              | D              | 1              |              |   |   |    | 1  |
| 14S-5              | Inst.          | 5              |              |   |   |    | 5  |
| 14S-6              | Inst.          | 6              |              |   |   |    | 6  |
| 14S-7              | A              | 3              |              |   |   |    | 3  |
| 14S-9              | A              | 2              |              |   |   |    | 2  |
| 14S-10             | Inst.          | 4              |              |   |   |    | 4  |
| 14S-12             | A              | 3              |              |   |   |    | 3  |
| 14-3               | A              | 1              |              |   | 1 |    |    |
| 16S-1              | A              | 7              |              |   |   |    | 7  |
| 16S-3              | B              | 1              |              |   |   |    | 1  |
| 16S-4              | D              | 2              |              |   |   |    | 2  |
| 16S-5              | A              | 3              |              |   |   |    | 3  |
| 16S-6              | A              | 3              |              |   |   |    | 3  |
| 16S-8              | A              | 5              |              |   |   |    | 5  |
| 16-2               | E              | 1              |              |   |   | 1  |    |
| 16-7               | A              | 3              |              |   | 1 |    | 2  |
| 16-9               | A              | 4              |              |   |   | 2  | 2  |
| 16-10              | A              | 3              |              |   |   | 3  |    |
| 16-11              | A              | 2              |              |   |   | 2  |    |
| 16-12              | A              | 1              |              | 1 |   |    |    |
| 16-13              | A              | 2              |              |   |   | 2  |    |
| 18-1               | A/Inst.        | 10             |              |   |   |    | 10 |
| 18-3               | D              | 2              |              |   |   | 2  |    |
| 18-4               | D              | 4              |              |   |   |    | 4  |
| 18-5               | D              | 3              |              |   |   | 2  | 1  |
| 18-6               | D              | 1              |              | 1 |   |    |    |
| 18-7               | B              | 1              |              |   | 1 |    |    |
| 18-8               | A              | 8              |              |   |   | 1  | 7  |
| 18-9               | Inst.          | 7              |              |   |   | 2  | 5  |
| 18-10              | A              | 4              |              |   |   | 4  |    |
| 18-11              | A              | 5              |              |   |   | 5  |    |
| 18-12              | A              | 6              |              |   |   |    | 6  |
| 18-13              | A              | 4              |              |   | 1 | 3  |    |
| 18-14              | A              | 2              |              | 1 |   |    | 1  |
| 18-15              | A              | 4              |              |   |   | 4  |    |
| 18-16              | C              | 1              |              |   |   | 1  |    |
| 18-17              | Inst.          | 7              |              |   |   | 2  | 5  |
| 18-19              | A              | 10             |              |   |   |    | 10 |
| 18-20              | A              | 5              |              |   |   |    | 5  |
| 18-22              | D              | 3              |              |   |   |    | 3  |
| 18-24              | A/Inst.        | 10             |              |   |   |    | 10 |
| 18-29              | A              | 5              |              |   |   |    | 5  |
| 18-30              | A              | 5              |              |   |   |    | 5  |

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 18-31              | A              | 5              |              |   |   |    | 5  |
| 20-2               | D              | 1              | 1            |   |   |    |    |
| 20-3               | D              | 3              |              |   |   | 3  |    |
| 20-4               | D              | 4              |              |   |   | 4  |    |
| 20-6               | D              | 3              |              |   |   |    | 3  |
| 20-7               | D/A            | 8              |              |   |   |    | 8  |
| 20-8               | Inst.          | 6              |              |   | 2 |    | 4  |
| 20-9               | D/A            | 8              |              |   |   | 1  | 7  |
| 20-11              | Inst.          | 13             |              |   |   |    | 13 |
| 20-12              | A              | 2              |              | 1 |   |    | 1  |
| 20-14              | A              | 5              |              |   | 2 | 3  |    |
| 20-15              | A              | 7              |              |   |   | 7  |    |
| 20-16              | A              | 9              |              |   |   | 2  | 7  |
| 20-17              | A              | 6              |              |   |   | 5  | 1  |
| 20-18              | A              | 9              |              |   |   | 3  | 6  |
| 20-19              | A              | 3              |              |   | 3 |    |    |
| 20-20              | A              | 4              |              | 1 |   | 3  |    |
| 20-21              | A              | 9              |              |   |   | 1  | 8  |
| 20-22              | A              | 6              |              |   | 3 |    | 3  |
| 20-23              | A              | 2              |              |   | 2 |    |    |
| 20-24              | A              | 4              |              |   | 2 |    | 2  |
| 20-25              | Inst.          | 13             |              |   |   |    | 13 |
| 20-27              | A              | 14             |              |   |   |    | 14 |
| 20-29              | A              | 17             |              |   |   |    | 17 |
| 20-30              | Inst.          | 13             |              |   |   |    | 13 |
| 20-33              | A              | 11             |              |   |   |    | 11 |
| 22-1               | D              | 2              |              |   | 2 |    |    |
| 22-2               | D              | 3              |              |   | 3 |    |    |
| 22-4               | A              | 4              |              |   | 2 | 2  |    |
| 22-5               | D              | 6              |              |   |   | 2  | 4  |
| 22-6               | D              | 3              |              |   | 2 |    | 1  |
| 22-7               | E              | 1              | 1            |   |   |    |    |
| 22-8               | E              | 2              |              |   |   | 2  |    |
| 22-9               | E              | 3              |              |   |   | 3  |    |
| 22-10              | E              | 4              |              |   |   |    | 4  |
| 22-11              | B              | 2              |              |   |   |    | 2  |
| 22-12              | D              | 5              |              |   | 2 |    | 3  |
| 22-13              | D/A            | 5              |              |   |   | 4  | 1  |
| 22-14              | A              | 19             |              |   |   |    | 19 |
| 22-15              | E/A            | 6              |              |   |   | 5  | 1  |
| 22-16              | A              | 9              |              |   |   | 3  | 6  |
| 22-17              | D/A            | 9              |              |   |   | 1  | 8  |
| 22-18              | D/A            | 8              |              |   |   |    | 8  |
| 22-19              | A              | 14             |              |   |   |    | 14 |
| 22-20              | A              | 9              |              |   |   |    | 9  |
| 22-21              | A              | 3              | 1            |   |   |    | 2  |
| 22-22              | A              | 4              |              |   | 4 |    |    |
| 22-23              | D/A            | 8              |              |   |   | 8  |    |
| 22-24              | D/A            | 6              |              |   |   | 2  | 4  |
| 22-27              | D/A            | 9              |              |   | 1 |    | 8  |
| 22-28              | A              | 7              |              |   |   | 7  |    |

† 10SL-4 arrangement available only with pin contacts in receptacle and socket contacts in plug

# MS/Standard

## insert arrangements, cont.

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 22-33              | D/A            | 7              |              |   |   |    | 7  |
| 22-34              | D              | 5              |              |   |   | 3  | 2  |
| 22-36              | D/A            | 8              |              |   |   | 8  |    |
| 24-2               | D              | 7              |              |   |   | 7  |    |
| 24-3               | D              | 7              |              |   |   | 2  | 5  |
| 24-5               | A              | 16             |              |   |   |    | 16 |
| 24-6               | D/A            | 8              |              |   |   | 8  |    |
| 24-7               | A              | 16             |              |   |   | 2  | 14 |
| 24-9               | A              | 2              |              | 2 |   |    |    |
| 24-10              | A              | 7              |              |   | 7 |    |    |
| 24-11              | A              | 9              |              |   | 3 | 6  |    |
| 24-12              | A              | 5              |              | 2 |   | 3  |    |
| 24-16              | D/A            | 7              |              |   | 1 | 3  | 3  |
| 24-17              | D              | 5              |              |   |   | 2  | 3  |
| 24-20              | D              | 11             |              |   |   | 2  | 9  |
| 24-21              | D              | 10             |              |   | 1 |    | 9  |
| 24-22              | D              | 4              |              |   | 4 |    |    |
| 24-27              | E              | 7              |              |   |   |    | 7  |
| 24-28              | Inst.          | 24             |              |   |   |    | 24 |
| 28-1               | D/A            | 9              |              |   | 3 | 6  |    |
| 28-2               | D              | 14             |              |   |   | 2  | 12 |
| 28-3               | E              | 3              |              |   | 3 |    |    |
| 28-4               | E/D            | 9              |              |   |   | 2  | 7  |
| 28-5               | D              | 5              |              | 2 |   | 1  | 2  |
| 28-6               | D              | 3              |              | 3 |   |    |    |
| 28-7               | D              | 2              |              | 2 |   |    |    |
| 28-8               | E/D/A          | 12             |              |   |   | 2  | 10 |
| 28-9               | D              | 12             |              |   |   | 6  | 6  |
| 28-10              | D/A            | 7              |              | 2 | 2 | 3  |    |
| 28-11              | A              | 22             |              |   |   | 4  | 18 |
| 28-12              | A              | 26             |              |   |   |    | 26 |
| 28-13              | A              | 26             |              |   |   |    | 26 |
| 28-15              | A              | 35             |              |   |   |    | 35 |
| 28-16              | A              | 20             |              |   |   |    | 20 |
| 28-17              | B/D/A          | 15             |              |   |   |    | 15 |
| 28-18              | C/D/A/Inst.    | 12             |              |   |   |    | 12 |
| 28-19              | B/D/A          | 10             |              |   |   | 4  | 6  |
| 28-20              | A              | 14             |              |   |   | 10 | 4  |
| 28-21              | A              | 37             |              |   |   |    | 37 |
| 28-22              | D              | 6              |              | 3 |   |    | 3  |

| Insert Arrangement | Service Rating | Total Contacts | Contact Size |   |   |    |    |
|--------------------|----------------|----------------|--------------|---|---|----|----|
|                    |                |                | 0            | 4 | 8 | 12 | 16 |
| 32-1               | E/D            | 5              | 2            |   |   | 3  |    |
| 32-2               | E              | 5              |              | 3 |   |    | 2  |
| 32-3               | D              | 9              | 1            | 2 |   | 2  | 4  |
| 32-4               | A/D            | 14             |              |   |   | 2  | 12 |
| 32-5               | D              | 2              | 2            |   |   |    |    |
| 32-6               | A              | 23             |              | 2 | 3 | 2  | 16 |
| 32-7               | Inst./A        | 35             |              |   |   | 7  | 28 |
| 32-8               | A              | 30             |              |   |   | 6  | 24 |
| 32-9               | D              | 14             |              | 2 |   |    | 12 |
| 32-10              | E/B/D/A        | 7              |              | 2 | 2 |    | 3  |
| 32-12              | A/D            | 15             |              |   |   | 5  | 10 |
| 32-13              | D              | 23             |              |   |   | 5  | 18 |
| 32-15              | D              | 8              | 2            |   |   | 6  |    |
| 32-16              | A              | 23             |              | 2 | 3 | 2  | 16 |
| 32-17              | D              | 4              |              | 4 |   |    |    |
| 32-22              | A              | 54             |              |   |   |    | 54 |
| 36-1               | D              | 22             |              |   |   | 4  | 18 |
| 36-3               | D              | 6              | 3            |   |   | 3  |    |
| 36-4               | D/A            | 3              | 3            |   |   |    |    |
| 36-5               | A              | 4              | 4            |   |   |    |    |
| 36-6               | A              | 6              | 2            | 4 |   |    |    |
| 36-7               | A              | 47             |              |   |   | 7  | 40 |
| 36-8               | A              | 47             |              |   |   | 1  | 46 |
| 36-9               | A              | 31             |              | 1 | 2 | 14 | 14 |
| 36-10              | A              | 48             |              |   |   |    | 48 |
| 36-11              | A              | 48             |              |   |   |    | 48 |
| 36-12              | A              | 48             |              |   |   |    | 48 |
| 36-13              | E/A            | 17             |              |   |   | 2  | 15 |
| 36-14              | D              | 16             |              |   | 5 | 5  | 6  |
| 36-15              | D/A            | 35             |              |   |   |    | 35 |
| 36-16              | A              | 47             |              |   |   | 7  | 40 |
| 36-17              | A              | 47             |              |   |   | 7  | 40 |
| 36-18              | A              | 31             |              | 1 | 2 | 14 | 14 |
| 36-20              | A              | 34             |              |   | 2 | 2  | 30 |
| 36-52              | A              | 52             |              |   |   |    | 52 |
| 40-1               | D              | 30             |              |   |   | 6  | 24 |
| 40-9               | A              | 47             |              |   | 1 | 22 | 24 |
| 40-56              | A              | 85             |              |   |   |    | 85 |
| 48-62              | D              | 85             |              |   |   |    | 85 |

# MS/Standard

## special insert arrangements

| Insert<br>Arrange-<br>ment | Service<br>Rating | Total<br>Con-<br>tacts | Contact Size |     |   |   |    |    |    |        |   |   |    |  |
|----------------------------|-------------------|------------------------|--------------|-----|---|---|----|----|----|--------|---|---|----|--|
|                            |                   |                        | 4/0          | 2/0 | 0 | 4 | 8  | 12 | 16 | Coax** |   |   |    |  |
|                            |                   |                        |              |     |   |   |    |    |    | 0      | 4 | 8 | 12 |  |
| 14S-A7                     | A                 | 7                      |              |     |   |   |    |    | 7  |        |   |   |    |  |
| 16-59                      | A                 | 4                      |              |     |   |   |    | 4  |    |        |   |   |    |  |
| 20-26                      | A                 | 19                     |              |     |   |   |    |    | 19 |        |   |   |    |  |
| 20-51                      | A                 | 3                      |              |     |   |   | 3  |    |    |        |   |   |    |  |
| 20-57                      | A                 | 7                      |              |     |   |   |    | 7* |    |        |   |   |    |  |
| 20-58                      | A                 | 10                     |              |     |   |   |    | 5  | 5  |        |   |   |    |  |
| 20-59                      | A                 | 3                      |              |     |   |   | 3* |    |    |        |   |   |    |  |
| 20-66                      | A                 | 6                      |              |     |   |   |    | 5* | 1  |        |   |   |    |  |
| 20-79                      | A/D               | 8                      |              |     |   |   |    | 1  | 7  |        |   |   |    |  |
| 22-63                      | A                 | 12                     |              |     |   |   |    | 4  | 8  |        |   |   |    |  |
| 22-65                      | A/D               | 8                      |              |     |   |   |    | 8* |    |        |   |   |    |  |
| 22-70                      | A                 | 13                     |              |     |   |   |    | 8  | 5  |        |   |   |    |  |
| 22-80                      | A                 | 3                      |              |     |   |   | 3* |    |    |        |   |   |    |  |
| 24-19                      | A                 | 12                     |              |     |   |   |    |    | 12 |        |   |   |    |  |
| 24-51                      | A                 | 5                      |              |     |   |   | 5  |    |    |        |   |   |    |  |
| 24-52                      | Hi Volt.          | 1                      |              |     |   |   |    | 1  |    |        |   |   |    |  |
| 24-53                      | A                 | 5                      |              |     |   |   | 5  |    |    |        |   |   |    |  |
| 24-58                      | A                 | 13                     |              |     |   |   | 3  | 3  | 7  |        |   |   |    |  |
| 24-59                      | A                 | 14                     |              |     |   |   |    | 7  | 7  |        |   |   |    |  |
| 24-60                      | A                 | 7                      |              |     |   |   | 7* |    |    |        |   |   |    |  |
| 24-65                      | A                 | 15                     |              |     |   |   |    | 11 | 4  |        |   |   |    |  |
| 24-66                      | D                 | 7                      |              |     |   |   |    | 7  |    |        |   |   |    |  |
| 24-67                      | Inst.             | 19                     |              |     |   |   |    | 19 |    |        |   |   |    |  |
| 24-71                      | A                 | 7                      |              |     |   |   | 7* |    |    |        |   |   |    |  |
| 24-75                      | A                 | 7                      |              |     |   |   | 7* |    |    |        |   |   |    |  |
| 24-79                      | A                 | 5                      |              |     |   |   | 5  |    |    |        |   |   |    |  |
| 24-80                      | Inst.             | 23                     |              |     |   |   |    |    | 23 |        |   |   |    |  |
| 24-84                      | A                 | 19                     |              |     |   |   |    | 1  |    |        |   |   | 18 |  |
| 24-96                      | Inst.             | 28                     |              |     |   |   |    |    | 28 |        |   |   |    |  |
| 24-AJ                      | A                 | 25                     |              |     |   |   |    |    | 25 |        |   |   |    |  |
| 28-51                      | A                 | 12                     |              |     |   |   |    | 12 |    |        |   |   |    |  |
| 28-59                      | A                 | 17                     |              |     |   |   |    | 7  | 10 |        |   |   |    |  |
| 28-66                      | A                 | 16                     |              |     |   |   | 2  | 14 |    |        |   |   |    |  |
| 28-72                      | Coax              | 3                      |              |     |   |   |    |    |    |        | 3 |   |    |  |
| 28-74                      | A                 | 16                     |              |     |   |   | 7* |    | 9  |        |   |   |    |  |
| 28-75                      | A                 | 16                     |              |     |   |   | 7* |    | 9  |        |   |   |    |  |
| 28-79                      | A                 | 16                     |              |     |   |   | 7  |    | 9  |        |   |   |    |  |
| 28-82                      | D                 | 6                      |              |     |   |   | 2  | 4  |    |        |   |   |    |  |
| 28-84                      | A                 | 9                      |              |     |   |   | 9  |    |    |        |   |   |    |  |
| 28-AY                      | A                 | 9                      |              |     |   | 4 |    |    | 5  |        |   |   |    |  |
| 32-14                      | D                 | 13                     |              |     |   |   |    | 13 |    |        |   |   |    |  |
| 32-25                      | A                 | 25                     |              |     |   |   |    | 25 |    |        |   |   |    |  |
| 32-31                      | A                 | 31                     |              |     |   |   |    |    | 31 |        |   |   |    |  |
| 32-48                      | Inst.             | 48                     |              |     |   |   |    |    | 48 |        |   |   |    |  |
| 32-52                      | D                 | 8                      |              |     | 2 |   |    | 6  |    |        |   |   |    |  |
| 32-53                      | Inst./E           | 42                     |              |     |   |   |    | 5  | 37 |        |   |   |    |  |
| 32-56                      | A                 | 30                     |              |     |   |   |    | 6* | 24 |        |   |   |    |  |
| 32-57                      | Coax              | 8                      |              |     |   |   |    | 6  |    | 2      |   |   |    |  |
| 32-58                      | Coax              | 4                      |              |     |   |   |    |    |    |        | 4 |   |    |  |
| 32-59                      | A                 | 42                     |              |     |   |   |    |    | 40 |        |   | 2 |    |  |
| 32-60                      | A                 | 23                     |              |     |   |   |    |    | 15 |        |   | 8 |    |  |
| 32-62                      | Coax              | 23                     |              |     |   | 2 | 1  | 2  | 16 |        |   | 2 |    |  |
| 32-64                      | Inst.             | 54                     |              |     |   |   |    |    | 54 |        |   |   |    |  |
| 32-68                      | A                 | 16                     |              |     |   |   |    |    | 12 |        | 4 |   |    |  |
| 32-73                      | A                 | 46                     |              |     |   |   |    |    | 46 |        |   |   |    |  |
| 32-75                      | Coax              | 9                      |              |     |   |   |    | 2  |    |        |   | 7 |    |  |
| 32-76                      | A                 | 19                     |              |     |   |   |    | 19 |    |        |   |   |    |  |
| 32-79                      | D                 | 5                      |              |     |   | 4 | 1  |    |    |        |   |   |    |  |
| 32-82                      | A                 | 16                     |              |     |   | 4 |    |    | 12 |        |   |   |    |  |

\* Crimp contacts accommodate wire the same size as the contact as well as wire of the next smaller, even size. Arrangements identified with an asterisk (\*) are exceptions. See insert arrangement drawings on pages 38-48 for application wire size.

\*\* Coaxial cable data can be found on insert arrangement drawings, pages 38-48. For further information on special contacts and cable see catalog 10-100.


24

| Insert<br>Arrange-<br>ment | Service<br>Rating | Total<br>Con-<br>tacts | Contact Size |     |   |    |    |     |     |        |    |    |    |  |
|----------------------------|-------------------|------------------------|--------------|-----|---|----|----|-----|-----|--------|----|----|----|--|
|                            |                   |                        | 4/0          | 2/0 | 0 | 4  | 8  | 12  | 16  | Coax** |    |    |    |  |
|                            |                   |                        |              |     |   |    |    |     |     | 0      | 4  | 8  | 12 |  |
| 32-AF                      | A                 | 55                     |              |     |   |    |    |     | 55  |        |    |    |    |  |
| 36-22                      | D                 | 22                     |              |     |   |    |    | 22  |     |        |    |    |    |  |
| 36-51                      | D                 | 4                      |              |     | 2 | 2  |    |     |     |        |    |    |    |  |
| 36-54                      | A                 | 39                     |              |     |   |    | 8  |     | 31  |        |    |    |    |  |
| 36-55                      | A                 | 39                     |              |     |   |    | 8* |     | 31  |        |    |    |    |  |
| 36-59                      | A                 | 53                     |              |     |   |    |    | 3*  | 50  |        |    |    |    |  |
| 36-60                      | A                 | 47                     |              |     |   |    |    | 7*  | 40  |        |    |    |    |  |
| 36-64                      | Coax              | 4                      |              |     |   |    |    |     |     | 4      |    |    |    |  |
| 36-65                      | Coax              | 4                      |              |     |   |    |    |     |     | 4      |    |    |    |  |
| 36-71                      | A                 | 53                     |              |     |   |    |    | 3   | 50  |        |    |    |    |  |
| 36-73                      | Coax              | 7                      |              |     |   |    |    |     |     |        | 7  |    |    |  |
| 36-74                      | A                 | 44                     |              |     |   |    |    |     | 43  |        |    | 1  |    |  |
| 36-75                      | A                 | 48                     |              |     |   |    |    |     | 48* |        |    |    |    |  |
| 36-76                      | A                 | 47                     |              |     |   |    |    |     | 47  |        |    |    |    |  |
| 36-77                      | D                 | 7                      |              |     |   | 7  |    |     |     |        |    |    |    |  |
| 36-78                      | A                 | 14                     |              |     |   |    | 12 |     | 2   |        |    |    |    |  |
| 36-79                      | A                 | 20                     |              |     |   |    |    | 20  |     |        |    |    |    |  |
| 36-80                      | A                 | 20                     |              |     |   |    |    | 20* |     |        |    |    |    |  |
| 36-83                      | Coax              | 7                      |              |     |   |    |    |     |     |        | 7  |    |    |  |
| 36-85                      | A/D               | 35                     |              |     |   |    |    |     | 35* |        |    |    |    |  |
| 36-97                      | C                 | 1                      | 1            |     |   |    |    |     |     |        |    |    |    |  |
| 36-99                      | D                 | 12                     |              |     |   | 3  | 3  | 3   | 3   |        |    |    |    |  |
| 36-AF                      | A                 | 48                     |              |     |   |    |    |     | 48  |        |    |    |    |  |
| 40-5                       | A                 | 5                      |              |     | 5 |    |    |     |     |        |    |    |    |  |
| 40-10                      | A                 | 29                     |              |     |   | 4  | 9  |     | 16  |        |    |    |    |  |
| 40-30                      | A                 | 30                     |              |     |   | 1  |    | 29  |     |        |    |    |    |  |
| 40-35                      | D                 | 35                     |              |     |   |    |    | 35  |     |        |    |    |    |  |
| 40-53                      | A                 | 60                     |              |     |   |    |    |     | 60  |        |    |    |    |  |
| 40-57                      | E                 | 4                      |              |     | 4 |    |    |     |     |        |    |    |    |  |
| 40-61                      | A                 | 59                     |              |     |   |    | 1  | 3   | 55  |        |    |    |    |  |
| 40-62                      | A                 | 60                     |              |     |   |    |    |     | 60  |        |    |    |    |  |
| 40-63                      | A                 | 61                     |              |     |   |    |    |     | 61* |        |    |    |    |  |
| 40-64                      | Coax              | 36                     |              |     |   |    |    | 3   | 20  |        |    | 13 |    |  |
| 40-66                      | Coax              | 4                      |              |     |   |    |    |     |     | 4      |    |    |    |  |
| 40-67                      | A                 | 11                     |              |     |   |    |    |     | 1   |        | 10 |    |    |  |
| 40-68                      | A                 | 21                     |              |     |   |    | 21 |     |     |        |    |    |    |  |
| 40-70                      | A                 | 61                     |              |     |   |    |    |     | 61  |        |    |    |    |  |
| 40-72                      | A                 | 11                     |              |     |   |    |    |     | 1   |        | 10 |    |    |  |
| 40-73                      | A                 | 61                     |              |     |   |    |    |     | 61  |        |    |    |    |  |
| 40-74                      | A                 | 6                      |              |     |   |    |    | 1   |     | 4      | 1  |    |    |  |
| 40-75                      | E                 | 5                      |              |     | 4 |    |    | 1   |     |        |    |    |    |  |
| 40-80                      | A                 | 11                     |              |     |   | 10 |    |     | 1   |        |    |    |    |  |
| 40-81                      | A                 | 62                     |              |     |   |    |    |     | 62* |        |    |    |    |  |
| 40-82                      | A                 | 62                     |              |     |   |    |    |     | 62  |        |    |    |    |  |
| 40-85                      | A                 | 60                     |              |     |   |    |    |     | 60* |        |    |    |    |  |
| 40-86                      | E                 | 4                      |              |     |   |    |    |     |     | 4      |    |    |    |  |
| 40-87                      | D                 | 7                      |              |     |   | 7  |    |     |     |        |    |    |    |  |
| 40-AD                      | A                 | 8                      |              |     | 4 |    | 4  |     |     |        |    |    |    |  |
| 40-AG                      | A                 | 38                     |              |     |   |    |    | 38  |     |        |    |    |    |  |
| 40-AP                      | E                 | 2                      | 2            |     |   |    |    |     |     |        |    |    |    |  |
| 40-AR                      | Inst.             | 13                     |              |     | 3 | 3  |    | 7   |     |        |    |    |    |  |
| 40-AS                      | A                 | 40                     |              |     |   |    |    | 25  | 15  |        |    |    |    |  |
| 40-AT                      | A                 | 43                     |              |     |   |    | 1  | 24  | 18  |        |    |    |    |  |
| 40-AU                      | A                 | 14                     |              |     |   | 3  | 10 |     | 1   |        |    |    |    |  |
| 40-AV                      | D                 | 3                      |              | 3   |   |    |    |     |     |        |    |    |    |  |
| 44-52                      | A                 | 104                    |              |     |   |    |    |     | 104 |        |    |    |    |  |
| 44-53                      | A                 | 36                     |              |     |   |    |    |     | 18  |        |    | 18 |    |  |
| 48-51                      | A                 | 56                     |              |     |   |    | 10 |     | 42  | 4      |    |    |    |  |
| 48-52                      | A                 | 61                     |              |     |   |    |    |     | 56  | 5      |    |    |    |  |
| 48-53                      | D                 | 37                     |              |     |   |    |    | 37  |     |        |    |    |    |  |
| 48-54                      | A                 | 56                     |              |     |   |    | 10 |     | 42  | 4      |    |    |    |  |
| 48-55                      | A                 | 78                     |              |     |   | 6  | 2  | 2   | 68  |        |    |    |    |  |
| 48-57                      | A                 | 56                     |              |     | 4 |    | 10 |     | 42  |        |    |    |    |  |

# MS/Standard insert alternate positioning

To avoid cross-plugging problems in applications requiring the use of more than one connector of the same size and arrangement, alternate rotations are available as indicated in the accompanying charts.

As shown in the diagram below, the front face of the pin insert is rotated within the shell in a clockwise direction from the normal shell key. The socket insert would be rotated counter-clockwise the same number of degrees in respect to the normal shell key.



The following insert arrangements have the same alternate insert rotations for W, X, Y and Z, which are:

| Degrees |     |     |     |
|---------|-----|-----|-----|
| W       | X   | Y   | Z   |
| 80      | 110 | 250 | 280 |

|       |       |       |       |       |       |
|-------|-------|-------|-------|-------|-------|
| 16-7  | 20-22 | 22-29 | 24-17 | 28-16 | 32-13 |
| 18-5  | 22-6  | 22-33 | 24-20 | 28-17 | 32-22 |
| 18-9  | 22-12 | 22-34 | 24-21 | 28-19 | 32-AF |
| 18-13 | 22-14 | 24-1  | 24-28 | 28-20 | 36-1  |
| 18-14 | 22-15 | 24-3  | 28-1  | 28-21 | 36-7  |
| 20-7  | 22-16 | 24-4  | 28-4  | 32-1  | 36-8  |
| 20-8  | 22-17 | 24-5  | 28-8  | 32-3  | 36-13 |
| 20-9  | 22-18 | 24-6  | 28-9  | 32-4  | 40-AR |
| 20-12 | 22-19 | 24-7  | 28-10 | 32-6  | 40-AS |
| 20-14 | 22-21 | 24-12 | 28-11 | 32-9  | 40-AT |
| 20-16 | 22-24 | 24-14 | 28-14 | 32-10 | 40-AU |
| 20-20 | 22-25 | 24-16 | 28-15 | 32-12 |       |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 10SL-4             | 63      | —   | —   | —   |
| 12S-3              | 70      | 145 | 215 | 290 |
| 14S-2              | —       | 120 | 240 | —   |
| 14S-5              | —       | 110 | —   | —   |
| 14S-7              | 90      | 180 | 270 | —   |
| 14S-9              | 70      | 145 | 215 | 290 |
| 16-9               | 35      | 110 | 250 | 325 |
| 16-10              | 90      | 180 | 270 | —   |
| 16-11              | 35      | 110 | 250 | 325 |
| 16-13              | 35      | 110 | 250 | 325 |
| 16S-1              | 80      | —   | —   | 280 |
| 16S-4              | 35      | 110 | 250 | 325 |
| 16S-5              | 70      | 145 | 215 | 290 |
| 16S-6              | 90      | 180 | 270 | —   |
| 16S-8              | —       | 170 | 265 | —   |
| 18-1               | 70      | 145 | 215 | 290 |
| 18-3               | 35      | 110 | 250 | 325 |
| 18-4               | 35      | 110 | 250 | 325 |
| 18-8               | 70      | —   | —   | 290 |
| 18-10              | —       | 120 | 240 | —   |
| 18-11              | —       | 170 | 265 | —   |
| 18-12              | 80      | —   | —   | 280 |
| 18-15              | —       | 120 | 240 | —   |
| 18-20              | 90      | 180 | 270 | —   |
| 18-22              | 70      | 145 | 215 | 290 |
| 18-29              | 90      | 180 | 270 | —   |
| 20-3               | 70      | 145 | 215 | 290 |
| 20-4               | 45      | 110 | 250 | —   |
| 20-5               | 35      | 110 | 250 | 325 |
| 20-6               | 70      | 145 | 215 | 290 |
| 20-15              | 80      | —   | —   | 280 |
| 20-17              | 90      | 180 | 270 | —   |
| 20-18              | 35      | 110 | 250 | 325 |
| 20-19              | 90      | 180 | 270 | —   |
| 20-21              | 35      | 110 | 250 | 325 |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 20-23              | 35      | 110 | 250 | 325 |
| 20-24              | 35      | 110 | 250 | 325 |
| 20-27              | 35      | 110 | 250 | 325 |
| 20-29              | 80      | —   | —   | 280 |
| 22-1               | 35      | 110 | 250 | 325 |
| 22-2               | 70      | 145 | 215 | 290 |
| 22-4               | 35      | 110 | 250 | 325 |
| 22-5               | 35      | 110 | 250 | 325 |
| 22-8               | 35      | 110 | 250 | 325 |
| 22-9               | 70      | 145 | 215 | 290 |
| 22-10              | 35      | 110 | 250 | 325 |
| 22-11              | 35      | 110 | 250 | 325 |
| 22-13              | 35      | 110 | 250 | 325 |
| 22-20              | 35      | 110 | 250 | 325 |
| 22-22              | —       | 110 | 250 | —   |
| 22-23              | 35      | —   | 250 | —   |
| 22-27              | 80      | —   | 250 | 280 |
| 22-28              | 80      | —   | —   | 280 |
| 22-63              | 20      | —   | —   | —   |
| 24-2               | 80      | —   | —   | 280 |
| 24-9               | 35      | 110 | 250 | 325 |
| 24-10              | 80      | —   | —   | 280 |
| 24-11              | 35      | 110 | 250 | 325 |
| 24-22              | 45      | 110 | 250 | —   |
| 24-27              | 80      | —   | —   | 280 |
| 28-2               | 35      | 110 | 250 | 325 |
| 28-3               | 70      | 145 | 215 | 290 |
| 28-5               | 35      | 110 | 250 | 325 |
| 28-6               | 70      | 145 | 215 | 290 |
| 28-7               | 35      | 110 | 250 | 325 |
| 28-12              | 90      | 180 | 270 | —   |
| 28-18              | 70      | 145 | 215 | 290 |
| 28-22              | 70      | 145 | 215 | 290 |
| 28-AY              | 45      | 110 | 250 | —   |
| 32-2               | 70      | 145 | 215 | 290 |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 32-5               | 35      | 110 | 250 | 325 |
| 32-7               | 80      | 125 | 235 | 280 |
| 32-8               | 80      | 125 | 235 | 280 |
| 32-14              | 65      | 130 | 230 | 295 |
| 32-15              | 35      | 110 | 250 | 280 |
| 32-17              | 45      | 110 | 250 | —   |
| 32-25              | 60      | 120 | —   | —   |
| 32-48              | 80      | —   | —   | —   |
| 32-64              | 80      | 100 | 110 | 250 |
| 32-68              | 30      | —   | —   | —   |
| 32-82              | 30      | —   | —   | —   |
| 36-3               | 70      | 145 | 215 | 290 |
| 36-4               | 70      | 145 | 215 | 290 |
| 36-5               | —       | 120 | 240 | —   |
| 36-6               | 35      | 110 | 250 | 325 |
| 36-9               | 80      | 125 | 235 | 280 |
| 36-10              | 80      | 125 | 235 | 280 |
| 36-14              | 90      | 180 | 270 | —   |
| 36-15              | 60      | 125 | 245 | 305 |
| 36-AF              | 65      | —   | —   | —   |
| 40-1               | 65      | 130 | 235 | 300 |
| 40-5               | 33      | —   | —   | 270 |
| 40-9               | 65      | 125 | 225 | 310 |
| 40-10              | 65      | 125 | 225 | 310 |
| 40-35              | 70      | 130 | 230 | 290 |
| 40-AD              | 45      | —   | —   | —   |
| 40-AG              | 37      | 74  | 285 | 322 |
| 40-AP              | 35      | 110 | 250 | 325 |
| 40-AV              | 90      | 180 | 270 | —   |

# MS/Standard

## contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |      |       |                           |                           |       |       |      |
|--------------------|------|-------|---------------------------|---------------------------|-------|-------|------|
|                    |      |       |                           |                           |       |       |      |
|                    |      |       | Front of<br>Socket Insert | Front of<br>Socket Insert |       |       |      |
| Insert Arrangement | 8S-1 | 10S-2 | 10SL-3                    | 10SL-4                    | 12S-3 | 12S-4 | 12-5 |
| Service Rating     | A    | A     | A                         | A                         | A     | D     | D    |
| Number of Contacts | 1    | 1     | 3                         | 2                         | 2     | 1     | 1    |
| Contact Size       | 16   | 16    | 16                        | 16                        | 16    | 16    | 12   |

|                    |       |       |       |       |       |       |       |
|--------------------|-------|-------|-------|-------|-------|-------|-------|
|                    |       |       |       |       |       |       |       |
| Insert Arrangement | 14S-1 | 14S-2 | 14S-4 | 14S-5 | 14S-6 | 14S-7 | 14S-9 |
| Service Rating     | A     | Inst. | D     | Inst. | Inst. | A     | A     |
| Number of Contacts | 3     | 4     | 1     | 5     | 6     | 3     | 2     |
| Contact Size       | 16    | 16    | 16    | 16    | 16    | 16    | 16    |

|                    |                           |                           |      |       |       |       |
|--------------------|---------------------------|---------------------------|------|-------|-------|-------|
|                    |                           |                           |      |       |       |       |
|                    | 100° Rotation<br>of 14S-2 | 100° Rotation<br>of 14S-7 |      |       |       |       |
| Insert Arrangement | 14S-10                    | 14S-12                    | 14-3 | 16S-1 | 16S-3 | 16S-4 |
| Service Rating     | Inst.                     | A                         | A    | A     | B     | D     |
| Number of Contacts | 4                         | 3                         | 1    | 7     | 1     | 2     |
| Contact Size       | 16                        | 16                        | 8    | 16    | 16    | 16    |

|                    |       |       |       |      |      |       |
|--------------------|-------|-------|-------|------|------|-------|
|                    |       |       |       |      |      |       |
| Insert Arrangement | 16S-5 | 16S-6 | 16S-8 | 16-2 | 16-7 | 16-9  |
| Service Rating     | A     | A     | A     | E    | A    | A     |
| Number of Contacts | 3     | 3     | 5     | 1    | 1 2  | 2 2   |
| Contact Size       | 16    | 16    | 16    | 12   | 8 16 | 12 16 |

CONTACT LEGEND

⊕

⊖

⦿

○

⊗

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |       |       |       |       |                              |      |
|--------------------|-------|-------|-------|-------|------------------------------|------|
|                    |       |       |       |       |                              |      |
| Insert Arrangement | 16-10 | 16-11 | 16-12 | 16-13 | 18-1                         | 18-3 |
| Service Rating     | A     | A     | A     | A     | B, C, F, G = A; Bal. = Inst. | D    |
| Number of Contacts | 3     | 2     | 1     | 2*    | 10                           | 2    |
| Contact Size       | 12    | 12    | 4     | 12    | 16                           | 12   |

|                    |      |       |      |      |       |       |
|--------------------|------|-------|------|------|-------|-------|
|                    |      |       |      |      |       |       |
| Insert Arrangement | 18-4 | 18-5  | 18-6 | 18-7 | 18-8  | 18-9  |
| Service Rating     | D    | D     | D    | B    | A     | Inst. |
| Number of Contacts | 4    | 2 1   | 1    | 1    | 1 7   | 2 5   |
| Contact Size       | 16   | 12 16 | 4    | 8    | 12 16 | 12 16 |

|                    |       |       |       |       |       |       |
|--------------------|-------|-------|-------|-------|-------|-------|
|                    |       |       |       |       |       |       |
| Insert Arrangement | 18-10 | 18-11 | 18-12 | 18-13 | 18-14 | 18-15 |
| Service Rating     | A     | A     | A     | A     | A     | A     |
| Number of Contacts | 4     | 5     | 6     | 1 3   | 1 1   | 4**   |
| Contact Size       | 12    | 12    | 16    | 8 12  | 4 16  | 12    |

|                    |       |       |       |       |       |                              |
|--------------------|-------|-------|-------|-------|-------|------------------------------|
|                    |       |       |       |       |       |                              |
| Insert Arrangement | 18-16 | 18-17 | 18-19 | 18-20 | 18-22 | 18-24                        |
| Service Rating     | C     | Inst. | A     | A     | D     | B, C, F, G = A; Bal. = Inst. |
| Number of Contacts | 1     | 2 5   | 10    | 5     | 3     | 10                           |
| Contact Size       | 12    | 12 16 | 16    | 16    | 16    | 16                           |






  






CONTACT LEGEND
16
12
8
4
0







\* A = Iron; B = Constantan  
 \*\* A, C = Iron; B, D = Constantan

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
|                    |                                                                                   | 110° Rotation<br>of 18-20                                                         | 260° Rotation<br>of 18-20                                                         |                                                                                    |                                                                                     |                                                                                     |
| Insert Arrangement | 18-29                                                                             | 18-30                                                                             | 18-31                                                                             | 20-2                                                                               | 20-3                                                                                | 20-4                                                                                |
| Service Rating     | A                                                                                 | A                                                                                 | A                                                                                 | D                                                                                  | D                                                                                   | D                                                                                   |
| Number of Contacts | 5                                                                                 | 5                                                                                 | 5                                                                                 | 1                                                                                  | 3                                                                                   | 4                                                                                   |
| Contact Size       | 16                                                                                | 16                                                                                | 16                                                                                | 0                                                                                  | 12                                                                                  | 12                                                                                  |

|                    |                                                                                    |                                                                                    |                                                                                    |                                                                                     |                                                                                      |                                                                                      |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-6                                                                               | 20-7                                                                               | 20-8                                                                               | 20-9                                                                                | 20-11                                                                                | 20-12                                                                                |
| Service Rating     | D                                                                                  | A, B, H, G = D; C, D, E, F = A                                                     | Inst.                                                                              | H = D; Bal. = A                                                                     | Inst.                                                                                | A                                                                                    |
| Number of Contacts | 3                                                                                  | 8                                                                                  | 2 4                                                                                | 1 7                                                                                 | 13                                                                                   | 1 1                                                                                  |
| Contact Size       | 16                                                                                 | 16                                                                                 | 8 16                                                                               | 12 16                                                                               | 16                                                                                   | 4 16                                                                                 |

|                    |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-14                                                                               | 20-15                                                                               | 20-16                                                                               | 20-17                                                                                | 20-18                                                                                 | 20-19                                                                                 |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                   | A                                                                                    | A                                                                                     | A                                                                                     |
| Number of Contacts | 2 3                                                                                 | 7                                                                                   | 2 7                                                                                 | 5 1                                                                                  | 3 6                                                                                   | 3                                                                                     |
| Contact Size       | 8 12                                                                                | 12                                                                                  | 12 16                                                                               | 12 16                                                                                | 12 16                                                                                 | 8                                                                                     |























CONTACT LEGEND
16
12
8
4
0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-20                                                                             | 20-21                                                                             | 20-22                                                                             | 20-23                                                                              | 20-24                                                                               | 20-25                                                                               |
| Service Rating     | A                                                                                 | A                                                                                 | A                                                                                 | A                                                                                  | A                                                                                   | Inst.                                                                               |
| Number of Contacts | 1 3                                                                               | 1 8                                                                               | 3 3                                                                               | 2                                                                                  | 2 2                                                                                 | 13                                                                                  |
| Contact Size       | 4 12                                                                              | 12 16                                                                             | 8 16                                                                              | 8                                                                                  | 8 16                                                                                | 16                                                                                  |

|                    |                                                                                   |                                                                                   |                                                                                    |                                                                                    |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-27                                                                             | 20-29                                                                             | 20-30                                                                              | 20-33                                                                              | 22-1                                                                                | 22-2                                                                                |
| Service Rating     | A                                                                                 | A                                                                                 | Inst.                                                                              | A                                                                                  | D                                                                                   | D                                                                                   |
| Number of Contacts | 14                                                                                | 17                                                                                | 13                                                                                 | 11                                                                                 | 2                                                                                   | 3                                                                                   |
| Contact Size       | 16                                                                                | 16                                                                                | 16                                                                                 | 16                                                                                 | 8                                                                                   | 8                                                                                   |

|                    |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |
| Insert Arrangement | 22-4                                                                                | 22-5                                                                                | 22-6                                                                                 | 22-7                                                                                  | 22-8                                                                                  |
| Service Rating     | A                                                                                   | D                                                                                   | D                                                                                    | E                                                                                     | E                                                                                     |
| Number of Contacts | 2 2                                                                                 | 2 4                                                                                 | 2 1                                                                                  | 1                                                                                     | 2                                                                                     |
| Contact Size       | 8 12                                                                                | 12 16                                                                               | 8 16                                                                                 | 0                                                                                     | 12                                                                                    |

⊕

⊖

⦿

○

⊗

CONTACT LEGEND

16

12

8

4

0

# MS/Standard

## contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |      |       |       |       |                       |
|--------------------|------|-------|-------|-------|-----------------------|
|                    |      |       |       |       |                       |
| Insert Arrangement | 22-9 | 22-10 | 22-11 | 22-12 | 22-13                 |
| Service Rating     | E    | E     | B     | D     | E = D; A, B, C, D = A |
| Number of Contacts | 3    | 4     | 2     | 2 3   | 4 1                   |
| Contact Size       | 12   | 16    | 16    | 8 16  | 12 16                 |

|                    |       |                          |       |                 |                                |
|--------------------|-------|--------------------------|-------|-----------------|--------------------------------|
|                    |       |                          |       |                 |                                |
| Insert Arrangement | 22-14 | 22-15                    | 22-16 | 22-17           | 22-18                          |
| Service Rating     | A     | D = E; A, B, C, E, F = A | A     | A = D; Bal. = A | A, B, F, G, H = D; C, D, E = A |
| Number of Contacts | 19    | 5 1                      | 3 6   | 1 8             | 8                              |
| Contact Size       | 16    | 12 16                    | 12 16 | 12 16           | 16                             |

|                    |       |       |       |       |                 |
|--------------------|-------|-------|-------|-------|-----------------|
|                    |       |       |       |       |                 |
| Insert Arrangement | 22-19 | 22-20 | 22-21 | 22-22 | 22-23           |
| Service Rating     | A     | A     | A     | A     | H = D; Bal. = A |
| Number of Contacts | 14    | 9     | 1 2   | 4     | 8               |
| Contact Size       | 16    | 16    | 0 16  | 8     | 12              |

⊕

⊖

⦿

○

⊗

CONTACT LEGEND

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                          |                 |       |                             |                       |
|--------------------|--------------------------|-----------------|-------|-----------------------------|-----------------------|
|                    |                          |                 |       |                             |                       |
| Insert Arrangement | 22-24                    | 22-27           | 22-28 | 22-33                       | 22-36                 |
| Service Rating     | C, D, E = D; A, B, F = A | J = D; Bal. = A | A     | A, B, C, D = D; E, F, G = A | H = D; Bal. = A*      |
| Number of Contacts | 2 4                      | 1 8             | 7     | 7                           | 8                     |
| Contact Size       | 12 16                    | 8 16            | 12    | 16                          | 12                    |
|                    |                          |                 |       |                             |                       |
| Insert Arrangement | 22-34                    | 24-2            | 24-3  | 24-5                        | 24-6                  |
| Service Rating     | D                        | D               | D     | A                           | A, G, H = D; Bal. = A |
| Number of Contacts | 3 2                      | 7               | 2 5   | 16                          | 8                     |
| Contact Size       | 12 16                    | 12              | 12 16 | 16                          | 12                    |
|                    |                          |                 |       |                             |                       |
| Insert Arrangement | 24-7                     | 24-9            | 24-10 | 24-11                       | 24-12                 |
| Service Rating     | A                        | A               | A     | A                           | A                     |
| Number of Contacts | 2 14                     | 2               | 7     | 3 6                         | 2 3                   |
| Contact Size       | 12 16                    | 4               | 8     | 8 12                        | 4 12                  |

\* A, C, E, G = Iron  
B, D, F, H = Constantan

CONTACT LEGEND

⊕

⬤

⬤

○

⊗

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                              |       |       |       |       |
|--------------------|------------------------------|-------|-------|-------|-------|
|                    |                              |       |       |       |       |
| Insert Arrangement | 24-16                        | 24-17 | 24-20 | 24-21 | 24-22 |
| Service Rating     | A, B, F, G = D; C, D, E, = A | D     | D     | D     | D     |
| Number of Contacts | 1 3 3                        | 2 3   | 2 9   | 1 9   | 4     |
| Contact Size       | 8 12 16                      | 12 16 | 12 16 | 8 16  | 8     |

|                    |       |       |                       |       |      |
|--------------------|-------|-------|-----------------------|-------|------|
|                    |       |       |                       |       |      |
| Insert Arrangement | 24-27 | 24-28 | 28-1                  | 28-2  | 28-3 |
| Service Rating     | E     | Inst. | A, J, E = D; Bal. = A | D     | E    |
| Number of Contacts | 7     | 24    | 3 6                   | 2 12  | 3    |
| Contact Size       | 16    | 16    | 8 12                  | 12 16 | 8    |

|                    |                       |         |      |      |
|--------------------|-----------------------|---------|------|------|
|                    |                       |         |      |      |
| Insert Arrangement | 28-4                  | 28-5    | 28-6 | 28-7 |
| Service Rating     | G, P, S = E; Bal. = D | D       | D    | D    |
| Number of Contacts | 2 7                   | 2 1 2   | 3    | 2    |
| Contact Size       | 12 16                 | 4 12 16 | 4    | 4    |

⊕

⊖

⦿

○

⊗

CONTACT LEGEND

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                |                                                  |                              |       |
|--------------------|--------------------------------|--------------------------------------------------|------------------------------|-------|
|                    |                                |                                                  |                              |       |
| Insert Arrangement | 28-8                           | 28-9                                             | 28-10                        | 28-11 |
| Service Rating     | L, M = E; B = D; Bal. = A      | D                                                | G = D; Bal. = A              | A     |
| Number of Contacts | 2 10                           | 6 6                                              | 2 2 3                        | 4 18  |
| Contact Size       | 12 16                          | 12 16                                            | 4 8 12                       | 12 16 |
|                    |                                |                                                  |                              |       |
| Insert Arrangement | 28-12                          | 28-13                                            | 28-15                        | 28-16 |
| Service Rating     | A                              | A                                                | A                            | A     |
| Number of Contacts | 26                             | 26                                               | 35                           | 20    |
| Contact Size       | 16                             | 16                                               | 16                           | 16    |
|                    |                                |                                                  |                              |       |
| Insert Arrangement | 28-17                          | 28-18                                            | 28-19                        |       |
| Service Rating     | R = B; M, N, P = D; A to L = A | M = C; G, H, J, K, L = D; A, B = A; Bal. = Inst. | H, M = B; A, B = D; Bal. = A |       |
| Number of Contacts | 15                             | 12                                               | 4 6                          |       |
| Contact Size       | 16                             | 16                                               | 12 16                        |       |

⊕

●

⦿

○

⊗

CONTACT LEGEND

16

12

8





4





0





# MS/Standard

## contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |
| Insert Arrangement | 28-20                                                                             | 28-21                                                                             | 28-22                                                                               | 32-1                                                                                |
| Service Rating     | A                                                                                 | A                                                                                 | D                                                                                   | A = E; B, C, D, E = D                                                               |
| Number of Contacts | 10 4                                                                              | 37                                                                                | 3 3                                                                                 | 2 3                                                                                 |
| Contact Size       | 12 16                                                                             | 16                                                                                | 4 16                                                                                | 0 12                                                                                |

|                    |                                                                                    |                                                                                    |                                                                                     |                                                                                      |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |  |  |  |  |
| Insert Arrangement | 32-2                                                                               | 32-3                                                                               | 32-4                                                                                | 32-5                                                                                 |
| Service Rating     | E                                                                                  | D                                                                                  | F, J, K, N = A; Bal. = D                                                            | D                                                                                    |
| Number of Contacts | 3 2                                                                                | 1 2 2 4                                                                            | 2 12                                                                                | 2                                                                                    |
| Contact Size       | 4 16                                                                               | 0 4 12 16                                                                          | 12 16                                                                               | 0                                                                                    |

|                    |                                                                                     |                                                                                     |                                                                                      |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |
| Insert Arrangement | 32-6                                                                                | 32-7                                                                                | 32-8                                                                                 | 32-9                                                                                  |
| Service Rating     | A                                                                                   | A, B, h, j = Inst.; Bal. = A                                                        | A                                                                                    | D                                                                                     |
| Number of Contacts | 2 3 2 16                                                                            | 7 28                                                                                | 6 24                                                                                 | 2 12                                                                                  |
| Contact Size       | 4 8 12 16                                                                           | 12 16                                                                               | 12 16                                                                                | 4 16                                                                                  |

CONTACT LEGEND

⊕

⊖

⦿

○

⊗

16

12

8

4

0

# MS/Standard contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                                     |                             |       |       |
|--------------------|-------------------------------------|-----------------------------|-------|-------|
|                    |                                     |                             |       |       |
| Insert Arrangement | 32-10                               | 32-12                       | 32-13 | 32-15 |
| Service Rating     | A, F = E; G = B; B, E = D; C, D = A | C, D, E, F, G = A; Bal. = D | D     | D     |
| Number of Contacts | 2 2 3                               | 5 10                        | 5 18  | 2 6   |
| Contact Size       | 4 8 16                              | 12 16                       | 12 16 | 0 12  |

|                    |           |       |       |       |
|--------------------|-----------|-------|-------|-------|
|                    |           |       |       |       |
| Insert Arrangement | 32-16     | 32-17 | 32-22 | 36-1  |
| Service Rating     | A         | D     | A     | D     |
| Number of Contacts | 2 3 2 16  | 4     | 54    | 4 18  |
| Contact Size       | 4 8 12 16 | 4     | 16    | 12 16 |

|                    |      |                 |      |      |
|--------------------|------|-----------------|------|------|
|                    |      |                 |      |      |
| Insert Arrangement | 36-3 | 36-4            | 36-5 | 36-6 |
| Service Rating     | D    | A = D; B, C = A | A    | A    |
| Number of Contacts | 3 3  | 3               | 4    | 2 4  |
| Contact Size       | 0 12 | 0               | 0    | 0 4  |

CONTACT LEGEND

⊕

◐

◑

○


⊗

1612840


# MS/Standard

## contact arrangements


front face of pin insert or rear face of socket insert illustrated




|                    |       |
|--------------------|-------|
| Insert Arrangement | 36-7  |
| Service Rating     | A     |
| Number of Contacts | 7 40  |
| Contact Size       | 12 16 |




|       |
|-------|
| 36-8  |
| A     |
| 1 46  |
| 12 16 |




|           |
|-----------|
| 36-9      |
| A         |
| 1 2 14 14 |
| 4 8 12 16 |




|                    |       |
|--------------------|-------|
| Insert Arrangement | 36-10 |
| Service Rating     | A     |
| Number of Contacts | 48    |
| Contact Size       | 16    |




|                           |
|---------------------------|
| 100° Rotation<br>of 36-10 |
| 36-11                     |
| A                         |
| 48                        |
| 16                        |




|                           |
|---------------------------|
| 110° Rotation<br>of 36-10 |
| 36-12                     |
| A                         |
| 48                        |
| 16                        |




|                    |                       |
|--------------------|-----------------------|
| Insert Arrangement | 36-13                 |
| Service Rating     | N, P, Q = E; Bal. = A |
| Number of Contacts | 2 15                  |
| Contact Size       | 12 16                 |



|         |
|---------|
| 36-14   |
| D       |
| 5 5 6   |
| 8 12 16 |




|                 |
|-----------------|
| 36-15           |
| M = D; Bal. = A |
| 35              |
| 16              |



CONTACT LEGEND

# MS/Standard contact arrangements


front face of pin insert or rear face of socket insert illustrated



100° Rotation  
of 36-7  
**36-16**


Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size

**A**  
**7 40**  
**12 16**




110° Rotation  
of 36-7  
**36-17**

**A**  
**7 40**  
**12 16**



100° Rotation  
of 36-9  
**36-18**


**1 2 14 14**  
**4 8 12 16**



**36-20**


Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size

**A**  
**2 2 30**  
**8 12 16**




**36-52**

**A**  
**52**  
**16**



**40-1**


**D**  
**6 24**  
**12 16**



**40-9**


Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size

**A**  
**1 22 24**  
**8 12 16**



**40-56**

**A**  
**85**  
**16**



**48-62**

**D**  
**85**  
**16**



CONTACT LEGEND



**16 12 8 4 0**






# Special contact arrangements




Requirements for more complex circuits prompted Amphenol to provide inserts not covered by the MS drawings. Illustrated here and on the following pages are insert layouts which have from one contact (high tension) to the 104 contact insert in shell size 44.

Many of these special inserts are also available in alternate keyway arrangements. Please contact Amphenol, Sidney, NY for additional information on special circuit application requirements.

front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 14S-A7                                                                            | 16-59                                                                             | 20-26                                                                             | 20-51                                                                              | 20-57                                                                               | 20-58                                                                               |
| Service Rating     | A                                                                                 | A                                                                                 | A                                                                                 | A                                                                                  | A                                                                                   | A                                                                                   |
| Number of Contacts | 7                                                                                 | 4                                                                                 | 19                                                                                | 3*                                                                                 | 7*                                                                                  | 5 5                                                                                 |
| Contact Size       | 16                                                                                | 12                                                                                | 16                                                                                | 8                                                                                  | 12 for #14 or 16 wire                                                               | 12 16                                                                               |

|                    |                                                                                    |                                                                                    |                                                                                    |                                                                                     |                                                                                      |                                                                                      |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 20-59                                                                              | 20-66                                                                              | 20-79                                                                              | 22-63                                                                               | 22-65                                                                                | 22-70                                                                                |
| Service Rating     | A                                                                                  | A                                                                                  | H = D; Bal. = A                                                                    | A                                                                                   | H = D; Bal. = A                                                                      | A                                                                                    |
| Number of Contacts | 3*                                                                                 | 1 5                                                                                | 7* 1*                                                                              | 4 8                                                                                 | 8*                                                                                   | 8 5                                                                                  |
| Contact Size       | 8 for #10 or 12 wire                                                               | 16 12 for #10 wire                                                                 | 16 12 for #16 wire                                                                 | 12 16                                                                               | 12 for #14 or 16 wire                                                                | 12 16                                                                                |

|                    |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |  |
| Insert Arrangement | 22-80                                                                               | 24-19                                                                               | 24-51                                                                               | 24-52                                                                                | 24-53                                                                                 | 24-58                                                                                 |
| Service Rating     | A                                                                                   | A                                                                                   | A                                                                                   | Hi-Volt                                                                              | A                                                                                     | A                                                                                     |
| Number of Contacts | 3*                                                                                  | 12                                                                                  | 5*                                                                                  | 1                                                                                    | 5*                                                                                    | 3 3 7                                                                                 |
| Contact Size       | 8 for #10 or 12 wire                                                                | 16                                                                                  | B, E for AN #10 or 12 wire<br>A, C, D for AN #8 wire                                | 12                                                                                   | 8                                                                                     | 8 12 16                                                                               |

\* Solderless

CONTACT LEGEND

⊕

⊖

⦿

○

⊗

16

12






8

4






0

# Special contact arrangements



front face of pin insert or rear face of socket insert illustrated

|                    |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |
| Insert Arrangement | 24-59                                                                             | 24-60                                                                             | 24-65                                                                              | 24-66                                                                               | 24-67                                                                               |
| Service Rating     | A                                                                                 | A                                                                                 | A                                                                                  | D                                                                                   | Inst.                                                                               |
| Number of Contacts | 7 7                                                                               | 7*                                                                                | 11 4                                                                               | 7                                                                                   | 19                                                                                  |
| Contact Size       | 12 16                                                                             | 8 for #10 or 12 wire                                                              | 12 16                                                                              | 12                                                                                  | 12                                                                                  |

|                    |                                                                                    |                                                                                    |                                                                                     |                                                                                      |                                                                                      |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
|                    |  |  |  |  |  |
| Insert Arrangement | 24-71                                                                              | 24-75                                                                              | 24-79                                                                               | 24-80                                                                                | 24-84                                                                                |
| Service Rating     | A                                                                                  | A                                                                                  | A                                                                                   | Inst.                                                                                | A                                                                                    |
| Number of Contacts | 2* 5*                                                                              | 5 2                                                                                | 5                                                                                   | 23                                                                                   | 1 18                                                                                 |
| Contact Size       | 8 8 for #10 or 12 wire                                                             | 8 8 for #16 wire                                                                   | 8                                                                                   | 16                                                                                   | 12 12 (Coax) RG-188/U or RG-174/U                                                    |

|                    |                                                                                     |                                                                                     |                                                                                       |                                                                                       |
|--------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                    |  |  |  |  |
| Insert Arrangement | 24-96                                                                               | 24-AJ                                                                               | 28-51                                                                                 | 28-59                                                                                 |
| Service Rating     | Inst.                                                                               | A                                                                                   | A                                                                                     | A                                                                                     |
| Number of Contacts | 28                                                                                  | 25                                                                                  | 12                                                                                    | 7 10                                                                                  |
| Contact Size       | 16                                                                                  | 16                                                                                  | 12                                                                                    | 12 16                                                                                 |

\* Solderless

CONTACT LEGEND

⊕

●

⦿

○

⊗

16

12

8

4

0

# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |       |                               |                               |                   |       |
|--------------------|-------|-------------------------------|-------------------------------|-------------------|-------|
|                    |       |                               |                               |                   |       |
| Insert Arrangement | 28-66 | 28-72                         | 28-74                         | 28-75             | 28-79 |
| Service Rating     | A     | —                             | A                             | A                 | A     |
| Number of Contacts | 2 14  | 3                             | 9* 4* 3*                      | 9* 7*             | 7 9   |
| Contact Size       | 8 12  | 4 (Coax) RG-59A/U or RG-62A/U | 16 8 8 for #10 wire (S, T, R) | 16 8 for #10 wire | 8 16  |

|                    |       |       |       |       |       |
|--------------------|-------|-------|-------|-------|-------|
|                    |       |       |       |       |       |
| Insert Arrangement | 28-82 | 28-84 | 28-AY | 32-14 | 32-25 |
| Service Rating     | D     | A     | A     | D     | A     |
| Number of Contacts | 2 4   | 9     | 4 5   | 13    | 25    |
| Contact Size       | 8 12  | 8     | 4 16  | 12    | 12    |

|                    |       |       |       |                        |
|--------------------|-------|-------|-------|------------------------|
|                    |       |       |       |                        |
| Insert Arrangement | 32-31 | 32-48 | 32-52 | 32-53                  |
| Service Rating     | A     | Inst. | D     | t, u = E; Bal. = Inst. |
| Number of Contacts | 31    | 48    | 6 2   | 5 37                   |
| Contact Size       | 16    | 16    | 12 0  | 12 16                  |

\* Solderless

CONTACT LEGEND

⊕

⊖

⦿

○

⊗

16

12

8

4

0

# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |                    |                     |                               |                      |
|--------------------|--------------------|---------------------|-------------------------------|----------------------|
|                    |                    |                     |                               |                      |
| Insert Arrangement | 32-56              | 32-57               | 32-58                         | 32-59                |
| Service Rating     | A                  | **                  | —                             | A                    |
| Number of Contacts | 24 6               | 6 2                 | 4                             | 40 2                 |
| Contact Size       | 16 12 for #10 wire | 12 0 (Coax) RG-71/U | 4 (Coax) RG-161/U or RG-179/U | 16 8 (Coax) RG-161/U |

|                    |                      |                             |       |                      |
|--------------------|----------------------|-----------------------------|-------|----------------------|
|                    |                      |                             |       |                      |
| Insert Arrangement | 32-60                | 32-62                       | 32-64 | 32-68                |
| Service Rating     | A                    | **                          | Inst. | A                    |
| Number of Contacts | 15 8                 | 2 1 2 16 2                  | 54    | 12 4                 |
| Contact Size       | 16 8 (Coax) RG-124/U | 4 8 12 16 8 (Coax) RG-124/U | 16    | 16 4 (Coax) RG-58C/U |

|                    |       |                       |       |       |       |
|--------------------|-------|-----------------------|-------|-------|-------|
|                    |       |                       |       |       |       |
| Insert Arrangement | 32-73 | 32-75                 | 32-76 | 32-79 | 32-82 |
| Service Rating     | A     | 8, 9 = D              | A     | D     | A     |
| Number of Contacts | 46    | 2 7                   | 19    | 4 1   | 4 12  |
| Contact Size       | 16    | 12 8 (Coax) RG-180B/U | 12    | 4 8   | 4 16  |

\*\* Consult Amphenol, Sidney, NY for service rating of power contacts.

CONTACT LEGEND

⊕

⊖

⦿

○

⊗

16

12

8





4





0

# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |       |       |       |       |
|--------------------|-------|-------|-------|-------|
|                    |       |       |       |       |
| Insert Arrangement | 32-AF | 36-22 | 36-51 | 36-54 |
| Service Rating     | A     | D     | D     | A     |
| Number of Contacts | 55    | 22    | 2 2   | 8 31  |
| Contact Size       | 16    | 12    | 0 4   | 8 16  |

|                                                                                    |                                                                                    |                                                                                     |                                                                                      |                                                 |
|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|-------------------------------------------------|
|  |  |  |  |                                                 |
| <b>Insert Arrangement</b>                                                          | <b>36-55</b>                                                                       | <b>36-59</b>                                                                        | <b>36-60</b>                                                                         | <b>36-64</b>                                    |
| <b>Service Rating</b>                                                              | <b>A</b>                                                                           | <b>A</b>                                                                            | <b>**</b>                                                                            | <b>-</b>                                        |
| <b>Number of Contacts</b>                                                          | <b>31 8</b>                                                                        | <b>50 3</b>                                                                         | <b>40 7</b>                                                                          | <b>4</b>                                        |
| <b>Contact Size</b>                                                                | <b>16 8 for #6 wire</b>                                                            | <b>16 12 for #10 wire</b>                                                           | <b>16 12 for #10 wire</b>                                                            | <b>0 (Coax) RG-11/U,<br/>RG-12/U or RG-13/U</b> |

|                                                                                     |                                                                                     |                                                                                      |                                                                                       |                      |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----------------------|
|  |  |  |  |                      |
| <b>Insert Arrangement</b>                                                           | <b>36-65</b>                                                                        | <b>36-71</b>                                                                         | <b>36-73</b>                                                                          | <b>36-74</b>         |
| <b>Service Rating</b>                                                               | —                                                                                   | A                                                                                    | —                                                                                     | A                    |
| <b>Number of Contacts</b>                                                           | 4                                                                                   | 3 50                                                                                 | 7                                                                                     | 43 1                 |
| <b>Contact Size</b>                                                                 | 0 (Coax) RG-59/U, RG-62/U<br>or RG-71/U                                             | 12 16                                                                                | 4 (Coax) RG-62B/U                                                                     | 16 8 (Coax) RG-187/U |

\*\* Consult Amphenol, Sidney, NY for service rating of power contacts.

CONTACT LEGEND

⊕

⬤

⬤

○

⊗

16

12

8

4

0


# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated


|                                                                                  |                 |                 |                  |                 |
|----------------------------------------------------------------------------------|-----------------|-----------------|------------------|-----------------|
|                                                                                  |                 |                 |                  |                 |
| Insert Arrangement                                                               | 36-75           | 36-76           | 36-77            | 36-78           |
| Service Rating                                                                   | A               | A               | D                | A               |
| Number of Contacts                                                               | 48              | 47              | 7                | 2 12            |
| Contact Size                                                                     | 16 for #14 wire | 16              | 4                | 16 8            |
|                                                                                  |                 |                 |                  |                 |
| Insert Arrangement                                                               | 36-79           | 36-80           | 36-83            | 36-85           |
| Service Rating                                                                   | A               | A               | —                | M = D; Bal. = A |
| Number of Contacts                                                               | 20              | 20              | 7                | 35              |
| Contact Size                                                                     | 12              | 12 for #10 wire | 4 (Coax) RG-58/U | 16 for #12 wire |
|                                                                                  |                 |                 |                  |                 |
| Insert Arrangement                                                               | 36-97           | 36-99           | 36-AF            | 40-5            |
| Service Rating                                                                   | C               | D               | A                | A               |
| Number of Contacts                                                               | 1               | 3 3 3 3         | 48               | 5               |
| Contact Size                                                                     | 4/0             | 4 8 12 16       | 16               | 0               |
| <div> <div> </div> <div>CONTACT LEGEND</div> <div> 16 12 8 4 0 4/0 </div> </div> |                 |                 |                  |                 |

# Special contact arrangements


front face of pin insert or rear face of socket insert illustrated



|                    |        |       |       |       |
|--------------------|--------|-------|-------|-------|
| Insert Arrangement | 40-10  | 40-30 | 40-35 | 40-53 |
| Service Rating     | A      | A     | D     | A     |
| Number of Contacts | 4 9 16 | 29 1  | 35    | 60    |
| Contact Size       | 4 8 16 | 12 4  | 12    | 16    |



|                    |       |         |       |
|--------------------|-------|---------|-------|
| Insert Arrangement | 40-57 | 40-61   | 40-62 |
| Service Rating     | E     | A       | A     |
| Number of Contacts | 4     | 1 3 55  | 60    |
| Contact Size       | 0     | 8 12 16 | 16    |



|                    |                 |                         |                   |
|--------------------|-----------------|-------------------------|-------------------|
| Insert Arrangement | 40-63           | 40-64                   | 40-66             |
| Service Rating     | A               | -                       | -                 |
| Number of Contacts | 61              | 3 20 13                 | 4                 |
| Contact Size       | 16 for #14 wire | 12 16 8 (Coax) RG-124/U | 0 (Coax) RG-63B/U |

⊕

⬤

⬤

○

⊗

CONTACT LEGEND

16

12

8


4

0


# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated


|                    |                     |
|--------------------|---------------------|
| Insert Arrangement | 40-67               |
| Service Rating     | A                   |
| Number of Contacts | 1 10                |
| Contact Size       | 16 4 (Coax) RG-59/U |




|                    |       |
|--------------------|-------|
| Insert Arrangement | 40-68 |
| Service Rating     | A     |
| Number of Contacts | 21    |
| Contact Size       | 8     |




|                    |       |
|--------------------|-------|
| Insert Arrangement | 40-70 |
| Service Rating     | A     |
| Number of Contacts | 61    |
| Contact Size       | 16    |




|                    |                     |
|--------------------|---------------------|
| Insert Arrangement | 40-72               |
| Service Rating     | A                   |
| Number of Contacts | 1 10                |
| Contact Size       | 16 4 (Coax) RG-9B/U |




|                    |       |
|--------------------|-------|
| Insert Arrangement | 40-73 |
| Service Rating     | A     |
| Number of Contacts | 61    |
| Contact Size       | 16    |




|                    |                                                  |
|--------------------|--------------------------------------------------|
| Insert Arrangement | 40-74                                            |
| Service Rating     | A                                                |
| Number of Contacts | 1 1 4                                            |
| Contact Size       | 12 4 (Coax) RG-62/U 0 (Coax) RG-9B/U or RG-214/U |




|                    |       |
|--------------------|-------|
| Insert Arrangement | 40-75 |
| Service Rating     | E     |
| Number of Contacts | 1 4   |
| Contact Size       | 12 0  |



|                    |       |
|--------------------|-------|
| Insert Arrangement | 40-80 |
| Service Rating     | A     |
| Number of Contacts | 1 10  |
| Contact Size       | 16 4  |



|                    |                 |
|--------------------|-----------------|
| Insert Arrangement | 40-81           |
| Service Rating     | A               |
| Number of Contacts | 62              |
| Contact Size       | 16 for #14 wire |



CONTACT LEGEND

⊕

●

⦿

○

⊗

16
12
8
4
0

# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated

|                    |       |                 |                    |       |
|--------------------|-------|-----------------|--------------------|-------|
|                    |       |                 |                    |       |
| Insert Arrangement | 40-82 | 40-85           | 40-86              | 40-87 |
| Service Rating     | A     | A               | —                  | D     |
| Number of Contacts | 62    | 60              | 4                  | 7     |
| Contact Size       | 16    | 16 for #14 wire | 0 (Coax) RG-115A/U | 4     |


|                    |       |       |       |        |
|--------------------|-------|-------|-------|--------|
|                    |       |       |       |        |
| Insert Arrangement | 40-AD | 40-AG | 40-AP | 40-AR  |
| Service Rating     | A     | A     | E     | Inst.  |
| Number of Contacts | 4 4   | 38    | 2     | 7 3 3  |
| Contact Size       | 8 0   | 12    | 4/0   | 12 4 0 |

|                    |       |         |        |       |
|--------------------|-------|---------|--------|-------|
|                    |       |         |        |       |
| Insert Arrangement | 40-AS | 40-AT   | 40-AU  | 40-AV |
| Service Rating     | A     | A       | A      | D     |
| Number of Contacts | 15 25 | 24 18 1 | 3 10 1 | 3     |
| Contact Size       | 16 12 | 12 16 8 | 4 8 16 | 2/0   |


|                |    |    |   |   |   |         |
|----------------|----|----|---|---|---|---------|
|                |    |    |   |   |   |         |
| CONTACT LEGEND | 16 | 12 | 8 | 4 | 0 | 2/0 4/0 |

# Special contact arrangements


front face of pin insert or rear face of socket insert illustrated




|                    |       |
|--------------------|-------|
| Insert Arrangement | 44-52 |
| Service Rating     | A     |
| Number of Contacts | 104   |
| Contact Size       | 16    |




|                    |                      |
|--------------------|----------------------|
| Insert Arrangement | 44-53                |
| Service Rating     | A                    |
| Number of Contacts | 18 18                |
| Contact Size       | 16 8 (Coax) RG-124/U |



|                    |                       |
|--------------------|-----------------------|
| Insert Arrangement | 48-51                 |
| Service Rating     | A                     |
| Number of Contacts | 42 10 4               |
| Contact Size       | 16 8 0 (Coax) RG-41/U |



|                    |                     |
|--------------------|---------------------|
| Insert Arrangement | 48-52               |
| Service Rating     | A                   |
| Number of Contacts | 56 5                |
| Contact Size       | 16 0 (Coax) RG-41/U |



|                    |       |
|--------------------|-------|
| Insert Arrangement | 48-53 |
| Service Rating     | D     |
| Number of Contacts | 37    |
| Contact Size       | 12    |

CONTACT LEGEND

⊕

●

⦿

○


⊗

16
12
8
4
0


# Special contact arrangements

front face of pin insert or rear face of socket insert illustrated


Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size



**48-54**  
**A**  
**42 10 4**  
**16 8 0 (Coax) RG-59/U**




**48-55**  
**A**  
**68 2 2 6**  
**16 12 8 4**



Insert Arrangement  
Service Rating  
Number of Contacts  
Contact Size

**48-57**  
**A**  
**42 10 4**  
**16 8 0**



**48-60**  
**A**  
**42 10 4**  
**16 8 0 (Coax) RG-214/U**

⊕

◐

◑

○

⊗

CONTACT LEGEND

16

12

8

4

0

# Thermocouple

## contact availability

A complete line of cylindrical connectors containing thermocouple insert arrangements is available. The contact layout for a particular arrangement will be found in either the MS/Standard contact arrangement section, pages 26-37, or the Special contact arrangement section, pages 38-48. All thermocouple contact layouts may contain either iron, alumel, chromel, constantan, standard (copper) or brass (dummy) contacts. See the thermocouple tabulations on the following pages.

The following abbreviations are used in the contact material column in the charts that follow. Also, thermocouple contacts are color coded as shown. (This identification is made by means of small dots of stain on the solder well end of the contact).

| Abbreviation | Material     | Color Code |
|--------------|--------------|------------|
| Ir.          | Iron         | Black      |
| Con.         | Constantan   | Yellow     |
| Cu.          | Copper Alloy | N/A        |
| Ch.          | Chromel      | White      |
| Al.          | Alumel       | Green      |
| Dummy        | Brass        | N/A        |

### WIRE WELL DATA

| Contact Size | Well Inside Dia.<br>+.004<br>-.002 | Well Depth<br>+.031<br>-.000 | Solder Well Barrel<br>Outside Dia. |
|--------------|------------------------------------|------------------------------|------------------------------------|
| 12           | .125                               | .250                         | .166 ±.003                         |
| 16           | .094                               | .188                         | .125 +.002<br>-.004                |

### RECOMMENDED WIRE

|                      |                                        |
|----------------------|----------------------------------------|
| I Chromel - Alumel   | Use wire in accordance with MIL-W-5848 |
| II Iron - Constantan | Use wire in accordance with MIL-W-5845 |

# Thermocouple

## contact arrangements

| Shell Size and Arrg. | Similar to MS Arrg. | Total Contacts | Contact Size |    | Pin Insert Rotation C W | Contact Material                                |
|----------------------|---------------------|----------------|--------------|----|-------------------------|-------------------------------------------------|
|                      |                     |                | 12           | 16 |                         |                                                 |
| 10SL-51              | 10SL-4              | 2              |              | 2  | 45°                     | A = Ir.; B = Con.                               |
| 10SL-52              | 10SL-4              | 2              |              | 2  | 45°                     | A = Cu.; B = Con.                               |
| 10SL-53              | 10SL-4              | 2              |              | 2  | 45°                     | A = Al.; B = Ch.                                |
| 10SL-54              | 10SL-3              | 3              |              | 3  | None                    | A = Ir.; B = Con.; C = Cu.                      |
| 10SL-55              | 10SL-3              | 3              |              | 3  | None                    | A = Al.; B = Ch.; C = Cu.                       |
| 10SL-56              | 10SL-4              | 2              |              | 2  | None                    | A = Al.; B = Ch.                                |
| 10SL-57              | 10SL-4              | 2              |              | 2  | None                    | A = Ch.; B = Con.                               |
| 10SL-58              | 10SL-3              | 3              |              | 3  | None                    | A = Ch.; B = Al.; C = Cu.                       |
| 10SL-59              | 10SL-4              | 2              |              | 2  | None                    | A = Ch.; B = Al.                                |
| 10SL-60              | 10SL-4              | 2              |              | 2  | None                    | A = Ir.; B = Con.                               |
| 10SL-61              | 10SL-4              | 2              |              | 2  | None                    | A = Cu.; B = Con.                               |
| 10SL-62              | 10SL-3              | 3              |              | 3  | None                    | A = Cu.; B = Al.; C = Ir.                       |
| 10SL-63              | 10SL-3              | 3              |              | 3  | None                    | A, C = Con.; B = Ch.                            |
| 10SL-64              | 10SL-3              | 3              |              | 3  | None                    | A, C = Ch.; B = Al.                             |
|                      |                     |                |              |    |                         |                                                 |
| 12S-51               | 12S-3               | 2              |              | 2  | 315°                    | A = Ch.; B = Al.                                |
| 12S-54               | 12S-3               | 2              |              | 2  | 315°                    | A = Ir.; B = Con.                               |
| 12S-55               | 12S-3               | 2              |              | 2  | 45°                     | A = Cu.; B = Con.                               |
| 12S-56               | 12S-3               | 2              |              | 2  | None                    | A = Al.; B = Ch.                                |
| 12S-57               | 12S-3               | 2              |              | 2  | 60°                     | A = Ch.; B = Al.                                |
| 12S-58               | 12S-3               | 2              |              | 2  | 120°                    | A = Ir.; B = Con.                               |
| 12S-59               | 12S-3               | 2              |              | 2  | None                    | A = Ir.; B = Con.                               |
| 12S-60               | 12S-3               | 2              |              | 2  | None                    | A = Cu.; B = Con.                               |
| 12S-61               | 12S-3               | 2              |              | 2  | None                    | A = Ch.; B = Con.                               |
| 12S-62               | 12S-3               | 2              |              | 2  | None                    | A = Ch.; B = Al.                                |
|                      |                     |                |              |    |                         |                                                 |
| 14S-51               | 14S-9               | 2              |              | 2  | 90°                     | A = Al.; B = Ch.                                |
| 14S-52               | 14S-2               | 4              |              | 4  | 45°                     | A, B = Cu.; C = Al.; D = Ch.                    |
| 14S-53               | 14S-9               | 2              |              | 2  | 90°                     | A = Ir.; B = Con.                               |
| 14S-54               | 14S-6               | 6              |              | 6  | 45°                     | A, C, E = Ir.; B, D, F = Con.                   |
| 14S-55               | 14S-2               | 4              |              | 4  | 45°                     | A, C = Ir.; B, D = Con.                         |
| 14S-56               | 14S-2               | 4              |              | 4  | 45°                     | A = Ir.; B = Con.; C, D = Cu.                   |
| 14S-57               | 14S-2               | 4              |              | 4  | 45°                     | A, C = Al.; B, D = Ch.                          |
| 14S-58               | 14S-7               | 3              |              | 3  | 45°                     | A = Al.; B = Ch.; C = Cu.                       |
| 14S-59               | 14S-9               | 2              |              | 2  | 90°                     | A = Cu.; B = Con.                               |
| 14S-60               | 14S-9               | 2              |              | 2  | None                    | A = Al.; B = Ch.                                |
| 14S-61               | 14S-6               | 6              |              | 6  | 45°                     | A = Al.; B = Ch.; C = Ir.; D = Con.; E, F = Cu. |
| 14S-63               | 14S-6               | 6              |              | 6  | None                    | A, C = Al.; B, D = Ch.; E = Ir.; F = Con.       |
| 14S-64               | 14S-2               | 4              |              | 4  | None                    | A, C = Con.; B, D = Cu.                         |
| 14S-65               | 14S-6               | 6              |              | 6  | None                    | A, C, E = Cu.; B, D, F = Con.                   |
| 14S-67               | 14S-6               | 6              |              | 6  | None                    | A = Al.; B = Ch.; Balance = Cu.                 |
| 14S-68               | 14S-2               | 4              |              | 4  | 45°                     | A = Ch.; B = Con.; C, D = Cu.                   |
| 14S-69               | 14S-7               | 3              |              | 3  | None                    | A = Con.; B = Ch.; C = Cu.                      |
| 14S-70               | 14S-2               | 4              |              | 4  | None                    | A, D = Ch.; B, C = Al.                          |
| 14S-71               | 14S-2               | 4              |              | 4  | None                    | A, B, D = Cu.; C = Con.                         |
| 14S-72               | 14S-9               | 2              |              | 2  | None                    | A = Con.; B = Cu.                               |
| 14S-73               | 14S-2               | 4              |              | 4  | None                    | A, B = Cu.; C = Al.; D = Ch.                    |

# Thermocouple contact arrangements

| Shell<br>Size<br>and Arrg. | Similar<br>to<br>MS Arrg. | Total<br>Contacts | Contact<br>Size |    | Pin<br>Insert<br>Rotation<br>C W | Contact Material                                |
|----------------------------|---------------------------|-------------------|-----------------|----|----------------------------------|-------------------------------------------------|
|                            |                           |                   | 12              | 16 |                                  |                                                 |
| 14S-74                     | 14S-2                     | 4                 |                 | 4  | None                             | A, B = Ch.; C, D = Al.                          |
| 14S-75                     | 14S-2                     | 4                 |                 | 4  | None                             | A, B = Cu.; C, D = Con.                         |
| 14S-76                     | 14S-2                     | 4                 |                 | 4  | None                             | A, C = Al.; B, D = Ch.                          |
| 14S-77                     | 14S-2                     | 4                 |                 | 4  | None                             | A, D = Al.; B, C = Ch.                          |
| 14S-78                     | 14S-9                     | 2                 |                 | 2  | None                             | A = Ch.; B = Al.                                |
|                            |                           |                   |                 |    |                                  |                                                 |
| 16S-52                     | 16S-4                     | 2                 |                 | 2  | None                             | A = Ch.; B = Al.                                |
| 16S-54                     | 16S-1                     | 7                 |                 | 7  | None                             | A = Al.; B = Ch.; Balance = Cu.                 |
| 16S-55                     | 16S-1                     | 7                 |                 | 7  | None                             | A = Con.; Balance = Cu.                         |
|                            |                           |                   |                 |    |                                  |                                                 |
| 16-52                      | 16-11                     | 2                 | 2               |    | 90°                              | A = Al.; B = Ch.                                |
| 16-53                      | 16-9                      | 4                 | 2               | 2  | 70°                              | A = Al.; C = Ch.; B, D = Cu.                    |
| 16-55                      | 16-10                     | 3                 | 3               |    | 45°                              | A = Al.; B = Ch.; C = Cu.                       |
| 16-56                      | 16-13                     | 2                 | 2               |    | 90°                              | A = Con.; B = Cu.                               |
| 16-57                      | 16-10                     | 3                 | 3               |    | None                             | A = Al.; B = Cu.; C = Ch.                       |
| 16-58                      | 16-10                     | 3                 | 3               |    | None                             | A = Con.; B, C = Cu.                            |
| 16-60                      | 16-13                     | 2                 | 2               |    | None                             | A = Al.; B = Ch.                                |
| 16-62                      | 16-11                     | 2                 | 2               |    | None                             | A = Con.; B = Cu.                               |
|                            |                           |                   |                 |    |                                  |                                                 |
| 18-51                      | 18-12                     | 6                 |                 | 6  | None                             | A = Ir.; B, E = Con.; D = Cu.; C, F = Dummy     |
| 18-52                      | 18-11                     | 5                 | 5               |    | None                             | A = Ir.; B = Con.; C = Ch.; D = Al.; E = Dummy  |
| 18-53                      | 18-12                     | 6                 |                 | 6  | None                             | A, D = Ir.; B, E = Con.; C, F = Dummy           |
| 18-54                      | 18-15                     | 4                 | 4               |    | None                             | A, C = Al.; B, D = Ch.                          |
| 18-56                      | 18-1                      | 10                |                 | 10 | 45°                              | A, C, E, G, I = Ir.; B, D, F, H, J = Con.       |
| 18-57                      | 18-12                     | 6                 |                 | 6  | 45°                              | A, C, E = Al.; B, D, F = Ch.                    |
| 18-59                      | 18-12                     | 6                 |                 | 6  | 45°                              | A, C = Ir.; B, E, F = Con.; D = Cu.             |
| 18-60                      | 18-11                     | 5                 | 5               |    | 45°                              | A, D = Al.; B, C, = Ch.; E = Cu.                |
| 18-61                      | 18-12                     | 6                 |                 | 6  | None                             | A, C = Ir.; B, D = Con.; E = Ch.; F = Al.       |
| 18-62                      | 18-12                     | 6                 |                 | 6  | None                             | A, B, C = Ir.; D, E, F = Con.                   |
| 18-63                      | 18-15                     | 4                 | 4               |    | None                             | A, C = Con.; B, D = Cu.                         |
| 18-65                      | 18-12                     | 6                 |                 | 6  | None                             | A = Ir.; B = Con.; Balance = Cu.                |
| 18-66                      | 18-1                      | 10                |                 | 10 | None                             | A, C, E, G, I = Cu.; B, D, F, H, J = Con.       |
| 18-67                      | 18-12                     | 6                 |                 | 6  | None                             | A, C, E = Cu.; B, D, F = Con.                   |
| 18-68                      | 18-11                     | 5                 | 5               |    | None                             | A, D = Al.; B, C = Ch.; E = Cu.                 |
| 18-69                      | 18-1                      | 10                |                 | 10 | None                             | A = Al.; B = Ch.; Balance = Cu.                 |
| 18-70                      | 18-11                     | 5                 | 5               |    | None                             | A = Ir.; B = Con.; C = Ch.; D = Al.; E = Cu.    |
| 18-71                      | 18-15                     | 4                 | 4               |    | None                             | A = Con.; Balance = Cu.                         |
| 18-72                      | 18-15                     | 4                 | 4               |    | None                             | D = Con.; Balance = Cu.                         |
| 18-73                      | 18-9                      | 7                 | 2               | 5  | None                             | A = Al.; D = Ch.; Balance = Cu.                 |
| 18-74                      | 18-12                     | 6                 |                 | 6  | None                             | A = Ch.; B = Al.; D = Ir.; E = Cu.; C, F = Con. |
|                            |                           |                   |                 |    |                                  |                                                 |
| 20-52                      | 20-4                      | 4                 | 4               |    | 315°                             | A = Ir.; B = Con.; C = Ch.; D = Al.             |
| 20-56                      | 20-7                      | 8                 |                 | 8  | 45°                              | A, B, G, H = Ir.; C, D, E, F = Con.             |
| 20-60                      | 20-7                      | 8                 |                 | 8  | 45°                              | D = Ch.; E = Al.; Balance = Cu.                 |
| 20-61                      | 20-29                     | 17                |                 | 17 | 45°                              | A, B, M = Cu.; Balance = Con.                   |
| 20-62                      | 20-15                     | 7                 | 7               |    | 80°                              | A, C, E = Al.; B, D, F = Ch.; G = Cu.           |
| 20-64                      | 20-27                     | 14                |                 | 14 | None                             | A = Al.; C = Ch.; Balance = Cu.                 |

# Thermocouple

## contact arrangements

| Shell Size and Arrg. | Similar to MS Arrg. | Total Contacts | Contact Size |    | Pin Insert Rotation C W | Contact Material                                                                                            |
|----------------------|---------------------|----------------|--------------|----|-------------------------|-------------------------------------------------------------------------------------------------------------|
|                      |                     |                | 12           | 16 |                         |                                                                                                             |
| 20-65                | 20-27               | 14             |              | 14 | None                    | A, B, C, D, E, F, G = Ir.; H, I, J, K, L, M, N = Con.                                                       |
| 20-67                | 20-16               | 9              | 2            | 7  | None                    | H = Al.; I = Ch.; Balance = Cu.                                                                             |
| 20-68                | 20-7                | 8              |              | 8  | None                    | A, B, G, H = Con.; C, D, E, F = Cu.                                                                         |
| 20-69                | 20-27               | 14             |              | 14 | None                    | A, B, C, D, E, F, G = Cu.; H, I, J, K, L, M, N = Con.                                                       |
| 20-70                | 20-29               | 17             |              | 17 | None                    | A, C, E, G, J, L, N, R, T = Ir.; B, D, F, H, K, M, P, S = Con.                                              |
| 20-71                | 20-29               | 17             |              | 17 | None                    | S = Al.; R = Ch.; Balance = Cu.                                                                             |
| 20-74                | 20-29               | 17             |              | 17 | None                    | A, C, E, G, J, L, N, R = Ir.; B, D, F, H, K, M, P, S = Con.; T = Cu.                                        |
| 20-75                | 20-15               | 7              | 7            |    | None                    | G = Al.; Balance = Ch.                                                                                      |
| 20-77                | 20-16               | 9              | 2            | 7  | None                    | A = Con.; Balance = Std.                                                                                    |
| 20-80                | 20-27               | 14             |              | 14 | None                    | A, C, E, G, I, K, M = Cu.; B, D, F, H, J, L, N = Con.                                                       |
| 20-81                | 20-27               | 14             |              | 14 | None                    | A, C, E, G, I, K, M = Ch.; B, D, F, H, J, L, N = Al.                                                        |
| 20-82                | 20-29               | 17             |              | 17 | None                    | A, C, E, G, J, L, N, R = Al.; B, D, F, H, K, M, P, S = Ch.; T = Cu.                                         |
|                      |                     |                |              |    |                         |                                                                                                             |
| 22-36                | 22-23               | 8              | 8            |    | 347°                    | A, C, E, G = Ir.; B, D, F, H = Con.                                                                         |
| 22-57                | 22-14               | 19             |              | 19 | 45°                     | A, C, E, G, J, L, N, R = Ir.; B, D, F, H, K, M, P, S = Con.; T, U, V = Cu.                                  |
| 22-60                | 22-14               | 19             |              | 19 | 45°                     | U = Al.; N = Ch.; Balance = Cu.                                                                             |
| 22-62                | 22-23               | 8              | 8            |    | 60°                     | A, B, F, G = Al.; C, D, E, H = Ch.                                                                          |
| 22-68                | 22-19               | 14             |              | 14 | 45°                     | A, C, E, G, J, L, M = Ir.; B, D, F, H, K, P, N = Con.                                                       |
| 22-69                | 22-19               | 14             |              | 14 | 45°                     | A, C, E, G, J, L, M = Cu.; B, D, F, H, K, P, N = Con.                                                       |
| 22-71                | 22-14               | 19             |              | 19 | None                    | V = Al.; U = Ch.; Balance = Cu.                                                                             |
| 22-72                | 22-5                | 6              | 2            | 4  | None                    | B = Al.; E = Ch.; Balance = Cu.                                                                             |
| 22-73                | 22-5                | 6              | 2            | 4  | None                    | E = Al.; B = Ch.; Balance = Cu.                                                                             |
| 22-74                | 22-23               | 8              | 8            |    | None                    | A, C, E, G = Ir.; B, D, F, H = Con.                                                                         |
| 22-75                | 22-23               | 8              | 8            |    | None                    | A = Al.; B, D, G, H = Cu.; C = Ch.; E = Ir.; F = Con.                                                       |
| 22-76                |                     | 21             |              | 21 | None                    | W = Con.; Balance = Cu.                                                                                     |
| 22-77                | 22-19               | 14             |              | 14 | None                    | B, D, F, H, J, K, M, P = Cu.; A, E, L = Ir.; C, G, N = Con.                                                 |
| 22-78                | 22-14               | 19             |              | 19 | None                    | A, C, E, G, H, K, M, P, R, T = Con.; Balance = Cu.                                                          |
| 22-79                | 22-10               | 4              |              | 4  | None                    | A, C, = Con.; B, D = Cu.                                                                                    |
|                      |                     |                |              |    |                         |                                                                                                             |
| 24-56                | 24-20               | 11             | 2            | 9  | 45°                     | E = Al.; F = Ch.; Balance = Cu.                                                                             |
| 24-57                | 24-28               | 24             |              | 24 | 45°                     | A, C, J, V, Y, W, K, E, H, U, S, M = Ch.; Balance = Al.                                                     |
| 24-62                | 24-28               | 24             |              | 24 | None                    | A, C, E, G = Ir.; B, D, F, H = Con.; R, T = Ch.; S, U = Al.; Balance = Cu.                                  |
| 24-63                | 24-28               | 24             |              | 24 | None                    | A, C, E, G, J, L, K, N, S, U, W, Y = Cu.; B, D, F, H, Q, R, M, P, T, V, X, Z = Con.                         |
| 24-64                | 24-5                | 16             |              | 16 | None                    | A, B, C, D, E, F, G, H = Ir.; J, K, L, M, N, P, R, S = Con.                                                 |
| 24-68                | 24-28               | 24             |              | 24 | None                    | D = Con.; Balance = Cu.                                                                                     |
| 24-81                | 24-7                | 16             | 2            | 14 | None                    | A, C, E, G, I, K, M, N, P = Cu.; B, D, F, H, J, L, O = Con.                                                 |
|                      |                     |                |              |    |                         |                                                                                                             |
| 28-53                | 28-11               | 22             | 4            | 18 | 45°                     | J, L = Al.; K, M = Ch.; Balance = Cu.                                                                       |
| 28-58                | 28-20               | 14             | 10           | 4  | 45°                     | A, C, E, G, K, M = Al.; B, D, F, H, L, N = Ch.; J, P = Cu.                                                  |
| 28-61                | 28-21               | 37             |              | 37 | 45°                     | A, C, J, Z, m, r, n, a, K, F, H, X, k, h, T, M, N, d = Ir.; Balance = Con.                                  |
| 28-63                | 28-20               | 14             | 10           | 4  | 45°                     | A, C, E, G, J = Al.; B, D, F, H, P = Ch.; Balance = Cu.                                                     |
| 28-64                | 28-15               | 35             |              | 35 | None                    | A, d = Al.; B, j = Ch.; C, D, E, F, G, N, P, R, S, H, J, K, L, M, W, X, Y, Z = Con.; Balance = Cu.          |
| 28-65                | 28-12               | 26             |              | 26 | None                    | A, C, E, G, J, L, N, R, T, V = Ir.; X, Z = Al.; B, D, F, H, K, M, P, S, U, W = Con.; Y, a = Ch.; b, d = Cu. |
| 28-67                | 28-16               | 20             |              | 20 | None                    | U = Con.; Balance = Cu.                                                                                     |
| 28-68                | 28-15               | 35             |              | 35 | 45°                     | T = Al.; U = Ch.; Balance = Cu.                                                                             |

## Thermocouple contact arrangements

[illegible]

\* Amphenol arrangement