

Reflecting small LEDs, directly mountable (φ3.1mm) (no need for solder modification)


SLI-343 Series

The SLI-343 series are 3.1mm LEDs which can be directly mounted on a printed circuit board. Three colors and two lens types are available for a total of six types, and they are suitable for use in a wide variety of applications.

●Features

- 1) Three colors : red, orange and yellow.
- 2) Two lens types : Colored diffused and Colored clear.
- 3) High reliability even in case of direct mount.
- 4) Blow-holeless solder type.

●External dimensions (Units : mm)



●Selection guide

Lens \ Emitting color	Red	Orange	Yellow
Lens			
Colored diffused	SLI-343UR	SLI-343DU	SLI-343YY
Colored clear	SLI-343URC	SLI-343DC	SLI-343YC

LED lamps

SLI-343 Series

●Absolute maximum ratings (Ta = 25°C)


Parameter	Symbol	Red	Orange	Yellow	Unit
		SLI-343UR SLI-343URC	SLI-343DU SLI-343DC	SLI-343YY SLI-343YC	
Power dissipation	P _D	125	125	125	mW
Forward current	I _F	50	50	50	mA
Peak forward current	I _{FP}	200*	200*	200*	mA
Reverse voltage	V _R	9	9	9	V
Operating temperature	T _{opr}	-25~+85			°C
Storage temperature	T _{stg}	-30~+100			°C
Soldering temperature	—	260°C 5 seconds maximum			—

* Pulse width 100μs Duty 1 / 10

●Electrical and optical characteristics (Ta = 25°C)

Parameter	Symbol	Conditions	Red			Orange			Yellow			Unit
			Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	
Forward voltage	V _F	I _F =2mA	(1.4)	1.85	2.2	(1.4)	1.85	2.2	(1.4)	1.85	2.2	V
		I _F =20mA	(1.45)	1.9	2.4	(1.45)	1.9	2.4	(1.45)	1.9	2.4	
Reverse current	I _R	V _R =9V	—	—	100	—	—	100	—	—	100	μA
Peak wavelength	λ _P	I _F =20mA	—	630	—	—	611	—	—	591	—	nm
Spectral line half width	Δλ	I _F =20mA	—	20	—	—	17	—	—	15	—	nm
Viewing angle	2θ _{1/2}	Diffused	—	40	—	—	40	—	—	40	—	deg
		Transparent	—	40	—	—	40	—	—	40	—	

●Luminous intensity vs. wavelength



●Luminous intensity

Color	Type	Conditions	Min.	Typ.	Max.	Unit
Red	SLI-343UR	I _F =2mA	—	35	—	mcd
		I _F =20mA	90	350	—	
	SLI-343URC	I _F =2mA	—	45	—	
		I _F =20mA	90	450	—	
Orange	SLI-343DU	I _F =2mA	—	35	—	
		I _F =20mA	90	350	—	
	SLI-343DC	I _F =2mA	—	50	—	
		I _F =20mA	90	500	—	
Yellow	SLI-343YY	I _F =2mA	—	30	—	
		I _F =20mA	90	300	—	
	SLI-343YC	I _F =2mA	—	35	—	
		I _F =20mA	90	350	—	

LED lamps

● Directional pattern




Fig.2

● Electrical characteristic curves (URC, UR, DC, DU, YC, YY)




Fig.3 Forward current vs. forward voltage




Fig.4 Luminous intensity vs. case temperature




Fig.5 Luminous intensity vs. forward current




Fig.6 Ratio maximum tolerable peak vs. pulse duration




Fig.7 Derating

Appendix

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document use silicon as a basic material.

Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.