



5102




5102-0-00-XX-00-00-33-0
Press-fit in .057 mounting hole

1502




1502-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

2956-0




2956-0-00-XX-00-00-03-0
Surface mount

2956-1




2956-1-00-XX-00-00-03-0
Surface mount

8940




8940-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

8876



8876-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole


0259/0286/1941



02XX-0-00-XX-00-00-03-0
Press-fit in .057/.059 mounting hole


Basic Part Number	Length L	Barb Dia. E	Mounting Hole
0259-0	.173	.062	.059
0286-0	.115	.060	.057
1941-0	.169	.058	.057

1938




1938-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

1940




1940-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

1942



1942-0-00-XX-00-00-03-0
Press-fit in .057 mounting hole

3024



3024-0-01-XX-00-00-03-0
Press-fit in .057 mounting hole

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
(Except Swage pins which are annealed)

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - 00 - 00 - 0X - 0

BASIC PART #



SPECIFY PIN FINISH:

- 01** 200 μ" TIN/LEAD OVER NICKEL
- 80** 200 μ" TIN OVER NICKEL
- 15** 10 μ" GOLD OVER NICKEL
- 21** 20 μ" GOLD OVER NICKEL
- 34** 50 μ" GOLD OVER NICKEL