



OPERATING HEAD MOUNTS
IN ANY OF FOUR
POSITIONS



.75 DIA. X .25 WIDE
STEEL ROLLER (4)








LEVER
INVERTED

LEVER ADJUSTING SCREW
WITH .156 REF. HEX SOCKET

CAM TRACKING VIEW

CAPTIVE HEAD
SCREW (4)



REVISIONS	DATE	BY	CHKD
A	CO18388	CO18785	
B	CO20461		
C	CO20897		
D	CO20673		
E	CO32809		
F	CO50952		
G	CO70394		
H	CO70394-B		
J	CO-77031		
K	CO-78083		

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS
OPERATING TORQUE - - 4.5 IN-LB MAX
FULL OVERTRAVEL TORQUE - 6 IN-LB MAX
RELEASE TORQUE - - .75 IN-LB MIN
PRETRAVEL - - - - - 23° MAX
DIFFERENTIAL TRAVEL - - - 16° MAX
OVERTRAVEL - - - - - 23° MIN
RELEASE TRAVEL - - - - - 4° MIN
SWITCH-BASIC REPLACEMENT - - 8AS42

ELECTRICAL DATA
CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)

(B)

10 A-125 OR 250 VAC
1/2 HP-125 VAC

SCALE 1/2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT 9 OZ

NOTE-

- 1-SWITCH IS ASSEMBLED FOR ACTUATION IN BOTH DIRECTIONS BUT MAY BE ADJUSTED TO ACTUATE IN EITHER THE CLOCKWISE DIRECTION ONLY OR THE COUNTERCLOCKWISE DIRECTION ONLY
- 2-TO CONVERT SWITCH FOR ACTUATION IN EITHER THE CLOCKWISE OR COUNTERCLOCKWISE DIRECTION ONLY, REMOVE ACTUATOR HEAD AND ROTATE THE NOTCHED PLUNGER 90° TO THE RIGHT FOR CLOCKWISE ACTUATION OR 90° TO THE LEFT FOR COUNTERCLOCKWISE ACTUATION

(3)

SEAL TO BE FURNISHED BY USER.

(4)

ROLLER LEVER MAY BE LOCKED IN ANY POSITION THRU 360°

5- LEVER FURNISHED UNASSEMBLED IN UNIT PACKING BOX