

TOSHIBA CMOS Digital Integrated Circuit Silicon Monolithic

# TC74LVXC3245FS

## Dual Supply Octal Configurable Voltage Interface Bus Transceiver


The TC74LVXC3245FS is a dual supply, advanced high-speed CMOS octal configurable voltage interface bus transceiver fabricated with silicon gate CMOS technology.

Designed for use as an interface between a 3.3 V bus and a 3.3V to 5 V bus in mixed 3.3 V/5 V supply systems' it achieves high-speed operation while maintaining the CMOS low power dissipation.

It is intended for 2 way asynchronous communication between data busses.

The direction of data transmission is determined by the level of the DIR input. The enable input ( $\overline{G}$ ) can be used to disable the device so that the busses are effectively isolated. The A-port interfaces with the 3.3-V bus, the B-port with the 3.3V to 5V bus. This device will allow the  $V_{CCB}$  voltage source pin and I/O pins on the B port to float when  $\overline{G}$  is "H".

All inputs are equipped with protection circuits against static discharge or transient excess voltage.



Weight: 0.14 g (typ.)


### Features

- Bi-directional interface between 3 V and 5 V buses
- High-speed:  $t_{pd} = 8.5 \text{ ns (max)}$   
( $V_{CCA} = 3.3 \text{ V}$ ,  $V_{CCB} = 5.0 \text{ V}$ )
- Low power dissipation:  $I_{CC} = 8 \mu\text{A (max)}$  ( $T_a = 25^\circ\text{C}$ )
- Symmetrical output impedance:  $I_{OUTA} = \pm 24 \text{ mA (min)}$   
 $I_{OUTB} = \pm 24 \text{ mA (min)}$   
( $V_{CCA} = V_{CCB} = 3.0 \text{ V}$ )
- Low noise:  $V_{OLP} = 1.5 \text{ V (max)}$
- Flexible  $V_{CCB}$  operating range
- Allows B port and  $V_{CCB}$  to float simultaneously when  $\overline{G}$  is "H"
- Package: SSOP (shrink small outline package)


Note: Do not apply a signal to any bus pins when it is in the output mode. Damage may result.

All floating (high impedance) bus pin must have their input levels fixed by means of pull-up or pull-down resistors.

Pin Assignment (top view)



IEC Logic Symbol




Truth Table

Inputs		Outputs	Function	
$\overline{G}$	DIR		A-Bus	B-Bus
L	L	A = B	Output	Input
L	H	B = A	Input	Output
H	X	Z	High impedance	

X: Don't care

Z: High impedance

## Block Diagram



## Absolute Maximum Ratings (Note 1)

Characteristics	Symbol	Rating	Unit
Supply voltage range (Note 2)	$V_{CCA}$	-0.5 to 7.0	V
	$V_{CCB}$	-0.5 to 7.0	
DC input voltage (DIR, $\bar{G}$ )	$V_{IN}$	-0.5 to $V_{CCA} + 0.5$	V
DC bus I/O voltage	$V_{IOA}$	-0.5 to $V_{CCA} + 0.5$	V
	$V_{IOB}$	-0.5 to $V_{CCB} + 0.5$	
Input diode current	$I_{IK}$	$\pm 20$	mA
Output diode current	$I_{I/OK}$	$\pm 50$	mA
DC output current	$I_{OUTA}$	$\pm 50$	mA
	$I_{OUTB}$	$\pm 50$	
DC $V_{CC}$ /ground current	$I_{CCA}$	$\pm 200$	mA
	$I_{CCB}$	$\pm 200$	
Power dissipation	$P_D$	180	mW
Storage temperature	$T_{stg}$	-65 to 150	°C

Note 1: Exceeding any of the absolute maximum ratings, even briefly, lead to deterioration in IC performance or even destruction.

Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc.).

Note 2: Don't supply a voltage to  $V_{CCB}$  terminal when  $V_{CCA}$  is in the OFF state.

**Operating Ranges (Note 1)**

Characteristics	Symbol	Rating	Unit
Supply voltage range (Note 2)	$V_{CCA}$	2.7 to 3.6	V
	$V_{CCB}$	3.0 to 5.5	
Input voltage (DIR, $\overline{G}$ )	$V_{IN}$	0 to $V_{CCA}$	V
Bus I/O voltage	$V_{I/OA}$	0 to $V_{CCA}$	V
	$V_{I/OB}$	0 to $V_{CCB}$	
Operating temperature	$T_{opr}$	-40 to 85	°C
Input rise and fall time	dt/dv	0 to 8	ns/V
		( $V_{CCA} = 2.7$ to $3.6$ V)	
		0 to 8 ( $V_{CCB} = 3.0$ to $5.5$ V)	

Note1: The operating ranges are required to ensure the normal operation of the device. Unused inputs and bus inputs must be tied to either  $V_{CC}$  or GND. Please connect both bus inputs and the bus outputs with  $V_{CC}$  or GND when the I/O of the bus terminal changes by the function. In this case, please note that the output is not short-circuited.

Note2: Don't use in  $V_{CCA} > V_{CCB}$ .

**Electrical Characteristics**
**DC Characteristics**

Characteristics		Sym- bol	Test Condition			Ta = 25°C			Ta = -40 to 85°C		Unit	
						VCCA (V)	VCCB (V)	Min	Typ.	Max		Min
Input voltage (VCCA)	H-level	VIHA	DIR, $\bar{G}$ , An	2.7	3.0	2.0	—	—	2.0	—	V	
				3.0	3.6	2.0	—	—	2.0	—		
				3.6	5.5	2.0	—	—	2.0	—		
	L-level	VILA	DIR, $\bar{G}$ , An	2.7	3.0	—	—	0.8	—	0.8		
				3.0	3.6	—	—	0.8	—	0.8		
				3.6	5.5	—	—	0.8	—	0.8		
Input voltage (VCCB)	H-level	VIHB	Bn	2.7	3.0	2.0	—	—	2.0	—	V	
				3.0	3.6	2.0	—	—	2.0	—		
				3.6	5.5	3.85	—	—	3.85	—		
	L-level	VILB	Bn	2.7	3.0	—	—	0.8	—	0.8		
				3.0	3.6	—	—	0.8	—	0.8		
				3.6	5.5	—	—	1.65	—	1.65		
Output voltage (VCCA)	H-level	VOHA	VINA = VIHA or VILA VINB = VIHB or VILB	IOH = -100 μA	3.0	3.0	2.9	3.0	—	2.9	—	V
				IOH = -12 mA	3.0	3.0	2.56	—	—	2.46	—	
				IOH = -24 mA	3.0	3.0	2.35	—	—	2.25	—	
				IOH = -12 mA	2.7	3.0	2.3	—	—	2.2	—	
				IOH = -24 mA	2.7	4.5	2.1	—	—	2.0	—	
	L-level	VOLA		IOL = 100 μA	3.0	3.0	—	0	0.1	—	0.1	
				IOL = 24 mA	3.0	3.0	—	—	0.36	—	0.44	
				IOL = 12 mA	2.7	3.0	—	—	0.36	—	0.44	
				IOL = 24 mA	2.7	4.5	—	—	0.42	—	0.5	

## DC Characteristics (continued)

Characteristics		Sym- bol	Test Condition			Ta = 25°C			Ta = -40 to 85°C		Unit	
						VCCA (V)	VCCB (V)	Min	Typ.	Max		Min
Output voltage (VCCB)	H-level	VOHB	VINA = VIHA or VILA VINB = VIHB or VILB	I <sub>OH</sub> = -100 μA	3.0	3.0	2.9	3.0	—	2.9	—	V
				I <sub>OH</sub> = -12 mA	3.0	3.0	2.56	—	—	2.46	—	
				I <sub>OH</sub> = -24 mA	3.0	3.0	2.35	—	—	2.25	—	
				I <sub>OH</sub> = -24 mA	3.0	4.5	3.86	—	—	3.76	—	
	L-level	VOLB		I <sub>OL</sub> = 100 μA	3.0	3.0	—	0	0.1	—	0.1	
				I <sub>OL</sub> = 24 mA	3.0	3.0	—	—	0.36	—	0.44	
				I <sub>OL</sub> = 24 mA	3.0	4.5	—	—	0.36	—	0.44	
3-state output Off-state current		IOZA	VINA = VIHA or VILA VINB = VIHB or VILB		3.6	3.6	—	—	±0.5	—	±5.0	μA
					3.6	5.5	—	—	±0.5	—	±5.0	
		IOZB	VI/OA = VCCA or GND VI/OB = VCCB or GND		3.6	3.6	—	—	±0.5	—	±5.0	
					3.6	5.5	—	—	±0.5	—	±5.0	
Input leakage current		IIN	VIN (DIR, $\overline{G}$ ) = VCCA or GND		3.6	3.6	—	—	±0.1	—	±1.0	μA
					3.6	5.5	—	—	±0.1	—	±1.0	
Quiescent supply current		ICCT	PER INPUT: VIN = 3.0 V		3.6	3.6	—	—	0.35	—	0.5	mA
		ICCA1	An = VCCA or GND Bn = Open, $\overline{G}$ = VCCA DIR = VCCA, VCCB = Open		3.6	Open	—	—	5	—	50	μA
		ICCA2	VINA = VIHA or VILA VINB = VIHB or VILB		3.6	3.6	—	—	5	—	50	
					3.6	5.5	—	—	5	—	50	
		ICCB	VINA = VIHA or VILA VINB = VIHB or VILB		3.6	3.6	—	—	5	—	50	
3.6	5.5				—	—	8	—	80			

## AC Characteristics (input: $t_r = t_f = 3 \text{ ns}$ , $C_L = 50 \text{ pF}$ , $R_L = 500 \Omega$ , $V_{CCA}=2.7 \text{ to } 3.6 \text{ V}$ )

Characteristics	Symbol	Test Condition	Ta = 25°C				Ta = -40 to 85°C		Unit
			V <sub>CCB</sub> (V)	Min	Typ.	Max	Min	Max	
Propagation delay time (An → Bn)	t <sub>pLH</sub>	Input: An Output: Bn (DIR = "H")	5.0 ± 0.5	—	5.7	8.0	1.0	8.5	ns
	t <sub>pHL</sub>		3.3 ± 0.3	—	6.2	8.5	1.0	9.0	
3-state output enable time ( $\overline{G}$ → Bn)	t <sub>pZL</sub>		5.0 ± 0.5	—	6.5	9.5	1.0	10.0	ns
	t <sub>pZH</sub>		3.3 ± 0.3	—	7.4	10.5	1.0	11.5	
3-state output disable time ( $\overline{G}$ → Bn)	t <sub>pLZ</sub>		5.0 ± 0.5	—	7.3	9.5	1.0	10.0	ns
	t <sub>pHZ</sub>		3.3 ± 0.3	—	6.6	9.5	1.0	10.0	
Propagation delay time (Bn → An)	t <sub>pLH</sub>	Input: Bn Output: An (DIR = "L")	5.0 ± 0.5	—	4.6	7.5	1.0	8.0	ns
	t <sub>pHL</sub>		3.3 ± 0.3	—	5.2	7.5	1.0	8.0	
3-state output enable time ( $\overline{G}$ → An)	t <sub>pZL</sub>		5.0 ± 0.5	—	7.0	10.5	1.0	11.5	ns
	t <sub>pZH</sub>		3.3 ± 0.3	—	7.0	10.5	1.0	11.5	
3-state output disable time ( $\overline{G}$ → An)	t <sub>pLZ</sub>		5.0 ± 0.5	—	6.1	9.5	1.0	10.0	ns
	t <sub>pHZ</sub>		3.3 ± 0.3	—	6.0	9.5	1.0	10.0	
Output to output skew	t <sub>osLH</sub>	(Note 1)	5.0 ± 0.5	—	—	1.5	—	1.5	ns
	t <sub>osHL</sub>		3.3 ± 0.3	—	—	1.5	—	1.5	
Input capacitance	C <sub>I</sub> NA	DIR, $\overline{G}$	5.0 ± 0.5	—	5	10	—	10	pF
Bus input capacitance	C <sub>I</sub> /O	An, Bn		—	8	—	—	—	
Power dissipation capacitance  (Note 2)	C <sub>P</sub> DA	A → B (DIR = "H")	5.0 ± 0.5	—	4	—	—	—	pF
		B → A (DIR = "L")		—	38	—	—	—	
	C <sub>P</sub> DB	A → B (DIR = "H")	5.0 ± 0.5	—	88	—	—	—	
		B → A(DIR = "L")		—	7	—	—	—	

Note 1: Parameter guaranteed by design.

$$(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)$$

Note 2: C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation:

$$I_{CC(opr)} = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC} / 8 \text{ (per bit)}$$

**Noise Characteristics (Ta = 25°C, input: tr = tf = 3 ns, CL = 50 pF, RL = 500 Ω)**





Characteristics	Symbol	Test Condition			Typ.	Limit	Unit
			V <sub>CCA</sub> (V)	V <sub>CCB</sub> (V)			
Quiet output maximum dynamic V <sub>OL</sub> (A)	V <sub>OLPA</sub>	Input: Bn Output: An (DIR = "L")	3.3	3.3	—	0.9	V
			3.3	5.0	—	0.9	
Quiet output minimum dynamic V <sub>OL</sub> (A)	V <sub>OLVA</sub>		3.3	3.3	—	−0.9	
			3.3	5.0	—	−0.9	
Quiet output maximum dynamic V <sub>OL</sub> (B)	V <sub>OLPB</sub>	Input: An Output: Bn (DIR = "H")	3.3	3.3	—	0.8	
			3.3	5.0	—	1.5	
Quiet output minimum dynamic V <sub>OL</sub> (B)	V <sub>OLVB</sub>		3.3	3.3	—	−0.8	
			3.3	5.0	—	−1.2	
Minimum high level dynamic input voltage V <sub>IH</sub> (A)	V <sub>IHDA</sub>	Input: An	3.3	3.3	—	2.0	V
			3.3	5.0	—	2.0	
Maximum low level dynamic input Voltage V <sub>IL</sub> (A)	V <sub>ILDA</sub>	Input: An	3.3	3.3	—	0.8	V
			3.3	5.0	—	0.8	
Minimum high level dynamic input voltage V <sub>IH</sub> (B)	V <sub>IHDB</sub>	Input: Bn	3.3	3.3	2.0	—	V
			3.3	5.0	3.5	—	
Maximum low level dynamic input voltage V <sub>IL</sub> (B)	V <sub>ILDB</sub>	Input: Bn	3.3	3.3	0.8	—	V
			3.3	5.0	1.5	—	



Package Dimensions

SSOP24-P-300-0.65D

Unit: mm



Weight: 0.14 g (typ.)

## RESTRICTIONS ON PRODUCT USE

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").** Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. **IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.** For details, please contact your TOSHIBA sales representative.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**