




REV. 2
DCO 142664

COIL: @ 25°C
 RESISTANCE _____ 720 OHMS ±10%
 NOMINAL VOLTAGE _____ 26.5 VDC
 MUST OPERATE _____ 13.5 VDC


 MUST RELEASE _____ 8.1 VDC MAX., 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE 4 MS MAX.
 _____ RELEASE 6 MS MAX.
 _____ CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO _____
 _____ 2 AMPS 28 VDC RESISTIVE
 _____ 100,000 OPERATIONS

DR. PBB 5-3-00

CK.



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. _____ QPL
 CUST. NO. M39016/53-012M REV. _____

3SBH RELAY

3SBH1231A2