

APL3015F3C

APL3015SF4C

Features


- WATER CLEAR LENS AVAILABLE.
- 3.0mmx1.5mm SMT LED, 1.4mm THICKNESS.
- HIGH POWER OUTPUT.
- PACKAGE: 2000PCS/REEL.

Description

F3 Made with Gallium Arsenide Infrared Emitting diodes.

SF4 Made with Gallium Aluminum Arsenide Infrared Emitting diodes.

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.2(0.0079)$ unless otherwise noted.
3. Lead spacing is measured where the lead emerge package.
4. Specifications are subject to change without notice.

Selection Guide

Part No.	Dice	Lens Type	Po= (mW/sr) @20mA		Viewing Angle
			Min.	Typ.	
AP3216F3C	GaAs	WATER CLEAR	0.5	1.2	120°
AP3216SF4C	GaAlAs	WATER CLEAR	0.5	1	120°

Note:

1. $\theta 1/2$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at $T_A=25^\circ\text{C}$


Item	P/N	Symbol	Typ.	Max.	Unit	Condition
Forward Voltage	F3 SF4	V_F	1.2 1.3	1.5 1.7	V	IF=20mA
Reverse Current	F3 SF4	I_R	-	10 10	uA	VR=5V
Junction Capacitance	F3 SF4	C	90 90	-	pF	V=0 f=1MHz
Peak Spectral Wavelength	F3 SF4	λ_P	940 880	-	nm	IF=20mA
Spectral Bandwidth	F3 SF4	$\Delta\lambda$	50 50	-	nm	IF=20mA

Absolute Maximum Ratings at $T_A=25^\circ\text{C}$





Item	Symbol	Maximum Rating	Units
Power Dissipation	P_T	100	mW
Forward Current	I_F	50	mA
Peak Forward Current	i_{FS}	1.2	A
Reverse Voltage	V_R	5	V
Operating Temperature	T_A	-40~ +85	°C
Storage Temperature	T_{STG}	-40~ +85	°C

Note:





1. 1/100 Duty Cycle, 10us Pluse Width.



APL3015F3C




APL3015SF4C




APL3015F3C, APL3015SF4C SMT Reflow Soldering Instructions

Number of reflow process shall be less than 2 times and cooling process to normal temperature is required between first and second soldering process.



Recommended Soldering Pattern (Units : mm)



Tape Specifications (Units : mm)

