







TOLERANCES:		ITEM/REQ'D	PART NO.	DESCRIPTION
±.005 BETWEEN HOLE CENTERS	MAT. AS NOTED	SCALE	NAME	
±.005 FROM BEARING EDGE	FINESS AS NOTED			
±.005 FROM A BENT SURFACE	DR. RD. 10-13-08		BID INDUSTRIES, INC.	PLASTICASE STYLE I
±.005 BETWEEN ASSEMBLED SURFACES	CH.		VILLAGEVIEW, OHIO	6.10 X 3.62 X 1.16
UNLESS OTHERWISE SPECIFIED	APP.			DWG. NO. PC-11477
QTY.	USED ON			ISSUE REVISIONS



MATERIAL : HIGH IMPACT UL-94-HB ABS.
 COLOR:
 LID & BASE ARE MOLDED IN LIGHT GREY COLOR
 FRONT & END PANELS
 ARE MOLDED IN DARK GREY COLOR
 FINISH:
 FRONT & END PANELS ARE SMOOTH WITH TEXTURE ONLY IN THE RECESS AREA.
 LID & BASE ARE SMOOTH WITH TEXTURE ONLY IN OUTSIDE RAISED AREA.
 FOUR (4) INTERNAL BOSSES ON BASE & LID ARE
 AVAILABLE FOR PCB ASSEMBLY. USE M2.5 OR
 #4 STD SHEET METAL SCREWS.
 ALL DIMENSIONAL TOLERANCES ARE ±.015
 RUBBER FEET PART NUMBER ----- AVAILABLE AS ACCESSORY

TOLERANCES:		ITEM/REQ'D	PART NO.	DESCRIPTION
±.005 BETWEEN HOLE CENTERS	MAT. AS NOTED	SCALE	NAME	
±.005 FROM BEARING EDGE	FINESS AS NOTED			
±.005 FROM A BENT SURFACE	DR. RD. 10-13-08		BID INDUSTRIES, INC.	PLASTICASE STYLE I
±.005 BETWEEN ASSEMBLED SURFACES	CH.		VILLAGEVIEW, OHIO	6.10 X 3.62 X 1.16
UNLESS OTHERWISE SPECIFIED	APP.			DWG. NO. PC-11477
QTY.	USED ON			ISSUE REVISIONS