


LOC		DIST		REVISIONS						
AD		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
					G1	REVISED PER ECO-09-024717		05NOV09	KK	AEG



RECOMMENDED HOLE LAYOUT

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
 - TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3

.000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL ENTIRE POST
- 4

BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5

.000100-.000200 MATTE TIN OVER .000050 NICKEL ENTIRE POST
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	5	3.984	3.900	39	40	9-103759-0
	5	3.484	3.400	34	35	-8-5
	5	2.984	2.900	29	30	-8-0
	5	2.484	2.400	24	25	-7-5
	5	1.984	1.900	19	20	-7-0
	5	1.484	1.400	14	15	-6-5
	5	1.384	1.300	13	14	-6-4
OBSOLETE	5	1.284	1.200	12	13	-6-3
	5	1.184	1.100	11	12	-6-2
	5	1.084	1.000	10	11	6-1
	5	.984	.900	9	10	-6-0
OBSOLETE	5	.884	.800	8	9	-5-9
	5	.784	.700	7	8	-5-8
	5	.684	.600	6	7	5-7
OBSOLETE	5	.584	.500	5	6	-5-6
	5	.484	.400	4	5	-5-5
	5	.384	.300	3	4	-5-4
	5	.284	.200	2	3	-5-3
OBSOLETE	5	.184	.100	1	2	5-2
OBSOLETE	5	.084			1	-5-103759-1
OBSOLETE	3	3.984	3.900	39	40	4-103759-0
OBSOLETE	3	3.884	3.800	38	39	3-9
OBSOLETE	3	3.784	3.700	37	38	3-8
OBSOLETE	3	3.684	3.600	36	37	3-7
OBSOLETE	3	3.584	3.500	35	36	3-6
6	3	3.484	3.400	34	35	3-5
OBSOLETE	3	3.284	3.300	33	34	3-4
OBSOLETE	3	3.284	3.200	32	33	3-3
OBSOLETE	3	3.184	3.100	31	32	3-2
OBSOLETE	3	3.084	3.000	30	31	3-1
6	3	2.984	2.900	29	30	3-0
OBSOLETE	3	2.884	2.800	28	29	2-9
OBSOLETE	3	2.784	2.700	27	28	2-8
OBSOLETE	3	2.684	2.600	26	27	2-7
OBSOLETE	3	2.584	2.500	25	26	2-6
6	3	2.484	2.400	24	25	2-5
OBSOLETE	3	2.384	2.300	23	24	2-4
OBSOLETE	3	2.284	2.200	22	23	2-3
OBSOLETE	3	2.184	2.100	21	22	2-2
OBSOLETE	3	2.084	2.000	20	21	2-1
6	3	1.984	1.900	19	20	2-0
OBSOLETE	3	1.884	1.800	18	19	1-9
OBSOLETE	3	1.784	1.700	17	18	1-8
OBSOLETE	3	1.684	1.600	16	17	1-7
OBSOLETE	3	1.584	1.500	15	16	1-6
OBSOLETE	3	1.484	1.400	14	15	-4-5
	3	1.384	1.300	13	14	-4-4
	3	1.284	1.200	12	13	-4-3
	3	1.184	1.100	11	12	-4-2
OBSOLETE	3	1.084	1.000	10	11	-1-1
	3	.984	.900	9	10	-4-0
	3	.884	.800	8	9	-9
	3	.784	.700	7	8	-8
OBSOLETE	3	.684	.600	6	7	-7
	3	.584	.500	5	6	-6
	3	.484	.400	4	5	-5
	3	.384	.300	3	4	-4
6	3	.284	.200	2	3	-3
6	3	.184	.100	1	2	-2
6	3	.084			1	-103759-1

PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER
---------	---	---	---	-----------	----------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. D. RINGLEY	23JUL85	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK R. FLICKER	12NOV87	NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± ± - ANGLES		APPLICATION SPEC	
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK; POSTS: PHOS BRONZE		FINISH: SEE TABLE		WEIGHT: -	
CUSTOMER DRAWING		SCALE: 4:1		SHEET 1 OF 1	
REV		G1		REV	