




+ HARNESSING

## SOLDERSLEEVE SHIELD TERMINATORS



✓ Active

TE CONNECTIVITY (TE)

**S200-5-01-100HN**

Raychem

S200-5-01-100HN

TE Internal Number: D92195-000

Alias ID: 9-1202143-8

EU RoHS Compliant

EU ELV Compliant

**Product Type** Shield Terminator

**Operating Temperature (Max) (°C)** 200

**Expanded Inside Diameter (Min)** 6.98 mm [ .275 in ]

**Recovered Inside Diameter (Max)** 7.62 mm [ .3 in ]

**Pre-Installed Lead** Yes

### PRODUCT DRAWING

English

## DOCUMENTATION

Product Drawings

**SolderSleeve Shield Terminator With Pre-Installed Braid 200deg.C, RoHS Compliant**

PDF

English

Catalog Pages/Data Sheets

**Raychem S200 Shield Terminators**

PDF

English

Product Specifications

Product Specification

**Installation Procedure For Standard SolderSleeve Shield Terminators**

PDF

**FEATURES**

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

**Product Type Features**

**Product Type** Shield Terminator

**Temperature Indicator** Yes

**Temperature Indicator Type** Fusible Ring

**Splice Type** Shield Terminator

**Configuration Features**

**Pre-Installed Lead** Yes

**Pre-Installed Lead Type** Braid

**Body Features**

**Shield Outside Diameter (Min)** 4.3 mm [.17 in]

**Lead Color** Braid

**Lead Plating Material** Nickel

**Termination Features**

**Termination Method** Solder

**Dimensions**

**Expanded Inside Diameter (Min)** 6.98 mm [.275 in]

**Recovered Inside Diameter (Max)** 7.62 mm [.3 in]

**Overall Length** 19.1 mm [.75 in]

**Pre-Installed Lead Wire Size (CMA)** 640

**Dielectric Outside Diameter (Max)** 6.98 mm [.275 in]

**Jacket Outside Diameter** 6.9 mm [.27 in]

**Usage Conditions**

**Operating Temperature (Max) (°C)** 200

**Resistance Properties** Immersion Protection

**Wire Temperature (Max) (°C)** 200

**Industry Standards**

**Government Qualified** No

**Statement of Compliance****Statement of Compliance**

PDF