



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	WIRE RANGE	MATERIAL	STYLE	"B"	"C"	COLOR (PRINT ON AREA)	LABELS/ROLL
N050X075CBC	12-10 AWG	GMC4	1	0.50 [12.70]	0.75 [19.05] 1.50 [38.10]	WHITE	125
N050X150CBC	8-2 AWG		2		0.75 [19.05]		75
N100X075CBC	12-10 AWG		1	1.00 [25.40]	1.25 [31.75]		125
N100X125CBC	10-6 AWG		2		1.50 [38.10]		75
N100X150CBC	8 -2 AWG		1		1.75 [44.45]		50
N100X175CBC	6 -1 AWG						
N050X075C1C	12-10 AWG	GMC6	2	0.50 [12.70]	0.75 [19.05]	WHITE	125
N050X075C2C	12-10 AWG		3		0.75 [19.05]	YELLOW	
N050X125C1C	10-6 AWG		2		1.25 [31.75]	WHITE	75
N050X125C2C	10-6 AWG		3		1.25 [31.75]	YELLOW	
N100X075C1C	12-10 AWG		2	1.00 [25.40]	0.75 [19.05]	WHITE	125
N100X075C2C	12-10 AWG		3		0.75 [19.05]	YELLOW	
N100X125C1C	10-6 AWG		2		1.25 [31.75]	WHITE	75
N100X125C2C	10-6 AWG		3		1.25 [31.75]	YELLOW	

NOTES:

1. DIMENSIONS IN []
ARE IN MILLIMETERS.



STYLE 1 STYLE 2 STYLE 3

							TITLE
4	9/10/14	RVU	SEWH	MSAD	ADD NEW STYLE 3 WITH BRIDGES. CHANGE PN, N050X075C2C, N050X125C2C, N100X075C2C, N100X125C2C FROM STYLE 2 TO 3.	GAECN02298	ITEM REVISION NAME I00743CJ/16
3	4/30/14	RVU	SEWH	MSAD	PART NUMBER, ALL N***X***CBC, C*C FOR THE VINYL & NYLON CLOTH CASSETTES SHOW A WIRE RANGE, ALL ARE NOT CORRECT.	GAECN01935	DATASET FILE NAME I00743CJ_DC_C10693/16D
2	11/17/12	HONG			CHANGE TO CURRENT TEMPLATE AND ADDED N100X075CBC	GAECN00399	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .025 [.635] .x. ± .03 [.762] ANGLES ±
1	06/25/10	RVU			ADD NEW PN N***X***C*C.	6029	THIRD ANGLE PROJECTION
0	04/21/08	RVU			DRAWING RELEASE	5403	DRAWING NUMBER: C10693
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY RVU DATE 4/22/08 CHK MSAD SCALE NTS
							SHT 1 OF 1 SIZE A