



## 0.39" Single Digit Displays

PART NO. : ELS-432GWA ECN :            Page: 1/5

### ■ Features :

- Industrial standard size.
- Low power consumption.
- Categorized for luminous intensity.

### ■ Applications:

- Audio equipment
- Instrument panels
- Digital read out display

### ■ Descriptions :

- The ELS-432 series is a large 10.0 mm (0.39")high seven segment display designed for viewing distances up to 7 meters.
- These displays provide excellent reliability in bright ambient light.
- These devices are made with white segments and gray surface.

| PART NO.   | Chip     |               |
|------------|----------|---------------|
|            | Material | Emitted Color |
| ELS-432GWA | GaP      | Green         |

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936

FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>




Device Number : CDDS-432-017      REV: 1

## 0.39" Single Digit Displays

PART NO. : ELS-432GWA      ECN :                 Page: 2/5

■ Package Dimensions:



COMMON ANODE  
1 CATHODE G  
2 CATHODE F  
3 COMMON ANODE  
4 CATHODE E  
5 CATHODE D  
6 CATHODE DP  
7 CATHODE C  
8 COMMON ANODE  
9 CATHODE B  
10 CATHODE A

■ Notes:

- 1.All dimensions are in millimeters , tolerance is 0.25mm unless otherwise noted.  
2.Above specification may be changed without notice.  
Supplier will reserve authority on material change for above specification.



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDDS-432-017 REV: 1

0.39" Single Digit Displays

PART NO. : ELS-432GWA ECN : Page: 3/5

■ Absolute maximum ratings at Ta = 25°C :

| Parameter                              | Symbol   | Rating      | Unit |
|----------------------------------------|----------|-------------|------|
| Reverse Voltage                        | VR       | 5           | V    |
| Forward Current                        | IF       | 30          | mA   |
| Operating Temperature                  | Topr     | -40 to +85  | °C   |
| Storage Temperature                    | Tstg     | -40 to +100 | °C   |
| Soldering Temperature                  | Tsol     | 260 ± 5     | °C   |
| Power Dissipation                      | Pd       | 100         | mW   |
| Peak Forward Current(Duty 1/10 @ 1KHZ) | IF(Peak) | 160         | mA   |

■ Electronic optical characteristics :

| Parameter                    |                   | Symbol | Min. | Typ. | Max. | Unit | Condition |
|------------------------------|-------------------|--------|------|------|------|------|-----------|
| Luminous Intensity           | Per segment       | Iv     | 1.05 | 3.20 | ---- | mcd  | IF=10mA   |
|                              | Per decimal point |        | 0.45 | 1.0  | ---- |      |           |
| Peak Wavelength              |                   | λ p    | ---- | 565  | ---- | nm   | IF=20mA   |
| Dominant Wavelength          |                   | λ d    | ---- | 570  | ---- | nm   | IF=20mA   |
| Spectrum Radiation Bandwidth |                   | △ λ    | ---- | 30   | ---- | nm   | IF=20mA   |
| Forward Voltage              |                   | VF     | 1.7  | 2.1  | 2.4  | V    | IF=20mA   |
| Reverse Current              |                   | IR     | ---- | ---- | 10   | μ A  | VR=5V     |



# EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDDS-432-017

REV: 1

0.39" Single Digit Displays




PART NO. : ELS-432GWA

ECN :

Page: 4/5

## Typical Electro-Optical Characteristic Curves:

CHIP Material:Gap  
Emitted Color:Yellow Green





# EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDDS-432-017

REV: 1

0.39" Single Digit Displays

PART NO. : ELS-432GWA

ECN :

Page: 5/5

## Reliability test items and conditions:

| NO | Item                             | Test Conditions                               | Test Hours/Cycle | Sample Size | Ac/Re |
|----|----------------------------------|-----------------------------------------------|------------------|-------------|-------|
| 1  | Solder Heat                      | TEMP : 260°C ± 5 °C                           | 5 SEC            | 76 PCS      | 0/1   |
| 2  | Temperature Cycle                | H : +85°C 30min<br>└ 5 min<br>L : -55°C 30min | 50 CYCLE         | 76 PCS      | 0/1   |
| 3  | Thermal Shock                    | H : +100°C 5min<br>└ 10 sec<br>L : -10°C 5min | 50 CYCLE         | 76 PCS      | 0/1   |
| 4  | High Temperature Storage         | TEMP : 100°C                                  | 1000 HRS         | 76 PCS      | 0/1   |
| 5  | Low Temperature Storage          | TEMP : -55°C                                  | 1000 HRS         | 76 PCS      | 0/1   |
| 6  | DC Operating Life                | IF = 10 mA                                    | 1000 HRS         | 76 PCS      | 0/1   |
| 7  | High Temperature / High Humidity | 85°C /85% RH                                  | 1000 HRS         | 76 PCS      | 0/1   |