






MATERIAL NO.	ENGINEERING NO.	LENGTH
1300140015	2R6004A20A120	12' +.75-0 [305mm +19.0-0]
1300140017	2R6004A20F030	3'0' +1.75-0 [.9M +44.5-0]
1300140019	2R6004A20F060	6'0' +2.19-0 [1.8M +55.6-0]



1	ORANGE
2	BLUE
3	BLACK
4	WHITE
5	RED
6	GREEN/YELLOW

- NOTES:
 1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. MATES WITH: 6/C MINI-CHANGE CORD ASSY.
 4. ELECTRICAL SPECIFICATIONS:
 VOLTAGE RATING: 600V AC/DC
 CURRENT RATING: 8 AMPS
 5. RoHS COMPLIANT

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
7	1	LABEL	PLASTIC FILM	BLACK/YELLOW
6	1	POTTING	EPOXY	
5	6	WIRE, 16 AWG (UL 1015)	PVC INSULATED	SEE WIRE DIAGRAM
4	6	SOCKET SLEEVE	ST.STEEL	
3	6	CONTACT SOCKET	BRASS	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	1	RECEPTACLE SHELL	ZINC ALLOY	E-COAT, BLACK

RELEASED
 EC NO: MNA2009-0655
 DRAWN BY: DRWINRSTONE 2009/04/03
 CHKD BY: WOODMAN
 APPR: J.MURPHY 2009/04/08

QUALITY SYMBOLS
 $\nabla=0$
 $\nabla=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	$\pm .005$	$\pm .0005$
3 PLACES	$\pm .005$	$\pm .0005$
2 PLACES	$\pm .01$	$\pm .001$
1 PLACE	± 0.3	$\pm .012$

ANGULAR $\pm 1/2^\circ$

DRAFT WHERE APPLICABLE
 MUST REMAIN
 WITHIN DIMENSIONS

DIMENSION STYLE
 IN/MM

DRAWN BY: R. STONE DATE: 2009/04/03
 CHECKED BY: B. WOODMAN DATE: 2009/04/03
 APPROVED BY: J. MURPHY DATE: 2009/04/07

MATERIAL NO. SEE CHART

SCALE 1:1 DESIGN UNITS INCH THIRD ANGLE PROJECTION

TITLE
 MINI-CHANGE RECEPTACLE
 FEMALE, 6 POLE
 1/2 IN NPT

MOLEX INCORPORATED

DOCUMENT NO. SD-130014-002 SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300140015](#)