




Weight: 0.31g Unit: mm



AND134CRP

GaAlAs Red Light Emission

T-1 3/4 Package (5 mm)

Features

- Peak wavelength ($\lambda_p = 660$ nm) high bright emission
- All plastic mold type, red diffused lens
- Low drive current: 20 mA for outdoor applications
0.5 mA for indoor applications
- Fast response time, capable of pulse operation

Maximum Ratings ($T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Rating	Unit
Forward Current	I_F	30	mA
Reverse Voltage	V_R	4	V
Power Dissipation	P_D	100	mW
Operating Temperature Range	T_{Opr}	-25 to 85	$^\circ\text{C}$
Storage Temperature Range	T_{Stg}	-25 to 100	$^\circ\text{C}$

Electro-Optical Characteristics ($T_a = 25^\circ\text{C}$)

Characteristics	Symbol	Test Condition	Minimum	Typical	Maximum	Unit
Forward Voltage	V_F	$I_F = 20$ mA	—	1.9	2.5	V
Reverse Current	I_R	$V_R = 4$ V	—	—	100	μA
Luminous Intensity	I_V	$I_F = 20$ mA	360	600	—	mcd
Peak Emission Wavelength	λ_p	$I_F = 20$ mA	—	660	—	nm
Spectral Line Half Width	$\Delta\lambda$	$I_F = 20$ mA	—	25	—	nm
Dominant Wavelength	λ_d	$I_F = 20$ mA	—	640	—	nm
Full Viewing Angle	θ	$I_V = 1/2$ Peak	—	40	—	degree

Precaution

Please be careful of the following:

1. Soldering temperature: 260°C max

Soldering time: 5 sec. max

Soldering portion of lead: up to 1.6 mm from the body of the device

The lead can be formed up to 5 mm from the body of the device without forming stress.

Soldering should be performed after the lead forming.

