

DWG. NO.
SD-54729-009

F

D

A

C

B

DO NOT SCALE DRAWING

8

7

6

5

4

3

2

1

F




E

D

C

B

A



注記 NOTES

1. 材質 MATERIAL
ハウジング : 液晶ポリマーガラス充填, 黒色, UL94V-0
HOUSING : LIQUID CRYSTAL POLYMER GLASS FILLED
COLOR BLACK, UL94V-0
ターミナル : 燐青銅 (t=0.15)
TERMINAL : PHOSPHOR BRONZE (t=0.15)
2. メッキ仕様 PLATING
金メッキ 0.25マイクロメートル以上。(コンタクト部)
GOLD 0.25MICROMETER MINIMUM (CONTACT AREA)
金メッキ 0.4マイクロメートル以下。(テール部)
GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)
下地メッキ : ニッケルメッキ 2.5マイクロメートル以上。
UNDER-PLATING : NICKEL 2.5MICROMETER MINIMUM

3. 嵌合相手 : 55559 シリーズ
MATES WITH : 55559 SERIES
4. テール平坦度は 0.1以下。
TAIL COPLANARITY TO BE 0.1 MAXIMUM
5. パターン書き込み禁止エリア
NO FOOT PRINT AREA.

5.5	7.7	54729-0241	24
3.5	5.7	54729-0161	16
B	A	MATERIAL NO.	CKT. NO.

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	RELEASED/REVISED '04/02/04 EC NO. J2004-0314 DRWN: R. SUMIYA CHK: S. AIHARA APPR: M. SASAO PROPOSED '01/04/11 EC NO. JC2001-0282 DRWN: M. HAYASHI CHK: T. ITO APPR: T. YAMAGUCHI	MATERIAL 材料 注記参照 SEE NOTES FINISH 仕上げ 注記参照 SEE NOTES WIRE RANGE 適用電線範囲 —//— INS. RANGE 被覆外径 —//—	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差 10 UNDER 未満 ±0.2 10 OVER 以上 ±0.25 30 UNDER 未満 ±0.3 30 OVER 以上 ±0.3 ANGLE 角度 ±3°	SCALE —//— DRAWN BY & DATE M. HAYASHI '01/04/11 CHECKED BY & DATE T. ITO '01/04/11 APPROVED BY & DATE T. YAMAGUCHI '01/04/11 CAD FILENAME 54729009.S01	MODEL NO. 54729-***1 DESIGN UNITS mm INCH THIRD ANGLE PROJECTION TITLE: 0.5 B-To-B Rec Hsg Assy (Hg±2mm) MOLEX MOLEX INCORPORATED	DIMENSIONS: mm INCH mm ONLY SHT REV REVISION ON CAD ONLY	MATERIAL NO. SEE CHART DRAWING NO. SD-54729-009 SHEET NO. 1 OF 1
----------------------------------	----------------------------------	----------------------------------	---	---	---	---	--	--	---

8

7

6

5

4

3

2

EN-02J(097) MXJ-54

54729009.S01