


# 263 Series

## PICO® II 250 Volt Fuse, Very Fast Acting



### Description

The PICO® II 263 Series Fuse is a specially designed axial leaded fuse that achieves a 250V rating in a small package.

### Features & Benefits

- 250V rating
- Very fast-acting
- Small size
- Wide range of current rating available (62mA to 5A)
- RoHS compliant and Halogen-free
- Wide operating temperature range
- Low temperature derating

### Additional Information



Resources



Accessories



Samples

### Applications

- Lighting system
- Power supply
- LCD/PDP TV
- LCD monitor
- Office automation machines
- Audio/Video system
- Medical equipment

### Electrical Characteristics

| % of Ampere Rating | Opening Time            |
|--------------------|-------------------------|
| 100%               | 4 Hours, <b>Min.</b>    |
| 200%               | 1 Second, <b>Max.</b>   |
| 300%               | 0.1 Second, <b>Max.</b> |

### Agency Approvals

| Agency | Agency File Number   | Ampere Range |
|--------|----------------------|--------------|
|        | E10480               | 0.062A - 5A  |
|        | PSE_NBK200416-JP1021 | 1A - 5A      |
|        | 29862                | 0.125 - 5A   |
|        | NA                   | 0.062A - 5A  |
|        | NA                   | 0.062A - 5A  |

### Electrical Characteristics


| Ampere Rating (A) | Amp Code | Max Voltage Rating (V) | Interrupting Rating            | Nominal Cold Resistance (Ohms) | Nominal Melting I <sup>2</sup> t (A <sup>2</sup> sec) | Nom Voltage Drop (mV) | Agency Approvals |    |    |     |    |
|-------------------|----------|------------------------|--------------------------------|--------------------------------|-------------------------------------------------------|-----------------------|------------------|----|----|-----|----|
|                   |          |                        |                                |                                |                                                       |                       | UKCA             | CE | UL | PSE | SP |
| 0.062             | .062     | 250                    | 50A@250VAC<br>PSE: 100A@125VAC | 5.50                           | 0.000192                                              | 0.74                  | x                | x  | x  | -   | -  |
| 0.125             | .125     | 250                    |                                | 1.745                          | 0.00251                                               | 0.3                   | x                | x  | x  | -   | x  |
| 0.250             | .250     | 250                    |                                | 0.715                          | 0.0165                                                | 0.235                 | x                | x  | x  | -   | x  |
| 0.375             | .375     | 250                    |                                | 0.391                          | 0.0444                                                | 0.195                 | x                | x  | x  | -   | x  |
| 0.500             | .500     | 250                    |                                | 0.252                          | 0.084                                                 | 0.302                 | x                | x  | x  | -   | x  |
| 0.750             | .750     | 250                    |                                | 0.150                          | 0.0411                                                | 0.176                 | x                | x  | x  | -   | x  |
| 1.00              | 001.     | 250*                   |                                | 0.105                          | 0.087                                                 | 0.165                 | x                | x  | x  | x   | x  |
| 1.50              | 015.     | 250*                   |                                | 0.0635                         | 0.2958                                                | 0.148                 | x                | x  | x  | x   | x  |
| 2.00              | 002.     | 250*                   |                                | 0.0444                         | 0.74                                                  | 0.137                 | x                | x  | x  | x   | x  |
| 2.50              | 02.5     | 250*                   |                                | 0.0340                         | 1.197                                                 | 0.128                 | x                | x  | x  | x   | x  |
| 3.00              | 003.     | 250*                   |                                | 0.0274                         | 1.77                                                  | 0.1225                | x                | x  | x  | x   | x  |
| 3.50              | 03.5     | 250*                   |                                | 0.0224                         | 2.33                                                  | 0.1175                | x                | x  | x  | x   | x  |
| 4.00              | 004.     | 250*                   |                                | 0.0193                         | 3.08                                                  | 0.1125                | x                | x  | x  | x   | x  |
| 5.00              | 005.     | 250*                   |                                | 0.0145                         | 5.55                                                  | 0.1065                | x                | x  | x  | x   | x  |

\* PSE Approval has max. voltage range of 125VAC.

# 263 Series

## PICO® II 250 Volt Fuse, Very Fast Acting

### Temperature Re-rating Curve



**Note:** Re-rating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

### Soldering Parameters

#### Recommended Process Parameters:


| Wave Parameter                                       | Lead-Free Recommendation          |
|------------------------------------------------------|-----------------------------------|
| Preheat:<br>(Depends on Flux Activation Temperature) | (Typical Industry Recommendation) |
| Temperature Minimum:                                 | 100° C                            |
| Temperature Maximum:                                 | 150° C                            |
| Preheat Time:                                        | 60-180 seconds                    |
| Solder Pot Temperature:                              | 260° C Maximum                    |
| Solder Dwell Time:                                   | 2-5 seconds                       |

#### Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350° C +/- 5°C  
 Heating Time: 5 seconds max.

**Note:** These devices are not recommended for IR or Convection Reflow process.

### Average Time Current Curves



# 263 Series


## PICO® II 250 Volt Fuse, Very Fast Acting

### Product Characteristics

|                              |                                                                                                                                 |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| <b>Materials</b>             | Encapsulated, Epoxy-Coated<br>Body: Solder Coated Copper Leads.<br>RoHS compliant<br>Product: Pure Tin-coated Copper wire leads |
| <b>Solderability</b>         | MIL-STD-202, Method 208.                                                                                                        |
| <b>Product Marking</b>       | Body marking, current rating and logo                                                                                           |
| <b>Operating Temperature</b> | -55°C to +125°C (Consider re-rating)                                                                                            |
| <b>Shock</b>                 | MIL-STD-202, Method 213, Test Condition I (100 G's peak for 6 milliseconds)                                                     |

|                                               |                                                                                                           |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------|
| <b>Vibration</b>                              | MIL-STD-202, Method 201 (10–55 Hz); MIL-STD-202, Method 204, Test Condition C (55–2000 Hz at 10 G's Peak) |
| <b>Salt Spray</b>                             | MIL-STD-202, Method 101, Test Condition B (48 hrs.)                                                       |
| <b>Insulation Resistance (After Opening):</b> | MIL-STD-202, Method 302, Test Condition A (10,000 ohms minimum at 100 volts)                              |
| <b>Resistance to Soldering Heat</b>           | MIL-STD-202, Method 210, Test Condition C (10 sec. at 260°C)                                              |
| <b>Thermal Shock</b>                          | MIL-STD-202, Method 107, Test Condition B (-55°C to 125°C)                                                |
| <b>Moisture Resistance</b>                    | MIL-STD-202, Method 106                                                                                   |
| <b>Lead Pull Force</b>                        | MIL-STD-202, Method 211, Test Condition A (will withstand 7 lb. axial pull test)                          |

### Dimensions



### Part Numbering System

**0263 xxxx W R T1 L**

**Series**

**Current Rating**

Refer to Amp Code column of Electrical Characteristics Table

**Quantity**

W = 3000  
M = 1000  
H = 100

**Type of Packaging**

R = Reel  
A = Ammo Pack  
X = Loose Pack

**Lead Length**

T1: 52.4mm (2.062")\*

**RoHS + HF**

### Packaging

| Packaging Option                     | Packaging Specification | Quantity                                                              | Quantity & Packaging Code |
|--------------------------------------|-------------------------|-----------------------------------------------------------------------|---------------------------|
| T1: 52.4mm (2.062")<br>Tape and Reel | EIA 296                 | Please refer to available quantities above in "Part Numbering System" |                           |

**Notes:** \* T1 dimension is defined as the length of the component between the two tapes. The full component length is 62.7mm (2.468").

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)