








- 1 PART NO & DATE CODE MARKED (WHITE), .062±.015 HIGH CHARS. IN APPROX. AREA SHOWN WHEN HOUSING SIZE PERMITS.
- 2 CAVITY IDENTs. MARKED (WHITE), .046±.015 HIGH CHARS., FIRST & EVERY FIFTH CAVITY, ONE SIDE AS SHOWN.
- 3 TOLERANCE NON-CUMULATIVE.
- 4. USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 5 AMP LOGO MOLDED IN TEXTURED AREA AS SHOWN.
- 6 FLASH ALLOWED TO BE .015 IN THIS AREA.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|                                        |  |                                  |                 |  |
|----------------------------------------|--|----------------------------------|-----------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>E. BRANDBERG<br>21-JUN-95 | TE Connectivity |  |
| DIMENSIONS:<br>mm                      |  | CHK<br>S. SHUEY<br>21-JUN-95     |                 |  |
|                                        |  | APVD<br>D. DUPLER<br>21-JUN-95   | NAME            |  |
|                                        |  | PRODUCT SPEC                     |                 |  |
| MATERIAL<br>FLAME RETARDANT            |  | APPLICATION SPEC                 |                 |  |
|                                        |  | WEIGHT                           |                 |  |
| FINISH                                 |  | SCALE                            |                 |  |
| -                                      |  | 4:1                              |                 |  |
|                                        |  | SHEET                            |                 |  |
|                                        |  | 2 OF 2                           |                 |  |
|                                        |  | REV                              |                 |  |
|                                        |  | U3                               |                 |  |