

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS					DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
	A	Redrawn in Autcad	JAP	11/25/91					
1199	B	Redrawn and Renamed	JWM	11/8/01	JC	11/26/01	JC	11/26/01	


Notes:

Material: Electro-tin plated Copper

Insulating Material: Vinyl (PVC) UL94V-0

Voltage Rating: 600V

Operating Temp: -40°F to 221°F (-40°C ~ 105°C)



SPC Part Number	Wire Range (AWG)	Stud Size	S	W	T	M	Color	Seam
CBS-TV-1406	16 ~ 14	#6 (.138)	.148					
CBS-TV-1408	16 ~ 14	#8 (.164)	.174	.30	.090	.170	Blue	Butted Seam
CBS-TV-1410	16 ~ 14	#10 (.190)	.200					
CBS-TV-1804	22 ~ 18	#4 (.112)	.120	.25				
CBS-TV-1806	22 ~ 18	#6 (.138)	.148		.070	.145	Red	Butted Seam
CBS-TV-1808	22 ~ 18	#8 (.164)	.174	.30				
CBS-TV-1810	22 ~ 18	#10 (.190)	.200					
CBS-ZV-1406	16 ~ 14	#6 (.138)	.148					Brazed Seam
CBS-ZV-1408	16 ~ 14	#8 (.164)	.174	.30	.090	.170	Blue	
CBS-ZV-1410	16 ~ 14	#10 (.190)	.200					
CBS-ZV-1806	22 ~ 18	#6 (.112)	.148					Brazed Seam
CBS-ZV-1808	22 ~ 18	#8 (.138)	.174	.30	.070	.145	Red	
CBS-ZV-1810	22 ~ 18	#10 (.164)	.200					

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE SUBSCRIBER OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY



ES8918



LR22190M6

OSHA
Acceptable

SPC-F005.DWG

Tolerances: Unless Otherwise Specified:		DRAWING TITLE:	
.X = ±.015	DATE: 3/7/91	Insulated Block Fork Terminals	
.XX = ±.010	CHECKED BY: JOHN COLE		
.XXX = ±.005	DATE: 11/27/91		
APPROVED BY: John Liska	DATE: 11/27/91	DRAWING NO. TA-441	
		SIZE: A	SCALE: NTS
		U.O.M.: INCHES [mm]	
		ELECTRONIC FILE TA-441.dwg	
		REV B	
		SHEET: 1 OF 1	