




AD6010-11 SERIES

External Dimensions



Frame: Plastic (UL: 94V-0)
Impeller: Plastic (UL: 94V-0)
Lead wire: UL 1007 AWG26

Specifications (Nominal)


*: Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x10	AD0605LB-GA0(GLT1)	◎ ※ ●	5	0.25	1.25	3400	0.410 14.500	0.090 2.390	26.0	30.0
	AD0605MB-GA0(GLT1)	◎ ※ ●	5	0.33	1.65	4000	0.523 18.490	0.110 2.670	32.8	
	AD0612LB-GA0(GLT1)	◎ ※ ●	12	0.10	1.20	3400	0.410 14.500	0.090 2.390	26.0	
	AD0612MB-GA0(GLT1)	◎ ※ ●	12	0.14	1.68	4000	0.523 18.490	0.110 2.670	32.8	
	AD0612HB-GA0(GLT1)	◎ ※ ●	12	0.25	3.00	4600	0.604 21.370	0.140 3.610	35.8	
	AD0624LB-GA0(GLT1)	◎ ※ ●	24	0.04	0.96	3400	0.410 14.500	0.090 2.390	26.0	
	AD0624MB-GA0(GLT1)	◎ ※ ●	24	0.10	2.40	4000	0.523 18.490	0.110 2.670	32.8	
	AD0624HB-GA0(GLT1)	◎ ※ ●	24	0.18	4.32	4600	0.604 21.370	0.140 3.610	35.8	

Specifications subject to change without notice.

The specification for bearing type is for reference only, for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主, 若需其他產品資訊請聯絡您在ADDA的業務代表, 謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

✓	✓		✓	✓