

HC-B 48-SMLD/1PG29

Order No.: 1772214



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1772214>

Box mounting base, with single locking latch, height 100 mm, with screw connection, 1x Pg29, with protective covers

Commercial data	
EAN	4017918036881
Pack	1 pcs.
Customs tariff	85389099
Weight/Piece	1.439 KG
Catalog page information	Page 507 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B48, DD216, M
Design	B48
Height	100 mm
Width	120 mm

Length	145 mm
Locking type	With single locking latch
Type of the screw connection	1x Pg29
Pg screw connection	With
Wrench size, union nut	37 mm
Cable exit	Conductor exit direction to the left (looking into the open single locking latch)
External cable diameter	18 mm ... 27 mm
Protective cover	Yes
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Locking latch material	Steel, galvanized
Material, protective cover	PA

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;