

Features

Unregulated Converters

- UL/CSA and EN-60950-1 Safety certified
- EN-60601 for Medical Applications
- 6kVDC Isolation
- Optional Continuous Short Circuit Protection
- Efficiency up to 82%
- Space Saving „Skinny DIP“ Package
- Very Low Isolation Capacitance
- Suitable for IGBT Applications

Description

Very high isolation in a small size are the main features of this miniature DIP24 converter, ideal for highly sophisticated industrial, test and measurement and medical designs where board space is at a premium.

Selection Guide

Part Number	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency Std (%)	Max Capacitive Load ⁽¹⁾
SIP 7					
RV-xx3.3S*	3.3, 5, 12, 15, 24	3.3	600	70	3300µF
RV-xx05S*	3.3, 5, 12, 15, 24	5	400	70-75	1200µF
RV-xx09S*	3.3, 5, 12, 15, 24	9	222	70-75	1200µF
RV-xx12S*	3.3, 5, 12, 15, 24	12	167	70-75	680µF
RV-xx15S*	3.3, 5, 12, 15, 24	15	132	75-80	680µF
RV-xx24S*	3.3, 5, 12, 15, 24	24	83	75-80	220µF
RV-xx3.3D*	3.3, 5, 12, 15, 24	±3.3	±300	70	±1500µF
RV-xx05D*	3.3, 5, 12, 15, 24	±5	±200	70-75	±470µF
RV-xx09D*	3.3, 5, 12, 15, 24	±9	±111	70-75	±470µF
RV-xx12D*	3.3, 5, 12, 15, 24	±12	±85	70-75	±220µF
RV-xx15D*	3.3, 5, 12, 15, 24	±15	±66	75-80	±220µF
RV-xx24D*	3.3, 5, 12, 15, 24	±24	±42	75-80	±100µF
RV-xx1509D	5, 12, 24	+15/-9	+67/-111	70-82	±330µF

xx = Input Voltage. Other input and output voltage combinations available on request.

* add Suffix "P" for Continuous Short Circuit Protection, e.g. RV-0505S/P, RV-0505D/P

Specifications (measured at T_A = 25°C, nominal input voltage, full load and after warm-up)

Input Voltage Range	±10%
Output Voltage Accuracy	±5%
Line Voltage Regulation	1.2%/1% of Vin typ.
Load Voltage Regulation	3.3V output types 20% max.
(10% to 100% full load)	5V output type 15% max.
	9V, 12V, 15V, 24V output types, RV-xx1509D 10% max.
Output Ripple and Noise (20MHz limited)	200mVp-p max.
Operating Frequency	20kHz min. / 50kHz typ. / 85kHz max.
	RV-xx1509D 20kHz min. / 47kHz typ.
Efficiency at Full Load	70% min. / 75% typ.
Minimum Load = 0%	Specifications valid for 10% minimum load only.
Isolation Voltage	(tested for 1 second) 6000VDC
	(rated for 1 minute**) 3000VAC / 60Hz
Isolation Capacitance	2pF min. / 12pF max.
Isolation Resistance	15 GΩ min.
Short Circuit Protection	1 Second
P-Suffix	Continuous
Operating Temperature Range (free air convection, without derating)	-40°C to +90°C (see Graph)
Storage Temperature Range	-55°C to +125°C

continued on next page


ECONOLINE

DC/DC-Converter

with 3 year Warranty

RECOM


2 Watt DIP24 Miniature Single & Dual Output



EN-60950-1 Certified
IEC/EN-60601-1 Certified*
UL/CSA 60950-1 Certified*
*** +15/-9 Version excluded**

RV

Derating-Graph (Ambient Temperature)



**Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

Refer to Application Notes


Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up))

Relative Humidity	95% RH		
Package Weight	9g		
Packing Quantity	15 pcs per Tube		
MTBF (+25°C)	Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F	1154 x 10 ³ hours
(+85°C)		using MIL-HDBK 217F	168 x 10 ³ hours
Certifications	UL/cUL General Safety Report: E358085	UL 60950-1 2nd Ed.	
	EN General Safety Report: SPCLVD1109103	EN60950-1:2006 + A12: 2011	
	EN Medical Safety Report: SPCMDD1205098-4	IEC/EN60601-1:2006, 3rd Edition	

Notes



Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

Tolerance Envelope





Typical Characteristics

RV-xx05S





RV-xx12S





Typical Characteristics

RV-xx05D




RV-xx12D






Applications

IGBT Application Circuit





Package Style and Pinning (mm)

24 PIN DIP Miniature Package Style



Recommended Footprint Details



Pin Connections

Pin #	Single
1	+Vin
2	-Vin
8, 9, 11, 14	NC
10, 15	-Vout
12 & 13	+Vout
16, 17, 23, 24	NC

NC = No Connection

XX.X ± 0.5 mm
XX.XX ± 0.25 mm

Pin Connections

Pin #	Dual
1	+Vin
2	-Vin
8, 17	-Vout
9, 11, 14, 16, 23, 24	NC
10 & 15	Com
12, 13	+Vout

NC = No Connection