


Precision Thin Film Non-Magnetic Resistor, Surface Mount Chip, ± 25 ppm/ $^{\circ}\text{C}$, Tolerances to 0.1 %



LINKS TO ADDITIONAL RESOURCES



Packages



Footprints




Product Page



Order Samples

These devices eliminate materials that would disturb magnetic fields applications such as in MRI magnetic resonance imaging machines. The PNM series chip resistor has been carefully engineered with non-magnetic materials to eliminate the effects of these stray magnetic fields on circuit performance, thereby resulting in simplified shielding requirements and improved sound quality in audio applications. Providing signal conditioning without distortion from magnetic fields.

CONSTRUCTION



ATTENTION!
Observe Precautions for
Handling Electrostatic Sensitive Devices!

FEATURES

- Non-magnetic
- Moisture resistant
- High purity alumina substrate
- Non-standard values available
- MIL-STD-202 method 106 moisture resistance with 10 % power
- 100 % visual inspected per MIL-PRF-55342
- Very low noise and voltage coefficient (< -30 dB)
- Non-inductive
- Laser-trimmed tolerances to ± 0.1 %
- Wraparound resistance less than 10 m Ω
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details


RoHS*
Available

HALOGEN
FREE
Available

GREEN
(5-2008)
Available

TYPICAL PERFORMANCE

	ABSOLUTE
TCR	25
TOL.	0.1


STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Tantalum nitride	-
Resistance Range	10 Ω to 3 M Ω	-
TCR: Absolute	± 25 ppm/ $^{\circ}\text{C}$ to ± 100 ppm/ $^{\circ}\text{C}$	-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$
Tolerance: Absolute	± 0.1 % to ± 1.0 %	+25 $^{\circ}\text{C}$
Stability: Absolute	$\Delta R \pm 0.03$ %	-
Stability: Ratio	-	-
Voltage Coefficient	0.1 ppm/V	-
Working Voltage	75 V to 200 V	-
Operating Temperature Range	-55 $^{\circ}\text{C}$ to +155 $^{\circ}\text{C}$	-
Storage Temperature Range	-55 $^{\circ}\text{C}$ to +155 $^{\circ}\text{C}$	-
Noise	< -30 dB	-
Shelf Life Stability: Absolute	-	-

COMPONENT RATINGS			
CASE SIZE ⁽¹⁾	POWER RATING (mW)	WORKING VOLTAGE (V)	RESISTANCE RANGE (Ω)
0402	50	75	20 to 35K
0502	100	75	20 to 65K
0505	150	75	20 to 130K
0603	150	75	10 to 130K
0805	200	100	10 to 301K
0705	200	100	10 to 301K
1005	250	100	10 to 301K
1010	500	150	50 to 600K
1206	400	200	10 to 1M
1505	400	150	10 to 1M
2208	750	150	10 to 1.75M
2010	800	200	10 to 2M
2512	1000	200	10 to 3M

Note

⁽¹⁾ 0705 and 0805 are the same (only use 0805 when ordering)



DIMENSIONS in inches (millimeters)					
					
CASE SIZE	L	W	T	D	E
0402	0.042 ± 0.008 (1.067 ± 0.203)	0.022 ± 0.005 (0.559 ± 0.127)	0.012 to 0.033 (0.305 to 0.838)	0.010 ± 0.005 (0.254 ± 0.127)	0.010 ± 0.005 (0.254 ± 0.127)
0502	0.055 ± 0.006 (1.397 ± 0.152)	0.025 ± 0.005 (0.635 ± 0.127)	0.012 to 0.033 (0.305 to 0.838)	0.010 ± 0.005 (0.254 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
0505	0.055 ± 0.006 (1.397 ± 0.152)	0.050 ± 0.005 (1.27 ± 0.127)	0.012 to 0.033 (0.305 to 0.838)	0.010 ± 0.005 (0.254 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
0603	0.064 ± 0.006 (1.626 ± 0.152)	0.032 ± 0.005 (0.813 ± 0.127)	0.020 max. (0.508 max.)	0.012 ± 0.005 (0.305 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
0705/0805	0.080 ± 0.006 (2.032 ± 0.152)	0.050 ± 0.005 (1.27 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.015 ± 0.005 (0.381 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
1005	0.105 ± 0.007 (2.667 ± 0.178)	0.050 ± 0.005 (1.27 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.015 ± 0.005 (0.381 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
1010	0.105 ± 0.007 (2.667 ± 0.178)	0.100 ± 0.005 (2.54 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.015 ± 0.005 (0.381 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
1206	0.126 ± 0.008 (3.2 ± 0.203)	0.063 ± 0.005 (1.6 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.020 ± 0.005 / -0.010 (0.508 ± 0.127 / -0.254)	0.020 ± 0.005 / -0.010 (0.508 ± 0.127 / -0.254)
1505	0.155 ± 0.007 (3.937 ± 0.178)	0.050 ± 0.005 (1.27 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.015 ± 0.005 (0.381 ± 0.127)	0.015 ± 0.005 (0.381 ± 0.127)
2010	0.209 ± 0.009 (5.309 ± 0.229)	0.098 ± 0.005 (2.489 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.020 ± 0.005 (0.508 ± 0.127)	0.020 ± 0.005 (0.508 ± 0.127)
2208	0.230 ± 0.007 (5.842 ± 0.178)	0.075 ± 0.005 (1.905 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.020 ± 0.005 (0.508 ± 0.127)	0.020 ± 0.005 (0.508 ± 0.127)
2512	0.259 ± 0.009 (6.579 ± 0.229)	0.124 ± 0.005 (3.15 ± 0.127)	0.015 to 0.033 (0.381 to 0.838)	0.020 ± 0.005 (0.508 ± 0.127)	0.020 ± 0.005 (0.508 ± 0.127)

Note

⁽¹⁾ 0705 and 0805 are the same (only use 0805 when ordering)

**ENVIRONMENTAL TESTS** (Vishay Performance vs. MIL-PRF-55342 Requirements)

ENVIRONMENTAL TEST	LIMITS MIL-PRF-55342 CHARACTERISTIC "H"	TYPICAL VISHAY PERFORMANCE
Resistance Temperature Characteristic	$\pm 50 \text{ ppm/}^\circ\text{C}$	$\pm 35 \text{ ppm/}^\circ\text{C}$
Max. Ambient Temperature at Rated Wattage	$+70 \text{ }^\circ\text{C}$	$+70 \text{ }^\circ\text{C}$
Max. Ambient Temperature at Power Derating	$+150 \text{ }^\circ\text{C}$	$+150 \text{ }^\circ\text{C}$
Thermal Shock ΔR	$\pm 0.25 \%$	$\pm 0.040 \%$
Low Temperature Operation ΔR	$\pm 0.25 \%$	$\pm 0.005 \%$
Short Time Overload ΔR	$\pm 0.10 \%$	$\pm 0.010 \%$
High Temperature Exposure ΔR	$\pm 0.20 \%$	$\pm 0.150 \%$
Resistance to Bonding Exposure ΔR	$\pm 0.25 \%$	$\pm 0.005 \%$
Moisture Resistance ΔR	$\pm 0.40 \%$	$\pm 0.029 \%$
Life + $70 \text{ }^\circ\text{C}$ at 1000 hours ΔR	$\pm 0.50 \%$	$\pm 0.03 \%$
Insulation Resistance	10 000 Ω minimum	$> 100 \text{ 000 M}\Omega$

FILM LOAD LIFE STABILITY (at $+125 \text{ }^\circ\text{C}$)**DERATING CURVE****GLOBAL PART NUMBER INFORMATION**

GLOBAL MODEL															
P	N	M	1	2	0	6	E	1	0	0	2	B	B	T	1
GLOBAL MODEL	CASE SIZE	TCR CHARACTERISTIC	RESISTANCE				TOLERANCE		TERMINATION			PACKAGING			
PNM non-magnetic resistor	0402 0502 0505 0603 0805 1005 1010 1206 1505 2208 2010 2512	E = 25 ppm (<i>R</i> ≥ 100 Ω) H = 50 ppm (<i>R</i> ≥ 50 Ω) K = 100 ppm (<i>R</i> ≥ 10 Ω)	The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. "R" designates the decimal point. Example: 10R0 = 10 Ω 1000 = 100 Ω 1001 = 1 kΩ				B = ± 0.1 % ⁽¹⁾ D = ± 0.5 % F = ± 1 % G = ± 2 % J = ± 5 %		B = wraparound Sn/Pb solder 63 % Sn/ 37 % Pb S = wraparound lead (Pb)-free solder 96.5 % Sn/3.0 % Ag/ 0.5 % Cu RoHS compliant - e1			BS = BULK 100 min., 1 mult WS = WAFFLE 100 min., 1 mult TAPE AND REEL T0 = 100 min., 100 mult T1 = 1000 min., 1000 mult ⁽²⁾ T3 = 300 min., 300 mult T5 = 500 min., 500 mult TF = Full reel TS = 100 min., 1 mult			

Notes⁽²⁾ B = 0.1 % tolerance available only above 100 Ω ⁽³⁾ Preferred packaging code



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.