


## Printed-circuit board connector - MCV 0,5/ 3-G-2,54 SMD R24 - 1821559

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)

Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Color: black,  
Contact surface: Gold, Mounting: SMD soldering, Sample values available under SAMPLE MC...



The illustration shows the 10-position version



### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 STK    |
| Minimum order quantity               | 315 STK  |
| Weight per Piece (excluding packing) | 1.840 g  |
| Custom tariff number                 | 85366990 |
| Country of origin                    | Germany  |

### Technical data

#### Environmental Product Compliance

|            |                                                |
|------------|------------------------------------------------|
| China RoHS | No hazardous substances above threshold values |
|------------|------------------------------------------------|

#### Dimensions

|                          |             |
|--------------------------|-------------|
| Length                   | 4.85 mm     |
| Pitch                    | 2.54 mm     |
| Dimension a              | 5.08 mm     |
| Width                    | 12.2 mm     |
| Constructional height    | 7.1 mm      |
| Height                   | 9.1 mm      |
| Length of the solder pin | 2 mm        |
| Pin dimensions           | 0,64 x 0,64 |
| Hole diameter            | 1.2 mm      |

# Printed-circuit board connector - MCV 0,5/ 3-G-2,54 SMD R24 - 1821559

## Technical data

### General


|                                        |                   |
|----------------------------------------|-------------------|
| Range of articles                      | MCV 0,5/...-G-SMD |
| Insulating material group              | IIIa              |
| Rated surge voltage (III/3)            | 2.5 kV            |
| Rated surge voltage (III/2)            | 2.5 kV            |
| Rated surge voltage (II/2)             | 2.5 kV            |
| Rated voltage (III/3)                  | 32 V              |
| Rated voltage (III/2)                  | 160 V             |
| Rated voltage (II/2)                   | 160 V             |
| Connection in acc. with standard       | EN-VDE            |
| Nominal current $I_N$                  | 6 A               |
| Insulating material                    | LCP               |
| Flammability rating according to UL 94 | V0                |
| Color                                  | black             |
| Number of positions                    | 3                 |

### Standards and Regulations


|                                        |        |
|----------------------------------------|--------|
| Connection in acc. with standard       | EN-VDE |
| Flammability rating according to UL 94 | V0     |

## Drawings

Drilling diagram




Dimensional drawing



## Printed-circuit board connector - MCV 0,5/ 3-G-2,54 SMD R24 - 1821559

Diagram



Type FMC 0,5/...-ST-2,54 with MCV 0,5/...-G-2,54 SMD R..

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |
| eCl@ss 9.0 | 27440402 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

#### Approvals

cULus Recognized / VDE Gutachten mit Fertigungsüberwachung / IEC60320 CB Scheme / EAC

## Printed-circuit board connector - MCV 0,5/ 3-G-2,54 SMD R24 - 1821559

### Approvals

Ex Approvals

#### Approval details

|                                                                                                                                                                                        |       |      |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|
| cULus Recognized <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> E60425-19920306 |       |      |
|                                                                                                                                                                                        | B     | C    |
| Nominal current I <sub>N</sub>                                                                                                                                                         | 6 A   | 6 A  |
| Nominal voltage U <sub>N</sub>                                                                                                                                                         | 150 V | 50 V |

|                                                                                                                                                                                      |       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|
| VDE Gutachten mit Fertigungsüberwachung  <a href="http://www.vde.de">http://www.vde.de</a> 40042258 |       |
|                                                                                                                                                                                      |       |
| Nominal current I <sub>N</sub>                                                                                                                                                       | 6 A   |
| Nominal voltage U <sub>N</sub>                                                                                                                                                       | 160 V |

|                                                                                                                                                                            |       |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|
| IECEE CB Scheme  <a href="http://www.iecee.org/">http://www.iecee.org/</a> DE1-55663-B1 |       |
|                                                                                                                                                                            |       |
| Nominal current I <sub>N</sub>                                                                                                                                             | 6 A   |
| Nominal voltage U <sub>N</sub>                                                                                                                                             | 160 V |

|             |
|-------------|
| EAC B.01742 |
|-------------|

### Accessories

#### Accessories

##### Labeled terminal marker

Marker card - SK 2,54/2,8:FORTL.ZAHLEN - 0804853



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 99, Mounting type: Adhesive, for terminal block width: 2.54 mm, Lettering field: 2.54 x 2.8 mm

## Printed-circuit board connector - MCV 0,5/ 3-G-2,54 SMD R24 - 1821559

### Accessories

Sample set - SAMPLE MCV 0,5/ 3-G-2,54 SMD - 1835875



Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: SMD soldering

---

### Additional products

Printed-circuit board connector - FMC 0,5/ 3-ST-2,54 - 1821106



Plug component, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 3, Pitch: 2.54 mm, Connection method: Push-in spring connection, Color: black, Contact surface: Gold