


AC POWER BUS VOLTAGE SUPPRESSOR**PHP & PIP PACKAGE****DESCRIPTION**

The PHP and PIP Series of devices are designed in accordance with DOD-STD-1399, section 300 interface standard and MIL-STD704A for shipboard systems, electrical power and alternating current. When large voltage transients endanger voltage sensitive components, this series provides reliable protection against power interruptions and shore power switch-over.

This series can be screened upon request for military requirements in accordance with MIL-PRF-19500 (applicable tests).

FEATURES

- DOD-STD-1399, MIL-STD-704, MIL-STD-2036 & MIL-PRF-19500/507 Compliant
- 7,500 & 15,000 kilowatts Peak Pulse Power per Line ($t_p = 10/1000\mu s$)
- Each Device 100% Tested
- Available in Multiple Voltages

APPLICATIONS

- Secondary AC Power Supply
- Aircraft & Shipboard AC Power Bus
- Heavy Duty AC Switching Power

MECHANICAL CHARACTERISTICS

- PHP: Hermetically Sealed Glass to Metal Sub-Assemblies
- PIP: Molded Epoxy Case Sub-Assemblies
- Approximate Weight: 46 grams
- Flammability Rating UL 94V-0
- Screening Available Upon Request:
 - H1 - Submodule Screening (Test Plans 05231 & 05232)
 - H2 - Submodule & Module Screening (Test Plan 05233)
 - H3 - Submodule & Module Screening with Group B & C Lot Testing (Test Plans 05234 & 05235)

TYPICAL DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified

PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power (tp = 10/1000µs) - See Figure 1	P _{PP}	7.5 & 15	kilowatts
Operating Temperature	T _L	-55 to 150	°C
Storage Temperature	T _{STG}	-55 to 150	°C
Steady State Power Dissipation @ 50°C	T _A	7.5	Watts

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified

PART NUMBER	AVERAGE RMS VOLTAGE V _{RMS} VOLTS	RATED STAND-OFF VOLTAGE V _{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE (Note 1) @1mA V _(BR) VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @ I _{PPM} V _C VOLTS	MAXIMUM LEAKAGE CURRENT @V _{WM} I _D µA	MAXIMUM PEAK PULSE CURRENT I _{PPM} AMPS	MAXIMUM PEAK PULSE POWER @ 1ms P _{PP} KILOWATTS
PHP8.4	8.4	12.0	14	22	250	341	7.5
PIP8.4	8.4	12.0	14	22	250	341	7.5
PHP24	24.0	34.0	40	67	250	112	7.5
PIP24	24.0	34.0	40	67	250	112	7.5
PHP30	30.0	42.5	50	84	250	90	7.5
PIP30	30.0	42.5	50	84	250	90	7.5
PHP60	60.0	85.0	100	167	250	90	15
PIP60	60.0	85.0	100	167	250	90	15
PHP120*	120.0	170.0	200	319	250	47	15
PIP120*	120.0	170.0	200	319	250	47	15
PHP208	208.0	295.0	347	536	250	28	15
PIP208	208.0	295.0	347	536	250	28	15
PHP250*	250.0	354.0	418	652	250	23	15
PIP250*	250.0	354.0	418	652	250	23	15
PHP275	275.0	390.0	460	710	250	21	15
PHP440	440.0	623.0	735	1138	250	13.2	15
PIP440	440.0	623.0	735	1138	250	13.2	15
PHP500*	500.0	708.0	835	1292	250	11.6	15
PIP500*	500.0	708.0	835	1292	250	11.6	15

NOTE

1. A * indicates that this series is recommended for marine applications. For military and aerospace applications, use the PHP Series, for industrial applications, use the PIP Series.
2. The following voltages have a peak pulse power rating of 7,500 Watts for an 10/1000µs waveshape (see Figure 1): 8.4V, 24V and 30V.

TYPICAL DEVICE CHARACTERISTICS

FIGURE 1
PEAK PULSE POWER VS PULSE TIME




FIGURE 2
PULSE WAVEFORM






FIGURE 3
POWER DERATING CURVE



PACKAGE INFORMATION

OUTLINE DIMENSIONS				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	56.38	57.91	2.22	2.28
B	49.02	50.03	1.93	1.97
C	3.43	4.17	0.135	0.165
D	20.32		0.800	
E	8.26	9.27	0.325	0.365
F	3.18 DIA.		0.125 DIA.	
G	16.76	18.29	0.660	0.720
H	34.16	35.69	1.345	1.405
I	6.35		0.250	
J	11.94	13.46	0.47	0.53
NOTES 1. Dimensions "D", "F" and "I" are nominal.				



ORDERING INFORMATION			
BASE PART NUMBER (xx = Voltage)	SUBMODULE SCREENING	SUBMODULE & MODULE SCREENING	SUBMODULE & MODULE SCREENING, GROUP B & C LOT TESTING
PHPxxx	H1	H2	H3
PIPxxx	H1	H2	H2
NOTES 1. Marking on Part - logo, date code and part number.			
Package outline per document number 06032.R1 9/09			

COMPANY INFORMATION

COMPANY PROFILE

In business more than 20 years, ProTek Devices™ is a privately held semiconductor company. The company offers a product line of overvoltage protection and overcurrent protection components. These include transient voltage suppressor array (TVS arrays) avalanche breakdown diode, steering diode TVS array and electronics SMD chip fuses. These components deliver circuit protection in electronic systems from numerous overvoltage and overcurrent events. They include lightning; electrostatic discharge (ESD); nuclear electromagnetic pulses (NEMP); inductive switching; and electromagnetic interference (EMI) / radio frequency interference (RFI). ProTek Devices also offers high performance interface and linear products. They include analog switches; multiplexers; LED drivers; LED wafer die for ESD protection; audio control ICs; RF and related high frequency products.

CONTACT US

Corporate Headquarters

2929 South Fair Lane
Tempe, Arizona 85282
USA

By Telephone

General: 602-431-8101
Sales: & Marketing: 602-414-5109
Customer Service: 602-414-5114
Product Technical Support: 602-414-5107

By Fax

General: 602-431-2288

By E-mail:

Asia Sales: asiasales@protekdevices.com
Europe Sales: europesales@protekdevices.com
U.S. Sales: ussales@protekdevices.com
Distributor Sales: distysales@protekdevices.com
Customer Service: service@protekdevices.com
Technical Support: support@protekdevices.com

ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19
Zervex
Singapore - 408538
Tel: +65-67488312
Fax: +65-67488313

Web

www.protekdevices.com

COPYRIGHT © ProTek Devices 1998 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice.

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.