

CAT. NO. & DIMENSIONS

RIGHT ANGLE TYPE		STRAIGHT TYPE		DIMENSIONS (NOTE1)
NOTE 2	CAT. NO.	NOTE 2	CAT. NO.	A±0.3
	SLD 4 R-1/2LF		SLD 4 S-1/2LF	12.75
	SLD 5 R-1/2LF		SLD 5 S-1/2LF	14.00
	SLD 6 R-1/2LF		SLD 6 S-1/2LF	15.25
	SLD 7 R-1/2LF		SLD 7 S-1/2LF	16.50
	SLD 8 R-1/2LF		SLD 8 S-1/2LF	17.75
	SLD 9 R-1/2LF		SLD 9 S-1/2LF	19.00
	SLD 10 R-1/2LF		SLD 10 S-1/2LF	20.25
	SLD 11 R-1/2LF		SLD 11 S-1/2LF	21.50
	SLD 12 R-1/2LF		SLD 12 S-1/2LF	22.75
	SLD 13 R-1/2LF		SLD 13 S-1/2LF	24.00
	SLD 14 R-1/2LF		SLD 14 S-1/2LF	25.25
	SLD 15 R-1/2LF		SLD 15 S-1/2LF	26.50
	SLD 16 R-1/2LF		SLD 16 S-1/2LF	27.75
	SLD 17 R-1/2LF	*	SLD 17 S-1/2LF	29.00
	SLD 18 R-1/2LF		SLD 18 S-1/2LF	30.25
	SLD 19 R-1/2LF		SLD 19 S-1/2LF	31.50
	SLD 20 R-1/2LF		SLD 20 S-1/2LF	32.75
	SLD 21 R-1/2LF	*	SLD 21 S-1/2LF	34.00
	SLD 22 R-1/2LF		SLD 22 S-1/2LF	35.25
	SLD 23 R-1/2LF		SLD 23 S-1/2LF	36.50
	SLD 24 R-1/2LF		SLD 24 S-1/2LF	37.75
	SLD 25 R-1/2LF	*	SLD 25 S-1/2LF	39.00
	SLD 26 R-1/2LF		SLD 26 S-1/2LF	40.25
	SLD 27 R-1/2LF		SLD 27 S-1/2LF	41.50
	SLD 28 R-1/2LF		SLD 28 S-1/2LF	42.75
	SLD 29 R-1/2LF		SLD 29 S-1/2LF	44.00
	SLD 30 R-1/2LF		SLD 30 S-1/2LF	45.25
	SLD 31 R-1/2LF		SLD 31 S-1/2LF	46.50
	SLD 32 R-1/2LF		SLD 32 S-1/2LF	47.75
	SLD 33 R-1/2LF		SLD 33 S-1/2LF	49.00
	SLD 34 R-1/2LF		SLD 34 S-1/2LF	50.25
	SLD 35 R-1/2LF		SLD 35 S-1/2LF	51.50
	SLD 36 R-1/2LF		SLD 36 S-1/2LF	52.75
	SLD 37 R-1/2LF		SLD 37 S-1/2LF	54.00
	SLD 38 R-1/2LF	*	SLD 38 S-1/2LF	55.25
	SLD 39 R-1/2LF		SLD 39 S-1/2LF	56.50
	SLD 40 R-1/2LF		SLD 40 S-1/2LF	57.75

CAT. NO.

SERIES NAME

NO. OF CONTACTS

R:RIGHT ANGLE TYPE

S:STRAIGHT TYPE

VARIATION

1:KINKED TERMINAL


2:STRAIGHT TERMINAL



LEAD FREE

NOTE.

1. SEE PART DRAWINGS FOR DIMENSIONS A.

2. PLEASE CONSULT US IN CASE OF USING PARTS WITH *MARK

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family 58KF		CODE JP	
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm		title CAT. NO. TABLE FOR 1.25mm SPACING CONNECTOR (Cat. No. SLD__R/S-1/2LF)			
A	J05-0435	H.T	6/22/'05	angles		linear		scale $\propto$		dwg no JSA 96548 type Product Customer Drawing			
B	J06-0503	H.T	11/28/'06										
				dr	11/28/06		FCI		sheet 1 of 1		size		
				engr	11/28/06				A4				
				chr	11/28/06								
				appd	11/28/06								
sheet index		revision		B							Rev.		
sheet		1								B			




1. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
2. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm THICK CIRCUIT BOARD.

PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	PBT RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BLACK
2	SLIDER		1	
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : Sn Ni UNDER PLATED (LEAD FREE)

n : NO. OF CONTACTS

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection mm		product family 58KF		CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified		angles		linear		title 1.25mm SPACING FPC/FFC CONNECTOR (Cat. No. SLD__R-1LF)		
A	J05-0435	H.T	7/8/'05									
B	J05-0733	H.T	10/28/'05									
C	J06-0503	H.T	11/28/'06									
				dr	11/28/06				dwg no		sheet 1 of 1	size
				enr	11/28/06				JSA 96549			A4
				chr	11/28/06				type		Product Customer Drawing	
				appd	11/28/06							
sheet index	revision	C										Rev.
	sheet	1										C



1. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

2. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm THICK CIRCUIT BOARD.


PT. NO.	PARTS NAME	MATERIAL	Q'TY	NOTE
1	HOUSING	PBT RESIN GLASS REINFORCED (UL94V-0)	1	COLOR : BLACK
2	SLIDER		1	
3	CONTACT	PHOSPHOR BRONZE	n	PLATING : Sn Ni UNDER PLATED (LEAD FREE)

n : NO. OF CONTACTS

mat'l. code				surface 58 / tolerance ISO 1302 V ISO 406 ISO 1101	projection	product family 58KF	CODE JP
ltr	ecn no	dr	date	tolerances unless otherwise specified		title 1.25mm SPACING FPC/FFC CONNECTOR (Cat. No. SLD__S-1LF)	
A	J05-0435	H.T	7/8/'05	angles linear ±0.3	mm		
B	J05-0733	H.T	10/28/'05				
C	J06-0503	H.T	11/28/'06		scale X	dwg no JSA 96550	sheet 1 of 1 size A4
				dr <i>K. Shouji</i> 11/28/06		type Product Customer Drawing	
				engr <i>K. Shouji</i> 11/28/06			
				chr <i>K. Shouji</i> 11/28/06			
				appd <i>S. Duda</i> 11/28/06			

sheet index	revision C	sheet 1	SC-SLD02 form: A4	JSA96548	96549	91823	1	2	Rev. C
-------------	------------	---------	-------------------	----------	-------	-------	---	---	--------

RECOMMENDED CABLE (FPC,FFC)



NOTES


1. SURFACE TREATMENT OF CONDUCTOR PORTIONS MUST BE TIN PLATED OR SOLDER PLATED WITH MORE THAN $1\mu\text{m}$ THICKNESS.
2. NO BURR AT EACH PORTION.
3. NO PEELING IN COMMON USE.

TYPE	DIMENSIONAL TOLERANCE	
	a	b
FPC	± 0.05	± 0.1
FFC	± 0.1	± 0.03

RECOMMENDED PC BOARD

THICKNESS : 0.9-2.0

HOLE PATTERN (COMPONENT SIDE)



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⊕		product family 58KF			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title RECOMMENDED PC BOARD AND CABLE (Cat. No. SLD_R/S-1/2_)			
1		H.T	9/9/98										
A	J06-0503	H.T	11/28/06	angles	linear					scale X			
				dr	11/28/06		FCI		dwg no		sheet 1 of 1	size	
				enr	11/28/06				JSA 91823		A4		
				chr	11/28/06								
				appd	11/28/06								
sheet index	revision sheet	A	1										