


# Surface Mount TRANSZORB® Transient Voltage Suppressors


**SMB (DO-214AA)**


**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
Available

## FEATURES

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- Available in unidirectional and bidirectional
- 600 W peak pulse power capability with a 10/1000  $\mu$ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available  
- Automotive ordering code: base P/NHE3 or P/NHM3
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

## TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, and telecommunication.

## MECHANICAL DATA

### Case: SMB (DO-214AA)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-E3 - RoHS-compliant, commercial grade

Base P/N-M3 - halogen-free, RoHS-compliant, commercial grade

Base P/NHE3\_X - RoHS-compliant and AEC-Q101 qualified

Base P/NHM3\_X - halogen-free, RoHS-compliant, and AEC-Q101 qualified

("\_X" denotes revision code e.g. A, B, ...)

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3, M3, HE3, and HM3 suffix meets JESD 201 class 2 whisker test

**Polarity:** for unidirectional types the band denotes cathode end, no marking on bidirectional types

## PRIMARY CHARACTERISTICS

|                                 |                               |
|---------------------------------|-------------------------------|
| $V_{WM}$ (unidirectional)       | 5.8 V to 459 V                |
| $V_{WM}$ (bidirectional)        | 5.8 V to 185 V                |
| $V_{BR}$ (unidirectional)       | 6.8 V to 540 V                |
| $V_{BR}$ (bidirectional)        | 6.8 V to 220 V                |
| $P_{PPM}$                       | 600 W                         |
| $P_D$                           | 5.0 W                         |
| $I_{FSM}$ (unidirectional only) | 100 A                         |
| $T_J$ max.                      | 150 °C                        |
| Polarity                        | Unidirectional, bidirectional |
| Package                         | SMB (DO-214AA)                |

## DEVICES FOR BIDIRECTION APPLICATIONS

For bidirectional devices use CA suffix (e.g. P6SMB10CA).

Electrical characteristics apply in both directions.

## MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)

| PARAMETER                                                                                  | SYMBOL         | VALUE          | UNIT |
|--------------------------------------------------------------------------------------------|----------------|----------------|------|
| Peak power dissipation with a 10/1000 $\mu$ s waveform <sup>(1)(2)</sup> (fig. 1)          | $P_{PPM}$      | 600            | W    |
| Peak pulse current with a 10/1000 $\mu$ s waveform <sup>(1)</sup>                          | $I_{PPM}$      | See next table | A    |
| Power dissipation on infinite heatsink at $T_A = 50$ °C                                    | $P_D$          | 5.0            | W    |
| Peak forward surge current 8.3 ms single half sine-wave unidirectional only <sup>(2)</sup> | $I_{FSM}$      | 100            | A    |
| Operating junction and storage temperature range                                           | $T_J, T_{STG}$ | -65 to +150    | °C   |

### Notes

<sup>(1)</sup> Non-repetitive current pulse, per fig. 3 and derated above  $T_A = 25$  °C per fig. 2

<sup>(2)</sup> Mounted on 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PART NUMBER | DEVICE MARKING CODE |      | BREAKDOWN VOLTAGE $V_{BR}$ AT $I_T$ <sup>(1)</sup> (V) |      | TEST CURRENT $I_T$ (mA) | STAND-OFF VOLTAGE $V_{WM}$ (V) | MAXIMUM REVERSE LEAKAGE AT $V_{WM}$ $I_D$ <sup>(3)</sup> ( $\mu\text{A}$ ) | MAXIMUM PEAK PULSE CURRENT $I_{PPM}$ <sup>(2)</sup> (A) | MAXIMUM CLAMPING VOLTAGE AT $I_{PPM}$ $V_C$ (V) | MAXIMUM TEMPERATURE COEFFICIENT OF $V_{BR}$ ( $\%/^{\circ}\text{C}$ ) |
|-------------|---------------------|------|--------------------------------------------------------|------|-------------------------|--------------------------------|----------------------------------------------------------------------------|---------------------------------------------------------|-------------------------------------------------|-----------------------------------------------------------------------|
|             | UNI                 | BI   | MIN.                                                   | MAX. |                         |                                |                                                                            |                                                         |                                                 |                                                                       |
| P6SMB6.8A   | 6V8A                | 6V8C | 6.45                                                   | 7.14 | 10                      | 5.80                           | 1000                                                                       | 57.1                                                    | 10.5                                            | 0.057                                                                 |
| P6SMB7.5A   | 7V5A                | 7V5C | 7.13                                                   | 7.88 | 10                      | 6.40                           | 500                                                                        | 53.1                                                    | 11.3                                            | 0.061                                                                 |
| P6SMB8.2A   | 8V2A                | 8V2C | 7.79                                                   | 8.61 | 10                      | 7.02                           | 200                                                                        | 49.6                                                    | 12.1                                            | 0.065                                                                 |
| P6SMB9.1A   | 9V1A                | 9V1C | 8.65                                                   | 9.55 | 1.0                     | 7.78                           | 50                                                                         | 44.8                                                    | 13.4                                            | 0.068                                                                 |
| P6SMB10A    | 10A                 | 10C  | 9.50                                                   | 10.5 | 1.0                     | 8.55                           | 10                                                                         | 41.4                                                    | 14.5                                            | 0.073                                                                 |
| P6SMB11A    | 11A                 | 11C  | 10.5                                                   | 11.6 | 1.0                     | 9.40                           | 5.0                                                                        | 38.5                                                    | 15.6                                            | 0.075                                                                 |
| P6SMB12A    | 12A                 | 12C  | 11.4                                                   | 12.6 | 1.0                     | 10.2                           | 5.0                                                                        | 35.9                                                    | 16.7                                            | 0.078                                                                 |
| P6SMB13A    | 13A                 | 13C  | 12.4                                                   | 13.7 | 1.0                     | 11.1                           | 5.0                                                                        | 33.0                                                    | 18.2                                            | 0.081                                                                 |
| P6SMB15A    | 15A                 | 15C  | 14.3                                                   | 15.8 | 1.0                     | 12.8                           | 1.0                                                                        | 28.3                                                    | 21.2                                            | 0.084                                                                 |
| P6SMB16A    | 16A                 | 16C  | 15.2                                                   | 16.8 | 1.0                     | 13.6                           | 1.0                                                                        | 26.7                                                    | 22.5                                            | 0.086                                                                 |
| P6SMB18A    | 18A                 | 18C  | 17.1                                                   | 18.9 | 1.0                     | 15.3                           | 1.0                                                                        | 23.8                                                    | 25.2                                            | 0.088                                                                 |
| P6SMB20A    | 20A                 | 20C  | 19.0                                                   | 21.0 | 1.0                     | 17.1                           | 1.0                                                                        | 21.7                                                    | 27.7                                            | 0.090                                                                 |
| P6SMB22A    | 22A                 | 22C  | 20.9                                                   | 23.1 | 1.0                     | 18.8                           | 1.0                                                                        | 19.6                                                    | 30.6                                            | 0.092                                                                 |
| P6SMB24A    | 24A                 | 24C  | 22.8                                                   | 25.2 | 1.0                     | 20.5                           | 1.0                                                                        | 18.1                                                    | 33.2                                            | 0.094                                                                 |
| P6SMB27A    | 27A                 | 27C  | 25.7                                                   | 28.4 | 1.0                     | 23.1                           | 1.0                                                                        | 16.0                                                    | 37.5                                            | 0.096                                                                 |
| P6SMB30A    | 30A                 | 30C  | 28.5                                                   | 31.5 | 1.0                     | 25.6                           | 1.0                                                                        | 14.5                                                    | 41.4                                            | 0.097                                                                 |
| P6SMB33A    | 33A                 | 33C  | 31.4                                                   | 34.7 | 1.0                     | 28.2                           | 1.0                                                                        | 13.1                                                    | 45.7                                            | 0.098                                                                 |
| P6SMB36A    | 36A                 | 36C  | 34.2                                                   | 37.8 | 1.0                     | 30.8                           | 1.0                                                                        | 12.0                                                    | 49.9                                            | 0.099                                                                 |
| P6SMB39A    | 39A                 | 39C  | 37.1                                                   | 41.0 | 1.0                     | 33.3                           | 1.0                                                                        | 11.1                                                    | 53.9                                            | 0.100                                                                 |
| P6SMB43A    | 43A                 | 43C  | 40.9                                                   | 45.2 | 1.0                     | 36.8                           | 1.0                                                                        | 10.1                                                    | 59.3                                            | 0.101                                                                 |
| P6SMB47A    | 47A                 | 47C  | 44.7                                                   | 49.4 | 1.0                     | 40.2                           | 1.0                                                                        | 9.3                                                     | 64.8                                            | 0.101                                                                 |
| P6SMB51A    | 51A                 | 51C  | 48.5                                                   | 53.6 | 1.0                     | 43.6                           | 1.0                                                                        | 8.6                                                     | 70.1                                            | 0.102                                                                 |
| P6SMB56A    | 56A                 | 56C  | 53.2                                                   | 58.8 | 1.0                     | 47.8                           | 1.0                                                                        | 7.8                                                     | 77.0                                            | 0.103                                                                 |
| P6SMB62A    | 62A                 | 62C  | 58.9                                                   | 65.1 | 1.0                     | 53.0                           | 1.0                                                                        | 7.1                                                     | 85.0                                            | 0.104                                                                 |
| P6SMB68A    | 68A                 | 68C  | 64.6                                                   | 71.4 | 1.0                     | 58.1                           | 1.0                                                                        | 6.5                                                     | 92.0                                            | 0.104                                                                 |
| P6SMB75A    | 75A                 | 75C  | 71.3                                                   | 78.8 | 1.0                     | 64.1                           | 1.0                                                                        | 5.8                                                     | 103                                             | 0.105                                                                 |
| P6SMB82A    | 82A                 | 82C  | 77.9                                                   | 86.1 | 1.0                     | 70.1                           | 1.0                                                                        | 5.3                                                     | 113                                             | 0.105                                                                 |
| P6SMB91A    | 91A                 | 91C  | 86.5                                                   | 95.5 | 1.0                     | 77.8                           | 1.0                                                                        | 4.8                                                     | 125                                             | 0.106                                                                 |
| P6SMB100A   | 100A                | 100C | 95.0                                                   | 105  | 1.0                     | 85.5                           | 1.0                                                                        | 4.4                                                     | 137                                             | 0.106                                                                 |
| P6SMB110A   | 110A                | 110C | 105                                                    | 116  | 1.0                     | 94.0                           | 1.0                                                                        | 3.9                                                     | 152                                             | 0.107                                                                 |
| P6SMB120A   | 120A                | 120C | 114                                                    | 126  | 1.0                     | 102                            | 1.0                                                                        | 3.6                                                     | 165                                             | 0.107                                                                 |
| P6SMB130A   | 130A                | 130C | 124                                                    | 137  | 1.0                     | 111                            | 1.0                                                                        | 3.4                                                     | 179                                             | 0.107                                                                 |
| P6SMB150A   | 150A                | 150C | 143                                                    | 158  | 1.0                     | 128                            | 1.0                                                                        | 2.9                                                     | 207                                             | 0.108                                                                 |
| P6SMB160A   | 160A                | 160C | 152                                                    | 168  | 1.0                     | 136                            | 1.0                                                                        | 2.7                                                     | 219                                             | 0.108                                                                 |
| P6SMB170A   | 170A                | 170C | 162                                                    | 179  | 1.0                     | 145                            | 1.0                                                                        | 2.6                                                     | 234                                             | 0.108                                                                 |
| P6SMB180A   | 180A                | 180C | 171                                                    | 189  | 1.0                     | 154                            | 1.0                                                                        | 2.4                                                     | 246                                             | 0.108                                                                 |
| P6SMB200A   | 200A                | 200C | 190                                                    | 210  | 1.0                     | 171                            | 1.0                                                                        | 2.2                                                     | 274                                             | 0.108                                                                 |
| P6SMB220A   | 220A                | 220C | 209                                                    | 231  | 1.0                     | 185                            | 1.0                                                                        | 1.8                                                     | 328                                             | 0.108                                                                 |
| P6SMB250A   | 250A                | -    | 237                                                    | 263  | 1.0                     | 214                            | 1.0                                                                        | 1.74                                                    | 344                                             | 0.110                                                                 |
| P6SMB300A   | 300A                | -    | 285                                                    | 315  | 1.0                     | 256                            | 1.0                                                                        | 1.45                                                    | 414                                             | 0.110                                                                 |
| P6SMB350A   | 350A                | -    | 333                                                    | 368  | 1.0                     | 300                            | 1.0                                                                        | 1.24                                                    | 482                                             | 0.110                                                                 |
| P6SMB400A   | 400A                | -    | 380                                                    | 420  | 1.0                     | 342                            | 1.0                                                                        | 1.10                                                    | 548                                             | 0.110                                                                 |
| P6SMB440A   | 440A                | -    | 418                                                    | 462  | 1.0                     | 376                            | 1.0                                                                        | 1.00                                                    | 602                                             | 0.110                                                                 |
| P6SMB480A   | 480A                | -    | 456                                                    | 504  | 1.0                     | 408                            | 1.0                                                                        | 0.91                                                    | 658                                             | 0.110                                                                 |
| P6SMB510A   | 510A                | -    | 485                                                    | 535  | 1.0                     | 434                            | 1.0                                                                        | 0.86                                                    | 698                                             | 0.110                                                                 |
| P6SMB540A   | 540A                | -    | 513                                                    | 567  | 1.0                     | 459                            | 1.0                                                                        | 0.81                                                    | 740                                             | 0.110                                                                 |

**Notes**

- (1) Pulse test:  $t_p \leq 50\text{ ms}$   
(2) Surge current waveform per fig. 3 and derate per fig. 2  
(3) For bi-directional types with  $V_{WM}$  of 10 V and less, the  $I_D$  limit is doubled  
(4) All terms and symbols are consistent with ANSI/IEEE CA62.35  
(5)  $V_F = 3.5\text{ V}$  at  $I_F = 50\text{ A}$  (uni-directional only)

**THERMAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

| PARAMETER                                                          | SYMBOL          | VALUE | UNIT                 |
|--------------------------------------------------------------------|-----------------|-------|----------------------|
| Typical thermal resistance, junction to ambient air <sup>(1)</sup> | $R_{\theta JA}$ | 100   | $^{\circ}\text{C/W}$ |
| Typical thermal resistance, junction to lead                       | $R_{\theta JL}$ | 20    |                      |

**Note**
<sup>(1)</sup> Mounted on minimum recommended pad layout

**ORDERING INFORMATION** (Example)

| PREFERRED P/N                   | UNIT WEIGHT (g) | VOLTAGE RANGE (V) |            | PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                      |
|---------------------------------|-----------------|-------------------|------------|--------------|---------------|------------------------------------|
|                                 |                 | UNI               | BI         |              |               |                                    |
| P6SMB6.8A-E3/52                 | 0.096           | 6.8 to 220        | 6.8 to 220 | 52           | 750           | 7" diameter plastic tape and reel  |
| P6SMB6.8A-M3/52                 | 0.096           | 6.8 to 540        | 6.8 to 220 | 52           | 750           | 7" diameter plastic tape and reel  |
| P6SMB6.8A-E3/5B                 | 0.096           | 6.8 to 220        | 6.8 to 220 | 5B           | 3200          | 13" diameter plastic tape and reel |
| P6SMB6.8A-M3/5B                 | 0.096           | 6.8 to 540        | 6.8 to 220 | 5B           | 3200          | 13" diameter plastic tape and reel |
| P6SMB6.8AHE3_A/H <sup>(1)</sup> | 0.096           | 6.8 to 220        | 6.8 to 220 | H            | 750           | 7" diameter plastic tape and reel  |
| P6SMB6.8AHM3_A/H <sup>(1)</sup> |                 |                   |            |              |               |                                    |
| P6SMB6.8AHE3_A/I <sup>(1)</sup> | 0.096           | 6.8 to 220        | 6.8 to 220 | I            | 3200          | 13" diameter plastic tape and reel |
| P6SMB6.8AHM3_A/I <sup>(1)</sup> |                 |                   |            |              |               |                                    |
| P6SMB250AHM3_C/H <sup>(2)</sup> | 0.096           | 250 to 540        | -          | H            | 750           | 7" diameter plastic tape and reel  |
| P6SMB250AHM3_C/I <sup>(2)</sup> | 0.096           | 250 to 540        | -          | I            | 3200          | 13" diameter plastic tape and reel |

**Notes**
<sup>(1)</sup> \_A is available for P6SMB6.8(C)A to P6SMB220(C)A, AEC-Q101 qualified

<sup>(2)</sup> \_C is available for P6SMB250A to P6SMB540A, AEC-Q101 qualified


**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)


Fig. 1 - Peak Pulse Power Rating Curve




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 3 - Pulse Waveform




Fig. 5 - Typical Transient Thermal Impedance




Fig. 4 - Typical Junction Capacitance






Fig. 6 - Maximum Non-Repetitive Peak Forward Surge Current

**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)




## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.