




DIMENSIONS



TERMINATION



TIN LEAD PART NUMBER

PART NUMBER

86093967113H45105E1


LEAD FREE PART NUMBER

PART NUMBER

86093967113H45ADLF

P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000



SPECIFICATION 105 = 2 grounding pins in position :
OR SPECIFICATION AD= row : a cavity : 1-32

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size A3		Scale 1.5
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR	LINEAR	0.X ±0.1	size A3		Scale 1.5
0.XX ±0.1			0.XXX ±0.1		ECN L506-0095		Spec ref -	
Dr	ROUILLARD	2001/02/06	Product family		DIN 8609		Rev.	
Eng	TARON	2001/02/06	title		STANDARD MALE 3 ROW		C	
Chr	LEGARE	2001/02/06	96 CONTACTS		C-8609-0934		sheet 1 of 1	
Appr	LEGARE	2001/02/06	catalog no		CUSTOMER			

rev	ecn no	dr	date
A	-	-	2001/02/06
B	LS05-001	JTA	2005/03/05
C	LS06-0095	LGO	2006/06/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17