

# 2 TOGGLE SWITCHES

## General Purpose Toggle Switches — AC Rated

### DESCRIPTION

These ac rated toggle switches offer the widest selection of features and the design flexibility to meet a variety of applications.

### Combi-Term Option

This is an extension of our ac rated General Purpose Toggle Switch. The "Combi-Term" design allows the user the option of Screw Terminals, .250" Quick Connects or Solder Termination all on the same switch. The special clips and screws are provided in a poly bag with the switch.

### SPECIFICATIONS

#### Rating:

See selection table.

#### Circuits:

1PST, 1PDT, 2PST, 2PDT, 3PST, 3PDT, 4PST & 4PDT.

Maintained and momentary.

#### Contact Mechanism:

Slow-make/Slow-brake butt contact.

### Terminal Types:

Screw Terminals — Brass designed to accept #6-32 x 3/16 binding head (Cat. No. 811-2) screws. Furnished unassembled.

Solder Lug Terminals — Tintillate plated brass.

Spade Terminals — Brass.

Combi-Term — Brass.

**STANDARD AC RATED TOGGLES SELECTION TABLE** (BOLD FACE TYPE INDICATES ITEMS NORMALLY IN DISTRIBUTOR STOCK)

| Rating                                                                  | Poles and Throw | Circuit with Toggle in                                                                               |                                                                                                          |                                                                                                                    | BASE CIRCUIT<br>SEE<br>PAGE 4.28 | Bushing Length<br>A mm (inches) | Lever Length<br>B mm (inches) | CATALOG NUMBERS                               |                                                      |                                   |                |
|-------------------------------------------------------------------------|-----------------|------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|----------------------------------|---------------------------------|-------------------------------|-----------------------------------------------|------------------------------------------------------|-----------------------------------|----------------|
|                                                                         |                 | UP<br>Position<br> | CENTER<br>Position<br> | DOWN<br>Position<br><br>(Keyway) |                                  |                                 |                               | Solder<br>Lugs                                | Screw<br>Terminals                                   | .250" Spade<br>Terminals          | Combi-Term     |
| ONE POLE                                                                |                 |                                                                                                      |                                                                                                          |                                                                                                                    |                                  |                                 |                               |                                               |                                                      |                                   |                |
| 6A, 125V ac<br>3A, 250V ac                                              | 1 P.S.T.        | ON                                                                                                   | NONE                                                                                                     | OFF                                                                                                                | A                                | 8.74 (.344)<br>11.91 (.469)     | 14.30 (.563)<br>14.30 (.563)  | <b>7580K7</b><br><b>7580K6</b>                | 7580K5<br><b>7580K4</b>                              | <b>7580K9</b><br><b>7580K8</b>    | N/A            |
|                                                                         | 1 P.D.T.        | ON                                                                                                   | OFF                                                                                                      | ON                                                                                                                 | B                                | 11.91 (.469)                    | 14.30 (.563)                  | 7581K6                                        | <b>7581K4</b>                                        | 7581K8                            |                |
|                                                                         | 1 P.D.T.        | ON                                                                                                   | NONE                                                                                                     | ON                                                                                                                 | B                                | 11.91 (.469)                    | 14.30 (.563)                  | <b>7582K6</b>                                 | <b>7582K4</b>                                        | 7582K8                            |                |
|                                                                         | 1 P.D.T.        | ON<br>ON*                                                                                            | NONE<br>OFF                                                                                              | ON*<br>ON*                                                                                                         | B                                | 11.91 (.469)                    | 14.30 (.563)                  | 7585K6<br>7587K6                              | 7585K4<br>7587K4                                     | 7585K8<br>7587K8                  |                |
| 10A, 250V ac<br>1/2 Hp, 250V ac                                         | 1 P.S.T.        | OFF                                                                                                  | NONE                                                                                                     | ON*                                                                                                                | A                                | 11.91 (.469)                    | 14.30 (.563)                  | 7506K3                                        | <b>7506K4</b>                                        | 7506K6                            |                |
|                                                                         | 1 P.S.T.        | OFF                                                                                                  | NONE                                                                                                     | ON*                                                                                                                | A                                | 11.91 (.469)                    | 17.48 (.688)                  | 7506K38                                       | 7506K36                                              | 7506K40                           |                |
|                                                                         | 1 P.D.T.        | ON*<br>ON                                                                                            | OFF<br>NONE                                                                                              | ON*<br>ON*                                                                                                         | B                                | 11.91 (.469)                    | 14.30 (.563)                  | 7509K4<br>7510K6                              | <b>7509K5</b><br>7510K7                              | 7509K7<br>7510K9                  |                |
|                                                                         | 1 P.D.T.        | ON<br>ON*                                                                                            | OFF<br>OFF                                                                                               | ON*<br>ON*                                                                                                         | B                                | 11.91 (.469)                    | 17.48 (.688)                  | 7508K38<br>7509K38                            | 7508K36<br>7509K36                                   | 7508K40<br>7509K40                |                |
| 15A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac<br>1/2 Hp, 125V-250V ac | 1 P.S.T.        | ON                                                                                                   | NONE                                                                                                     | OFF                                                                                                                | A                                | 8.74 (.344)<br>11.91 (.469)     | 14.30 (.563)<br>14.30 (.563)  | 7501K12<br><b>7501K13</b>                     | 7500K13 ②<br><b>7500K14 ②</b>                        | 7501K14<br><b>7501K15</b>         |                |
| 15A, 125V ac<br>10A, 250V ac<br>1/2 Hp, 125V ac<br>3/4 Hp, 250V ac      | 1 P.D.T.        | ON                                                                                                   | OFF                                                                                                      | ON                                                                                                                 | B                                | 11.91 (.469)                    | 14.30 (.563)                  | <b>7503K13 ②</b>                              | <b>7502K13</b>                                       | <b>7503K15</b>                    |                |
|                                                                         | 1 P.D.T.        | ON                                                                                                   | NONE                                                                                                     | ON                                                                                                                 | B                                | 11.91 (.469)                    | 14.30 (.563)                  | <b>7505K4</b>                                 | <b>7504K4 ②</b>                                      | <b>7505K6</b>                     |                |
| 20A, 125V ac<br>10A, 250V ac<br>1/2 Hp, 125V ac<br>3/4 Hp, 250V ac      | 1 P.S.T.        | ON                                                                                                   | NONE                                                                                                     | OFF                                                                                                                | A                                | 11.91 (.469)                    | 17.48 (.688)                  | 7546K38                                       | 7546K36                                              | 7546K40                           |                |
| 20A, 125V AC<br>10A, 250V AC<br>1 Hp, 120-240V ac                       | 1 P.S.T.        | ON                                                                                                   | NONE                                                                                                     | OFF                                                                                                                | A                                | 11.89 (.468)                    | 17.45 (.687)                  | <b>7802K11</b>                                | <b>7802K31</b>                                       | <b>7802K21 ③</b>                  | <b>7802K41</b> |
|                                                                         | 1 P.D.T.        | ON<br>ON<br>ON*                                                                                      | OFF<br>NONE<br>OFF                                                                                       | ON<br>ON<br>ON*                                                                                                    | B                                | 11.89 (.468)                    | 17.04 (.671)                  | <b>7802K12</b><br><b>7802K13</b><br>7802K17 ① | <b>7802K32</b><br><b>7802K33</b><br><b>7802K37 ④</b> | 7802K22<br>7802K23 ③<br>7802K27 ④ |                |
| 30A, 125V ac<br>25A, 250V ac ①                                          | 1 P.S.T.        | ON                                                                                                   | NONE                                                                                                     | OFF                                                                                                                | A                                | 8.74 (.344)                     | 14.30 (.563)                  | —                                             | <b>7576K2</b>                                        | —                                 | N/A            |

Selection Table continues on page 2.4.

\* Momentary Contact.

① Single pole switch in 2-pole base.

② Also 4.2A L @ 125V ac Rating.

③ Also 7.5A @ 277V ac, 3/4 Hp @ 120, 240 and 277V ac.

④ Not CSA Certified.

## Base Material:

Thermoset molding material.

## Mounting Means:

Threaded Bushing —  
11.89mm (.468") dia.,  
32 threads/inch.

## Keyway —

1.73 x .89mm deep  
(.068 x .035" deep), provides  
antirotation feature.

## Hardware Supplied —

1 hexagon locknut  
(**Cat. No. 15-192**) and  
1 bright nickel plated knurled  
facenut (**Cat. No. 15-124F1**),  
except 7700-7705 which have  
bright nickel hexagon facenut  
(**Cat. No. 15-966-2**).  
Furnished unassembled.

## Finish:

Bright nickel plated toggle lever  
and bushing.

## Dielectric Withstand:

1,000V RMS minimum.

## Operating Temperature Range:

-17.8°C to +65.6°C  
(0°F to +150°F).

## Approvals:

UL Recognized.

CSA Certified (except as noted).



## Contact Material:

| 7500, 7600, 7700 and 7900 Series Switches |                                             |                                          |
|-------------------------------------------|---------------------------------------------|------------------------------------------|
| Amperage                                  | Movable                                     | Stationary                               |
| 3 to 6                                    | Silver Plated Copper                        | Silver Plated Copper                     |
| 10 to 20                                  | Silver Plated Copper with Silver Buttons    | Silver Plated Copper with Silver Buttons |
| 20 to 30                                  | Silver Plated Copper with Cad Oxide Buttons | Copper with Cad Oxide Buttons            |
| 7800 Series Switches                      |                                             |                                          |
| 3 to 6                                    | Silver Plated Copper                        | Silver Plated Copper                     |
| 10 to 20                                  | Copper with Silver Buttons                  | Copper with Silver Buttons               |

**OPTIONAL FEATURES** — General Purpose AC Rated Toggles, pages 2.2-2.4. Features shown below may not be available on all toggle models. Contact your local Eaton Sales Representative.

### FEATURES FOR 7500, 7600, 7700, 7900 SERIES


|                                                                              |
|------------------------------------------------------------------------------|
| 3-Independent "ON" Circuit (2PDT or 4PDT only, refer to page 4.28)           |
| Short (11/32") Bushing                                                       |
| Tall (15/32") Bushing                                                        |
| White Nylon Designer Lever (See above dimensions)                            |
| Black Nylon Designer Lever (See above dimensions)                            |
| Hardware Furnished Assembled                                                 |
| Reversing Jumpers (Not for use with 3-Independent "ON" Circuit)              |
| Short (15/32") Bat Lever                                                     |
| Tall (11/16") Bat Lever (Not available with Short Bushing)                   |
| Rotate Keyway 180°                                                           |
| Lever Seal                                                                   |
| Omit One Pole (2P, 3P, 4P only. Not for use with 3-Independent "ON" Circuit) |

### FEATURES FOR 7800 SERIES ONLY

|                                                                              |
|------------------------------------------------------------------------------|
| 3-Independent "ON" Circuit (2PDT or 4PDT only, refer to page 4.28)           |
| Hardware Furnished Assembled                                                 |
| Reversing Jumpers (Not for use with 3-Independent "ON" Circuit)              |
| Rotate Keyway 180°                                                           |
| Silicone Lever Seal (1P and 2P only)                                         |
| Omit One Pole (2P, 3P, 4P only. Not for use with 3-Independent "ON" Circuit) |

## DIMENSIONS

APPROXIMATE IN MM (INCHES)



Single Pole



7500, 7600, 7700, 7900 Series  
Double Pole



7800 Series  
Double Pole



Four Pole

# 2 TOGGLE SWITCHES

## General Purpose Toggle Switches — AC Rated (continued)

**STANDARD AC RATED TOGGLES SELECTION TABLE** (BOLD FACE TYPE INDICATES ITEMS NORMALLY IN DISTRIBUTOR STOCK)

| Rating                                                                                                 | Poles and Throw | Circuit with Toggle in                                                                           |                                                                                                      |                                                                                                             | BASE CIRCUIT SEE PAGE 4.28 | Bushing Length A mm (inches) | Lever Length B mm (inches)   | CATALOG NUMBERS                 |                                 |                                     |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|--------------------------------------------------------------------------------------------------------|-----------------|--------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|----------------------------|------------------------------|------------------------------|---------------------------------|---------------------------------|-------------------------------------|-----------------------------------|------------|--|--|--|--|--|--|--|--|--|--|--|
|                                                                                                        |                 | UP Position<br> | CENTER Position<br> | DOWN Position<br> (Keyway) |                            |                              |                              | Solder Lugs                     | Screw Terminals                 | .250" Spade Terminals               | Combi-Term                        |            |  |  |  |  |  |  |  |  |  |  |  |
| TWO POLE                                                                                               |                 |                                                                                                  |                                                                                                      |                                                                                                             |                            |                              |                              |                                 |                                 |                                     |                                   | TWO POLE   |  |  |  |  |  |  |  |  |  |  |  |
| 6A, 125V ac<br>3A, 250V ac<br>2A, 277V ac<br>2.5A, L @ 125V ac                                         | 2 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | C                          | 11.91 (.469)                 | 14.30 (.563)                 | 7590K6                          | 7590K4                          | 7590K8                              | N/A                               |            |  |  |  |  |  |  |  |  |  |  |  |
| 6A, 125V ac<br>3A, 250V ac<br>2.5A, L @ 125V ac                                                        | 2 P.D.T.        | ON                                                                                               | OFF                                                                                                  | ON                                                                                                          | D                          | 11.91 (.469)                 | 14.30 (.563)                 | 7591K6                          | 7591K4                          | 7591K8                              |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 2 P.D.T.        | ON                                                                                               | NONE                                                                                                 | ON                                                                                                          | D                          | 11.91 (.469)                 | 14.30 (.563)                 | 7592K6                          | 7592K4                          | 7592K8                              |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 6A, 125V ac<br>3A, 250V ac                                                                             | 2 P.D.T.        | ON*                                                                                              | OFF                                                                                                  | ON*                                                                                                         | D                          | 11.91 (.469)                 | 14.30 (.563)                 | 7597K6                          | 7597K4                          | 7597K8                              |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 15A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac<br>1/2 Hp, 125V ac                                     | 2 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | C                          | 8.74 (.344)<br>11.91 (.469)  | 14.30 (.563)<br>14.30 (.563) | 7561K5<br>7561K4                | 7560K6<br>7560K5                | 7561K7<br>7561K6                    |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 15A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 125-250V ac                                                    | 2 P.D.T.        | ON                                                                                               | OFF                                                                                                  | ON                                                                                                          | D                          | 8.74 (.344)<br>11.91 (.469)  | 14.30 (.563)<br>14.30 (.563) | 7563K5<br>7563K4                | 7562K5<br>7562K4                | 7563K7<br>7563K6                    |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 15A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac                                                        | 2 P.D.T.        | ON                                                                                               | NONE                                                                                                 | ON                                                                                                          | D                          | 11.91 (.469)                 | 14.30 (.563)                 | 7565K5                          | 7564K6                          | 7565K7                              |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 15A, 125V ac<br>10A, 250V ac<br>1/2 Hp, 250V ac                                                        | 2 P.S.T.        | OFF                                                                                              | NONE                                                                                                 | ON*                                                                                                         | C                          | 11.91 (.469)                 | 14.30 (.563)                 | 7566K4                          | 7566K5                          | 7566K7                              |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 2 P.D.T.        | ON<br>ON*                                                                                        | OFF<br>OFF<br>NONE                                                                                   | ON*<br>ON*<br>ON*                                                                                           | D                          | 11.91 (.469)                 | 14.30 (.563)                 | 7568K3 ❶<br>7569K1<br>7570K4    | 7568K2 ❶<br>7569K2<br>7570K5    | 7568K4 ❶<br>7569K3<br>7570K7        |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 2 P.D.T.        | ON*                                                                                              | OFF                                                                                                  | ON*                                                                                                         | D                          | 11.91 (.469)                 | 17.48 (.688)                 | 7569K38                         | 7569K36                         | 7569K40                             |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 20A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac<br>1/2 Hp, 125V ac                                     | 2 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | C                          | 11.91 (.469)                 | 17.48 (.688)                 | 7630K38                         | 7630K36                         | 7630K40                             |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 2 P.D.T.        | ON                                                                                               | NONE                                                                                                 | ON                                                                                                          | D                          | 11.91 (.469)                 | 17.48 (.688)                 | 7632K38                         | 7632K36                         | 7632K40                             |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 20A, 125V ac<br>10A, 250V ac<br>1 Hp, 120-240V ac                                                      | 2 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | C                          | —                            | —                            | 7803K11                         | 7803K31                         | 7803K21 ❸                           | 7803K41                           |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 2 P.D.T.        | ON<br>ON<br>ON*                                                                                  | OFF<br>NONE<br>OFF                                                                                   | ON<br>ON<br>ON*                                                                                             | D                          | —                            | —                            | 7803K12<br>7803K13<br>7803K17 ❸ | 7803K32<br>7803K33<br>7803K37 ❸ | 7803K22 ❶<br>7803K23 ❸<br>7803K27 ❸ | 7803K42<br>7803K43 ❸<br>7803K47 ❸ |            |  |  |  |  |  |  |  |  |  |  |  |
| THREE POLE                                                                                             |                 |                                                                                                  |                                                                                                      |                                                                                                             |                            |                              |                              |                                 |                                 |                                     |                                   | THREE POLE |  |  |  |  |  |  |  |  |  |  |  |
| 15A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac<br>1 Hp, 3 Ph 125-600V ac<br>1 Hp 1 & 2 Ph 125-480V ac | 3 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | E                          | 11.91 (.469)                 | 17.48 (.688)                 | 7700K1                          | 7700K2                          | 7700K3                              | N/A                               |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 3 P.D.T.        | ON<br>ON                                                                                         | OFF<br>NONE                                                                                          | ON<br>ON                                                                                                    | F                          | 11.91 (.469)                 | 17.48 (.688)                 | 7701K1<br>7702K1                | 7701K2<br>7702K2                | 7701K3<br>7702K3                    |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 3 P.D.T.        | ON*<br>ON*                                                                                       | OFF<br>NONE                                                                                          | ON<br>ON                                                                                                    | F                          | 11.91 (.469)                 | 17.48 (.688)                 | 7704K1<br>7705K1                | 7704K2<br>7705K2                | 7704K3<br>7705K3                    |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 20A, 125V ac<br>10A, 250V ac<br>1 Hp, 120V ac<br>1, 2, & 3 phase                                       | 3 P.D.T.        | ON                                                                                               | OFF                                                                                                  | ON                                                                                                          | F                          | —                            | —                            | 7804K12 ❷❸                      | 7804K32 ❸                       | 7804K22 ❸                           | 7804K42 ❸                         |            |  |  |  |  |  |  |  |  |  |  |  |
| FOUR POLE                                                                                              |                 |                                                                                                  |                                                                                                      |                                                                                                             |                            |                              |                              |                                 |                                 |                                     |                                   | FOUR POLE  |  |  |  |  |  |  |  |  |  |  |  |
| 15A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac                                                        | 4 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | E                          | 11.91 (.469)                 | 17.48 (.688)                 | 7691K14                         | 7690K8                          | —                                   | N/A                               |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 4 P.D.T.        | ON<br>ON                                                                                         | OFF<br>NONE                                                                                          | ON<br>ON                                                                                                    | F                          | 11.91 (.469)                 | 17.48 (.688)                 | 7693K2<br>7695K5                | 7692K13<br>7694K4               | —                                   |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 20A, 125V ac<br>10A, 250V ac<br>3/4 Hp, 250V ac<br>1/2 Hp, 125V ac                                     | 4 P.S.T.        | ON                                                                                               | NONE                                                                                                 | OFF                                                                                                         | E                          | 11.91 (.469)                 | 17.48 (.688)                 | 7933K38                         | 7933K36                         | 7933K40                             |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
|                                                                                                        | 4 P.D.T.        | ON<br>ON                                                                                         | OFF<br>NONE                                                                                          | ON<br>ON                                                                                                    | F                          | 11.91 (.469)                 | 17.48 (.688)                 | 7934K38<br>7935K38              | 7934K36<br>7935K36              | 7934K40<br>7935K40                  |                                   |            |  |  |  |  |  |  |  |  |  |  |  |
| 20A, 125V ac<br>10A, 250V ac<br>1 Hp, 125-240V ac<br>2 & 3 phase                                       | 4 P.D.T.        | ON                                                                                               | OFF                                                                                                  | ON                                                                                                          | F                          | —                            | —                            | 7805K12 ❸                       | 7805K32 ❸                       | 7805K22 ❸                           | 7805K42 ❸                         |            |  |  |  |  |  |  |  |  |  |  |  |

\* Momentary Contact.

❶ Also 1/2 Hp at 125-250V ac Rating.


❷ 1 Hp @ 240-480V ac 1 or 2 phase and 240-600V ac, 3 phase.

❸ Not CSA Certified.


❹ Also 7.5A, 277V ac, 3/4 Hp, 120-240-277V ac.

## DIMENSIONS — 7500, 7600, 7700, 7900 SERIES APPROXIMATE IN MM (INCHES)


### 1PST MAINTAINED & MOMENTARY (SCREW TERMINALS)




### 1PDT MAINTAINED & MOMENTARY (SOLDER LUGS)




### 1PDT MAINTAINED & MOMENTARY (SPADE TERMINALS)




### 2PDT MAINTAINED (SCREW TERMINALS)




### 2PDT MAINTAINED (SOLDER LUGS)




### 2PDT MAINTAINED (SPADE TERMINALS)



### 2PDT MOMENTARY (SCREW TERMINALS)



### 2PDT MOMENTARY (SOLDER LUGS)



# 2 TOGGLE SWITCHES

## General Purpose Toggle Switches — AC Rated (continued)

**DIMENSIONS — 7500, 7600, 7700, 7900 SERIES** APPROXIMATE IN MM (INCHES)

| 2PDT MOMENTARY (SPADE TERMINALS)              | 3PDT MAINTAINED & MOMENTARY (SCREW TERMINALS) |
|-----------------------------------------------|-----------------------------------------------|
|                                               |                                               |
| 3PDT MAINTAINED & MOMENTARY (SOLDER LUGS)     | 3PDT MAINTAINED & MOMENTARY (SPADE TERMINALS) |
|                                               |                                               |
| 4PDT MAINTAINED & MOMENTARY (SCREW TERMINALS) | 4PDT MAINTAINED & MOMENTARY (SOLDER LUGS)     |
|                                               |                                               |
| 4PDT MAINTAINED & MOMENTARY (SPADE TERMINALS) |                                               |
|                                               |                                               |