

Surface Mount, Micro-Miniature

Power Splitter/Combiner

2 Way-0° 50Ω

1000 to 2500 MHz

SBTC-2-25X+



No Leads

CASE STYLE: AT1667


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.


Pin Connections

SUM PORT	6
PORT 1	3
PORT 2	4
GROUND	1,2
NOT USED	5

Outline Drawing



PCB Land Pattern




Outline Dimensions (inch mm)

A	B	C	D	E	F
.150	.150	.150	.050	.030	.025
3.81	3.81	3.81	1.27	0.76	0.64
G	H	J	K		wt
.028	.050	.160	.030		grams
0.71	1.27	4.06	0.76		0.10

Demo Board MCL P/N: TB-274

Suggested PCB Layout (PL-152)



NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020 ± 0.0015 ; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

■ DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wide band frequency, 1000-2500 MHz
- excellent amplitude unbalance, 0.2 dB typ.
- small size, 0.166"x0.150"x0.155"
- temperature stable LTCC base
- small size
- low cost
- aqueous washable
- protected by US patent 6,963,255

Applications

- PCN/PCS
- DECT
- PHS




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)	INSERTION LOSS (dB) ABOVE 3.0 dB	PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ. Min.	Typ. Max.	Max.	Max.
1000-2500	20 14	1.4 2.5	14	1.2
1400-1800	18 14	0.9 1.7	8	0.7
1800-2000	19 16	1.0 1.7	8	0.8

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB) S-1	Total Loss ¹ (dB) S-2	Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
1000.00	4.10	3.83	0.28	22.47	2.79	1.72	1.68	1.57
1100.00	4.07	3.85	0.21	21.47	2.54	1.66	1.59	1.51
1200.00	4.05	3.90	0.15	20.62	2.39	1.61	1.51	1.46
1300.00	4.01	3.93	0.08	19.92	2.34	1.56	1.45	1.41
1400.00	3.98	3.96	0.04	19.49	2.36	1.51	1.39	1.36
1500.00	3.96	4.00	0.05	19.21	2.47	1.47	1.33	1.32
1600.00	3.93	4.03	0.10	19.18	2.66	1.42	1.28	1.27
1700.00	3.90	4.06	0.16	19.29	2.92	1.37	1.24	1.23
1800.00	3.88	4.09	0.21	19.68	3.28	1.32	1.21	1.18
1900.00	3.86	4.12	0.27	20.37	3.70	1.26	1.19	1.14
2000.00	3.84	4.16	0.32	21.53	4.23	1.20	1.18	1.10
2100.00	3.83	4.21	0.37	23.36	4.87	1.13	1.18	1.08
2200.00	3.84	4.26	0.42	26.19	5.57	1.06	1.18	1.10
2300.00	3.88	4.34	0.46	28.88	6.36	1.09	1.18	1.15
2500.00	4.08	4.63	0.55	21.85	8.22	1.39	1.15	1.30

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic

