

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

BELDEN
SENDING ALL THE RIGHT SIGNALS

9908 Hook-up/Lead - UL AWM Styles 1028 and 1015

For more Information
please call

1-800-Belden1



Description:

Tinned copper conductor, PVC insulation.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	8	84x27	TC - Tinned Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.045

Overall Insulation

Overall Cable

Overall Nominal Diameter: 0.250 in.

Mechanical Characteristics (Overall)

Bulk Cable Weight: 72 lbs/1000 ft.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	600 V, 105°C
UL Type:	MTW or AWM 1015/1028
CSA Rating:	600 V, 105°C
CSA Type:	TEW
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test: VW-1

Plenum/Non-Plenum

Plenum (Y/N): No

Put Ups and Colors:

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

9908 Hook-up/Lead - UL AWM Styles 1028 and 1015

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9908 002100	100 FT	7.700 LB	RED		#8 STR PVC RED
9908 002250	250 FT	18.500 LB	RED		#8 STR PVC RED
9908 004100	100 FT	7.700 LB	YELLOW		#8 STR PVC YEL
9908 009100	100 FT	7.700 LB	WHITE		#8 STR PVC WHT
9908 009250	250 FT	18.500 LB	WHITE		#8 STR PVC WHT
9908 010100	100 FT	8.000 LB	BLACK		#8 STR PVC BLK
9908 010250	250 FT	18.500 LB	BLACK		#8 STR PVC BLK

Revision Number: 2 Revision Date: 08-26-2008

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9908 002100](#) [9908 009250](#) [9908 004100](#)