




BLACK FLANGE MOUNT HEADERS								
CKT. SIZE	PART NUMBER	ENG NUMBER	PLATING	DIM "A"	DIM "B"	DIM "C"	DIM "D"	PACKAGING
2	15-97-8022	30070-02A3	TIN	.213	—	.354	.606	BULK
	15-97-8027	30070-02A1	GOLD	(5.40)	—	(9.00)	(15.40)	
4	15-97-8042	30070-04A3	TIN	.378	.165	.520	.772	
	15-97-8047	30070-04A1	GOLD	(9.60)	(4.20)	(13.20)	(19.60)	
6	15-97-8062	30070-06A3	TIN	.543	.331	.685	.937	
	15-97-8067	30070-06A1	GOLD	(13.80)	(8.40)	(17.40)	(23.80)	
8	15-97-8082	30070-08A3	TIN	.709	.496	.850	1.102	
	15-97-8087	30070-08A1	GOLD	(18.00)	(12.60)	(21.60)	(28.00)	
10	15-97-8102	30070-10A3	TIN	.874	.661	1.016	1.268	
	15-97-8107	30070-10A1	GOLD	(22.20)	(16.80)	(25.80)	(32.20)	
12	15-97-8122	30070-12A3	TIN	1.039	.827	1.181	1.433	TRAY
	15-97-8127	30070-12A1	GOLD	(26.40)	(21.00)	(30.00)	(36.40)	
16	15-97-8162	30070-16A3	TIN	1.370	1.157	1.512	1.764	
	15-97-8167	30070-16A1	GOLD	(34.80)	(29.40)	(38.40)	(44.80)	



RECOMMENDED HOLE LAYOUT FOR .070/(1.78) MAX. P.C.BOARD
VIEWED FROM COMPONENT SIDE OF BOARD



OPTION 2
FLANGE MOUNT
SEE SHEET 1 FOR PEG MOUNT



FINISHED PART LEGEND

30070 - * * * *

BASE NUMBER

CIRCUIT SIZE


PCB MOUNTING & COLOR

"B" OR "1" = PEG (SEE SHEET 1)

"A" = FLANGE COLOR = BLACK

"3" = PEG (SEE SHEET 1)

PLATING (SEE NOTE 2)



SEE SHEET 1 EC NO: UCP2014-0823 2013/08/21 DRW:NGUYEN CHKD:JBELL 2013/08/21 APPR:FSMITH 2013/08/22	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± 0.25 ± .014 1 PLACE ± 0.36 ± --- 0 PLACE ± ± ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE IN/MM DRAWN BY DATE TGREGORI 2006/03/28 CHECKED BY DATE JCOMERCI 2006/03/28 APPROVED BY DATE FSMITH 2010/04/09 MATERIAL NO. SEE CHART	SCALE 4:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION MINI-FIT TPA RIGHT ANGLE HEADER ASSY molex DOCUMENT NO. SD-30070-001 SHEET NO. 2 OF 2