

# FGA70N30T 300V, 70A PDP IGBT

## Features

- High current capability
- Low saturation voltage:  $V_{CE(sat)} = 1.5V$  @  $I_C = 40A$
- High input impedance
- Fast switching
- RoHS compliant


## Application

. PDP System




## General Description

Using Novel Trench IGBT Technology, Fairchild's new series of trench IGBTs offer the optimum performance for PDP applications where low conduction and switching losses are essential.



TO-3P



## Absolute Maximum Ratings

| Symbol          | Description                                                             |                       | Ratings     | Units      |
|-----------------|-------------------------------------------------------------------------|-----------------------|-------------|------------|
| $V_{CES}$       | Collector-Emitter Voltage                                               |                       | 300         | V          |
| $V_{GES}$       | Gate-Emitter Voltage                                                    |                       | $\pm 30$    | V          |
| $I_C$ pulse(1)* | Pulsed Collector Current                                                | @ $T_C = 25^\circ C$  | 160         | A          |
| $P_D$           | Maximum Power Dissipation                                               | @ $T_C = 25^\circ C$  | 201         | W          |
|                 | Maximum Power Dissipation                                               | @ $T_C = 100^\circ C$ | 90.6        | W          |
| $T_J$           | Operating Junction Temperature                                          |                       | -55 to +150 | $^\circ C$ |
| $T_{stg}$       | Storage Temperature Range                                               |                       | -55 to +150 | $^\circ C$ |
| $T_L$           | Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds |                       | 300         | $^\circ C$ |

## Thermal Characteristics

| Symbol                 | Parameter                               | Typ. | Max. | Units        |
|------------------------|-----------------------------------------|------|------|--------------|
| $R_{\theta JC}$ (IGBT) | Thermal Resistance, Junction-to-Case    | --   | 0.62 | $^\circ C/W$ |
| $R_{\theta JA}$        | Thermal Resistance, Junction-to-Ambient | --   | 40   | $^\circ C/W$ |

### Notes:

(1) Repetitive test, pulse width = 100usec, Duty = 0.2

\*  $I_C$  pulse limited by max  $T_J$

## Package Marking and Ordering Information

| Device Marking | Device      | Package | Packaging Type | Qty per Tube | Max Qty per Box |
|----------------|-------------|---------|----------------|--------------|-----------------|
| FGA70N30T      | FGA70N30TTU | TO-3P   | Tube           | 30ea         | -               |

## Electrical Characteristics T<sub>C</sub> = 25°C unless otherwise noted

| Symbol                                             | Parameter                                    | Test Conditions                                                                                                                       | Min. | Typ. | Max.  | Units |
|----------------------------------------------------|----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|------|------|-------|-------|
| Off Characteristics                                |                                              |                                                                                                                                       |      |      |       |       |
| BV <sub>CES</sub>                                  | Collector-Emitter Breakdown Voltage          | V <sub>GE</sub> = 0V, I <sub>C</sub> = 250uA                                                                                          | 300  | --   | --    | V     |
| ΔB <sub>V<sub>CES</sub></sub> /<br>ΔT <sub>J</sub> | Temperature Coefficient of Breakdown Voltage | V <sub>GE</sub> = 0V, I <sub>C</sub> = 250uA                                                                                          | --   | 0.2  | --    | V/°C  |
| I <sub>CES</sub>                                   | Collector Cut-Off Current                    | V <sub>CE</sub> = V <sub>CES</sub> , V <sub>GE</sub> = 0V                                                                             | --   | --   | 250   | uA    |
| I <sub>GES</sub>                                   | G-E Leakage Current                          | V <sub>GE</sub> = V <sub>GES</sub> , V <sub>CE</sub> = 0V                                                                             | --   | --   | ± 400 | nA    |
| On Characteristics                                 |                                              |                                                                                                                                       |      |      |       |       |
| V <sub>GE(th)</sub>                                | G-E Threshold Voltage                        | I <sub>C</sub> = 250uA, V <sub>CE</sub> = V <sub>GE</sub>                                                                             | 3.0  | 4.5  | 5.5   | V     |
| V <sub>CE(sat)</sub>                               | Collector to Emitter Saturation Voltage      | I <sub>C</sub> = 20A, V <sub>GE</sub> = 15V                                                                                           | --   | 1.2  | 1.5   | V     |
|                                                    |                                              | I <sub>C</sub> = 40A, V <sub>GE</sub> = 15V                                                                                           | --   | 1.5  | --    | V     |
|                                                    |                                              | I <sub>C</sub> = 70A, V <sub>GE</sub> = 15V<br>T <sub>C</sub> = 25°C                                                                  | --   | 1.8  | --    | V     |
|                                                    |                                              | I <sub>C</sub> = 70A, V <sub>GE</sub> = 15V<br>T <sub>C</sub> = 125°C                                                                 | --   | 1.9  | --    | V     |
| Dynamic Characteristics                            |                                              |                                                                                                                                       |      |      |       |       |
| C <sub>ies</sub>                                   | Input Capacitance                            | V <sub>CE</sub> = 30V, V <sub>GE</sub> = 0V<br>f = 1MHz                                                                               | --   | 3000 | --    | pF    |
| C <sub>oes</sub>                                   | Output Capacitance                           |                                                                                                                                       | --   | 160  | --    | pF    |
| C <sub>res</sub>                                   | Reverse Transfer Capacitance                 |                                                                                                                                       | --   | 110  | --    | pF    |
| Switching Characteristics                          |                                              |                                                                                                                                       |      |      |       |       |
| t <sub>d(on)</sub>                                 | Turn-On Delay Time                           | V <sub>CC</sub> = 200V, I <sub>C</sub> = 40A<br>R <sub>G</sub> = 15Ω, V <sub>GE</sub> = 15V<br>Resistive Load, T <sub>C</sub> = 25°C  | --   | 32   | --    | ns    |
| t <sub>r</sub>                                     | Rise Time                                    |                                                                                                                                       | --   | 90   | --    | ns    |
| t <sub>d(off)</sub>                                | Turn-Off Delay Time                          |                                                                                                                                       | --   | 175  | --    | ns    |
| t <sub>f</sub>                                     | Fall Time                                    |                                                                                                                                       | --   | 170  | 300   | ns    |
| t <sub>d(on)</sub>                                 | Turn-On Delay Time                           | V <sub>CC</sub> = 200V, I <sub>C</sub> = 40A<br>R <sub>G</sub> = 15Ω, V <sub>GE</sub> = 15V<br>Resistive Load, T <sub>C</sub> = 125°C | --   | 30   | --    | ns    |
| t <sub>r</sub>                                     | Rise Time                                    |                                                                                                                                       | --   | 90   | --    | ns    |
| t <sub>d(off)</sub>                                | Turn-Off Delay Time                          |                                                                                                                                       | --   | 185  | --    | ns    |
| t <sub>f</sub>                                     | Fall Time                                    |                                                                                                                                       | --   | 235  | --    | ns    |
| Q <sub>g</sub>                                     | Total Gate Charge                            | V <sub>CE</sub> = 200V, I <sub>C</sub> = 40A<br>V <sub>GE</sub> = 15V                                                                 | --   | 125  | --    | nC    |
| Q <sub>ge</sub>                                    | Gate-Emitter Charge                          |                                                                                                                                       | --   | 25   | --    | nC    |
| Q <sub>gc</sub>                                    | Gate-Collector Charge                        |                                                                                                                                       | --   | 55   | --    | nC    |

## Typical Performance Characteristics

Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage Characteristics




Figure 4. Transfer Characteristics




Figure 5. Saturation Voltage vs. Case Temperature at Variant Current Level





Figure 6. Saturation Voltage vs. Vge



## Typical Performance Characteristics (Continued)

Figure 7. Saturation Voltage vs.  $V_{GE}$




Figure 8. Capacitance Characteristics




Figure 9. Gate Charge Characteristics




Figure 10. SOA Characteristics




Figure 11. Turn-on Characteristics vs. Gate Resistance





Figure 12. Turn-off Characteristics vs. Gate Resistance



## Typical Performance Characteristics (Continued)

Figure 13. Turn-on Characteristics vs. Collector Current




Figure 14. Turn-off Characteristics vs. Collector Current




Figure 15. Switching Loss vs. Gate Resistance




Figure 16. Switching Loss vs. Collector Current






Figure 17. Transient Thermal Impedance of IGBT



# TO-3PN





## TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

|                                                  |                                |                                                                                    |                             |
|--------------------------------------------------|--------------------------------|------------------------------------------------------------------------------------|-----------------------------|
| ACE <sup>®</sup>                                 | HiSeC <sup>™</sup>             | PowerSaver <sup>™</sup>                                                            | TinyBoost <sup>™</sup>      |
| Across the board. Around the world. <sup>™</sup> | i-Lo <sup>™</sup>              | PowerTrench <sup>™</sup>                                                           | TinyBuck <sup>™</sup>       |
| ActiveArray <sup>™</sup>                         | ImpliedDisconnect <sup>™</sup> | Programmable Active Droop <sup>™</sup>                                             | TinyLogic <sup>®</sup>      |
| Bottomless <sup>™</sup>                          | IntelliMAX <sup>™</sup>        | QFET <sup>®</sup>                                                                  | TINYOPTO <sup>™</sup>       |
| Build it Now <sup>™</sup>                        | ISOPLANAR <sup>™</sup>         | QS <sup>™</sup>                                                                    | TinyPower <sup>™</sup>      |
| CoolFET <sup>™</sup>                             | MICROCOUPLER <sup>™</sup>      | QT Optoelectronics <sup>™</sup>                                                    | TinyWire <sup>™</sup>       |
| CROSSVOLT <sup>™</sup>                           | MicroPak <sup>™</sup>          | Quiet Series <sup>™</sup>                                                          | TruTranslation <sup>™</sup> |
| CTL <sup>™</sup>                                 | MICROWIRE <sup>™</sup>         | RapidConfigure <sup>™</sup>                                                        | μSerDes <sup>™</sup>        |
| Current Transfer Logic <sup>™</sup>              | Motion-SPM <sup>™</sup>        | RapidConnect <sup>™</sup>                                                          | UHC <sup>®</sup>            |
| DOME <sup>™</sup>                                | MSX <sup>™</sup>               | ScalarPump <sup>™</sup>                                                            | UniFET <sup>™</sup>         |
| E <sup>2</sup> CMOS <sup>™</sup>                 | MSXPro <sup>™</sup>            | SMART START <sup>™</sup>                                                           | VCX <sup>™</sup>            |
| EcoSPARK <sup>®</sup>                            | OCX <sup>™</sup>               | SPM <sup>®</sup>                                                                   | Wire <sup>™</sup>           |
| EnSigna <sup>™</sup>                             | OCXPro <sup>™</sup>            | STEALTH <sup>™</sup>                                                               |                             |
| FACT Quiet Series <sup>™</sup>                   | OPTOLOGIC <sup>®</sup>         | SuperFET <sup>™</sup>                                                              |                             |
| FACT <sup>®</sup>                                | OPTOPLANAR <sup>®</sup>        | SuperSOT <sup>™</sup> -3                                                           |                             |
| FAST <sup>®</sup>                                | PACMAN <sup>™</sup>            | SuperSOT <sup>™</sup> -6                                                           |                             |
| FASTr <sup>™</sup>                               | PDP-SPM <sup>™</sup>           | SuperSOT <sup>™</sup> -8                                                           |                             |
| FPS <sup>™</sup>                                 | POP <sup>™</sup>               | SyncFET <sup>™</sup>                                                               |                             |
| FRFET <sup>®</sup>                               | Power220 <sup>®</sup>          | TCM <sup>™</sup>                                                                   |                             |
| GlobalOptoisolator <sup>™</sup>                  | Power247 <sup>®</sup>          | The Power Franchise <sup>®</sup>                                                   |                             |
| GTO,                                             | PowerEdge,                     |  |                             |

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status         | Definition                                                                                                                                                                                               |
|--------------------------|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production       | This datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production        | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.                                                   |
| Obsolete                 | Not In Production      | This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.                                      |

Rev. I25