


	10	9	8	7	6	5	4	3	2	19073
	MATERIAL NUMBER	ENG. NO.	MATERIAL NUMBER TAPE MOUNTED	ENG. NO.	STUD SIZE	"S" ±.005	"W" MAX	"C" MIN	"L" MAX	
F	190730081	BB-837-04	-----	-----	04	.119 (3.02)	.322 (8.18)	.285 (7.24)	.885 (22.48)	
	190730083	BB-837-06	190730084	BB-837-06T	06	.146 (3.71)				
	190730085	BB-837-08	190730086	BB-837-08T	08	.173 (4.39)				
	190730087	BB-837-10	190730088	BB-823-10T	10	.198 (5.03)				
E	190730302	BB-839-06	190730093	BB-839-06T	06	.146 (3.71)	.352 (8.94)	.310 (7.87)	.936 (23.77)	
	190730094	BB-839-08	190730096	BB-839-08T	08	.173 (4.39)				
	190730097	BB-839-10	190730099	BB-839-10T	10	.198 (5.03)				



SALES DRAWING

- NOTES:
1. MATERIAL: COPPER (.031/0.79) THICK PLATING: ELECTROPLATE TIN
 2. FERRULE: TIN-PLATED BRASS
 3. INSULATION: BLUE NYLON
 4. MWID=MAXIMUM WIRE INSULATION DIA.
 5. ALL DIMENSIONS IN INCHES (MM).
 6. WIRE SIZE: 16-14 AWG
1.0-2.5 MM²

EC NO: ETC2004-0123		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 4:1	DESIGN UNITS INCH		THIRD ANGLE PROJECTION	REVISE ON CAD ONLY	A	
DRWN:DMYRICK 2004/01/05									TITLE			
CHKD:SBEITZEL 2004/01/05						DIMENSION STYLE IN/MM		RING TONGUE TERMINAL AVIKRIMP, 800-SERIES 16-14 AWG				
APPR:RDEROSS 2004/01/06						DRAWN BY DMYRICK DATE 03/12/15		MOLEX MOLEX INCORPORATED				
						CHECKED BY SBEITZEL DATE 03/12/15						
		REV		ANGULAR ± 1 °		APPROVED BY RDEROSS	DATE 03/12/15	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-19073-006	SHEET NO. 1 OF 1	B	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						