


*** UNCONTROLLED DOCUMENT * FOR REFERENCE ONLY**

STEWARD



CORE DIMENSIONS

UNCOATED CORE 35T1417-000				
	MM	INCHES	MM	INCHES
OD	36.00	(1.417)	± .51	(.020)
ID	23.00	(.906)	± .51	(.020)
TH	10.00	(.394)	± .25	(.010)
EPOXY COATING 35T1417-00H				
OD	37.27	(1.467)	± max	
ID	21.73	(.856)	± min	
TH	11.02	(.434)	± max	

WEIGHT / K 29.4840 KGS 65.0000 LBS
INITIAL PERMEABILITY **5000**

ELECTRICAL SPECIFICATIONS

	MIN (μH)	MIN TOL.	NOM (μH)	MAX (μH)	MAX TOL.	FREQ. (kHz)	VOLT. (V)	TURNS
L1	3.634	(-20%)	4.453	5.452	+20%	100	≤.0284	1
L2	363.4	(-20%)	445.3	545.2	+20%	100	≤.2838	10
Q	10	-	-	-	-	100	≤.0284	1

COATING SPECIFICATIONS

		Max. Coating Thickness (mm)	Min. DLB VAC	Min. DLB VDC	TEST FORCE (LB)
TYPE					
35T1417-000	UNCOATED	-	-	-	-
35T1417-00H	EPOXY	0.76	1000	1333	9.34

NOTES

Steward

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.

Date:	01/05/2006	DWG #:	35T1417-00H-E	Title:	35T1417-00H	REV:	E
Drawn By:	JRK						

REV	Description	ECN #	Date	INT
E	Chg Coating description from Poly to Epoxy Add Kgs to Weight		01/05/06	JRK