





STRIP MATERIAL NUMBER	FINISH
84590-0020	OVERALL NICKEL 80µ" MINIMUM



WIRE INSULATION O.D. RANGE $\frac{.055-.085}{1.40-2.16}$

- NOTES:
1. MATERIAL: COPPER ALLOY .0120/0.305 THICK.
 2. FINISH: SEE CHART.
 3. STRIP TERMINALS ARE REELED AS SHOWN ABOVE, 3000 PARTS PER REEL.
 4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR ASSEMBLIES.
 5. ALL DIMENSIONS ARE REFERENCE.
 6. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

UPDATE WIRE INSL. OD EC NO: WNA2008-0261 DRWING: 2008/04/29 CHKD:RDEROSS 2008/04/30 APPR:RDEROSS 2008/05/01 G		DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± .010</td></tr><tr><td>2 PLACES</td><td>± 0.25</td><td>± .02</td></tr><tr><td>1 PLACE</td><td>± 0.5</td><td>± ---</td></tr><tr><td colspan="3">ANGULAR ± 1 °</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .010	2 PLACES	± 0.25	± .02	1 PLACE	± 0.5	± ---	ANGULAR ± 1 °			DIMENSION STYLE IN/MM DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE MATERIAL NO. SIZE	SCALE 2:1 TITLE CONTACT PIN 16-18 AWG molex MOLEX INCORPORATED DOCUMENT NO. SD-84590-005 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DESIGN UNITS INCH	THIRD ANGLE PROJECTION SHEET NO. 1 OF 1
	mm	INCH																								
4 PLACES	± ---	± ---																								
3 PLACES	± ---	± .010																								
2 PLACES	± 0.25	± .02																								
1 PLACE	± 0.5	± ---																								
ANGULAR ± 1 °																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																										