




ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	12.0	± Max
T:	5.1	± Max
Lead Diameter	0.8	± Nom
S:	7.8	± Nom
L:	38.0	± Nom
Coating Lead Run Down (straight Leads)	5.0	± Max
B:	6.35	± Nom
C:	3.42	± Nom



Electrical Specifications

Resistance:	20.0 Ω	± 20 %
Max Steady State Current upto 65°C:	2.00	A
Max Rec. Energy Rating:	30	J
Actual Failure Instantaneous Energy:	60	J
Resistance @ 100% Max Current:	0.45	Ω
Resistance @ 50% Max Current:	0.85	Ω
Body Temperature at 100% Max Current:	132.00	°C
Dissipation Constant:	12.7	mw/°C
Thermal Time Constant:	40	Sec.
Material Type (for Beta and Curve):	H	

SL12 20002

Date: 04/11/2012	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: