


THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				, 19		LOC		DIST						REVISIONS													
© COPYRIGHT 19				BY AMP INCORPORATED.				ALL INTERNATIONAL RIGHTS RESERVED.				G		14		P		F		ZONE		LTR		DESCRIPTION		DATE		APPD			
AMP PART NO		MATERIAL		PKG TYPE		QTY																		J		REV PER 0G3A-0328-02		07JUN02		JR MS	
8-36934-3		M/F 8-36934-0		BOX		25																									



AMP WIRE RANGE	UL E13288 Listed
4/0 AWG SOLID OR STRANDED	4/0 AWG SOLID OR STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
4/0 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 4/OW* APPROX AS SHOWN
- 2 STAMP 200 APPROX AS SHOWN
- 3 MATERIAL THK: 2.59±0.08 [.102±.003]

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -			DR 5/20/93 DK SCHRUM		 AMP Incorporated Harrisburg, PA 17105-3608					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE		MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 1/27/94 RD HEIM		NAME TERMINAL, RING TONGUE, SOLISTRAND					
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		WIRE CROSS SECTIONAL AREA RANGE: 96.3-117.0mm² [190,000-231,100] CIR MILS SOLID OR STRANDED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B 545		APPD 1/27/94 RE ROSER							
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPLICATION SPEC -		APPD 1/27/94 JL MECKLEY							
								PRODUCT SPEC -		SIZE 		CAGE CODE 00779		DRAWING NO C-36934	
								WEIGHT -		SCALE 2:1		SHEET 1 OF 1			