

MODULAR CONNECTORS

CL 222 TM

Plug for copper foil, stranded wire flat type cable

• Material • Finish

Part name	Material	Finish
Plug case	Polycarbonate	Clear
Terminal	Phosphor Bronze	Gold plated

Applicable Cable	
Conductor diameter	Copper foil or AWG # 26
Insulator diameter	φ0.9-φ1.0


• Electrical Performance

Item	Condition	Specification
Current rating	Per pin	0.5A
Voltage rating	Per pin	125V AC
Insulation Resistance	100V DC	100 M Ω Min.
Withstanding Voltage	1 minute	500V r.m.s AC


• TM3P-44P




(Packing unit: 100 Pcs.)



CL No.	Part No.	RoHS
222-0207-2	TM3P-44P	YES




Applicable cable section




• TM3P-62P, 64P & 66P




(Packing unit: 100 Pcs.)



CL No.	Part No.	RoHS
222-0278-0	TM3P-62P	YES
222-0208-5	TM3P-64P	
222-0209-8	TM3P-66P	



Applicable cable section




Note: Shown TM3P-64P.


MODULAR CONNECTORS

CL 222 TM


• TM8P-88P



(Packing unit: 100 Pcs.)



CL No.	Part No.	RoHS
222-1817-9	TM8P-88P	YES



MODULAR CONNECTORS

CL 222 TM

Plug for copper foil, stranded wire circular type cable

• Material • Finish

Part name	Material	Finish
Plug case	Polycarbonate	Clear
Terminal	Phosphor Bronze	Gold plated

Applicable Cable	
Conductor diameter	Copper foil or AWG # 26
Insulator diameter	φ0.9-φ1.0

• Electrical Performance



Item	Condition	Specification
Current rating	Per pin	0.5A
Voltage rating	Per pin	125V AC
Insulation Resistance	100V DC	100 M Ω Min.
Withstanding Voltage	1 minute	500V r.m.s AC

• TM4P-44P



CL No.	Part No.	RoHS
222-0279-3	TM4P-44P	YES



(Packing unit: 100 Pcs.)




Applicable cable section





• TM4P-64P & 66P


CL No.	Part No.	RoHS
222-0280-2	TM4P-64P	YES
222-0281-5	TM4P-66P	YES





(Packing unit: 100 Pcs.)



TM4P-64P



TM4P-66P



Applicable cable section


Note: Shown TM4P-64P.

MODULAR CONNECTORS




CL 222 TM

• TM10P-88P

CL No.	Part No.	RoHS
222-1818-1	TM10P-88P	YES




(Packing unit: 100 Pcs.)



MODULAR CONNECTORS

CL 222 TM



CL No.	Part No.	Applicable connector
902-0030-8-01	TC-2220-44(01)	TM3P-44P、TM4P-44P
902-0031-0-01	TC-2220-64(01)	TM3P-64P、TM4P-64P TM3P-62P
902-0032-3-01	TC-2220-66(01)	TM3P-66P、TM4P-66P
250-0228-1	TC-2220-8/10P-88-1	TM8P-88P、TM10P-88P TM10P1-88P

* This tool is made of metal and offers rigidity and durability. The handle is equipped with a ratchet mechanism that allows the press fit height of the plate contact to be set uniformly, and also permits the prevention of insufficient clamping.

* The tool can be used for insulation stripping of flat cables and round cables. Note that model TC-2220-66(01) is for use with flat cables only. Also note that model TC-2220-8/10P-88-1 is not equipped with an insulation stripping mechanism.

* The cable is pulled out by the lever which permits consistent insulation stripping.

Note: Please note that depending on the specifications of the cable, there may be instances in which the insulation cannot be stripped.

When using the tool with products other than Hirose Electric modular plugs, the wiring quality cannot be guaranteed; therefore, please be sure to use Hirose Electric plugs.

Item	Part No.	CL No.	Applicable connector
Press	CM-105	901-0005-4	
Applicator	Applicator 105-TMP-44	901-0195-1	TM3P-44P、TM4P-44P
	Applicator 105-TMP-64	901-0194-9	TM3P-64P、TM4P-64P TM2P-62P
	Applicator 105-TMP-66	901-0193-6	TM3P-66P、TM4P-66P
	AP105-TM10P1-88P	901-2569-0	TM8P-88P、TM10P-88P

MODULAR CONNECTORS

CL 222 TM

Plug for Solid Wire Cable

• Material • Finish

Part name	Material	Finish
Plug case	Polycarbonate	Clear
Terminal	Phosphor Bronze	Gold plated

Applicable Cable	
Conductor diameter	$\phi 0.4 \sim \phi 0.65$ *
Insulator diameter	$\phi 0.96$ max.


* In case of use $\phi 0.65$, not to be connected fully for 6 pins and 8 pins depend on size of insulator diameter.

• Electrical Performance


Item	Condition	Specification
Current rating	Per pin	0.5A
Voltage rating	Per pin	30V AC
Insulation Resistance	100V DC	100 M Ω Min.
Withstanding Voltage	1 minute	500V r.m.s AC

• TM20P-66P

CL No.	Part No.	RoHS
222-2275-3	TM20P-66P	YES



Mating Condition Figure




TM5RE3 66


(Packing unit: 100 Pcs.)

• TM20P-88P

CL No.	Part No.	RoHS
222-2217-7	TM20P-88P	YES



Mating Condition Figure



TM5RE3 88

(Packing unit: 100 Pcs.)

Exclusive Hand Tool for Connection



CL No.	Part No.	Applicable Connector
250-0240-7	TC2-TM20P-66P	TM20P-66P
250-0241-0	TC2-TM20P/30P-88P	TM20P-88P

MODULAR CONNECTORS

CL 222 TM

Plug for Thin Wire Cable

• Material • Finish

Part name	Material		Finish
Plug case	Polycarbonate *	6 Pins	Clear blue
		8 Pins	Clear
Terminal	Phosphor Bronze		Gold plated

*UL94V-0




Applicable Cable	
Conductor diameter	AWG # 28(7/0.127)
Insulator diameter	φ0.787 max.

• Electrical Performance

Item	Condition	Specification
Current rating	Per pin	0.5A
Voltage rating	Per pin	125V AC
Insulation Resistance	100V DC	100 M Ω Min.
Withstanding Voltage	1 minute	500V r.m.s AC




• TM30P-66P

CL No.	Part No.	RoHS
222-2684-2	TM30P-66P	YES



• TM30P-88P

CL No.	Part No.	RoHS
222-2685-5	TM30P-88P	YES



Exclusive Hand Tool for Connection



CL No.	Part No.	Applicable Connector
250-0145-6	TC1-TM30P-66P	TM30P-66P
250-0241-0	TC2-TM20P/30P-88P	TM30P-88P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hirose Electric:

[TC-2220-8/10P-88-1](#) [TM3P-44P](#) [TM3P-64P](#) [TM3P-66P](#) [TM3P-88P](#) [TM3P-62P](#) [TM4P-44P](#) [TM4P-64P](#) [TM4P-66P](#)
[TM4P-88P](#) [TM4P-1212P](#) [TM4P-1212P\(01\)](#) [TM8P-88P](#) [TM10P-88P](#) [TM20P-88P](#) [TM20P-66P](#) [TM30P-66P](#)
[TM30P-88P](#) [TM10P1-88P](#) [TC-2220-64\(01\)](#) [TC-2220-66\(01\)](#) [TC-2220-44\(01\)](#)