






PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL

PC BOARD VERSIONS		
PRODUCT NR:	PCB THICKNESS	DIM "A"
89014-X02/X02LF	1.6	2.90
89014-X12/X12LF	2.4	3.53



- NOTES:
- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - INDICATED HOLES ARE UNPLATED.
 - PLATING OF SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn FOR LEAD FREE.
 - PRODUCT MARKING: PART NUMBER & BATCH ID.
 - SET BACK FOR TAIL BLOCK
 - TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
 - DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.

RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 ELECTRONICS www.fciconnect.com		
ltr	ecn no	dr	date							
A	H40101	VWO	940209	linear		projection		title		
B	H40487	DOB	940802					5 ROW R.A. S.T.B. SIGNAL		
C	V00578	LLA	000316	angles				RECEPT. 24 mm MODULE		
D	V00850	GNV	000512	dr	H v Woensel	940127		product family		
E	p004-0104	CLU	041223	engr	H v Woensel	940127	mm	METRAL (tm)	code	
F	p007-0170	Cent	05/22/07	chr	E Feijen	940127	scale	size dwg no	213	
G	p009-0088	Cent	06/06/08	app	H v Woensel	940127	5:1	A2	89014	
sheet index	revision	G	1							sheet 1 of 1