

TOSHIBA TRANSISTOR SILICON PNP EPITAXIAL TYPE (PCT PROCESS)

2SA1954

GENERAL PURPOSE AMPLIFIER APPLICATIONS


SWITCHING AND MUTING SWITCH APPLICATION

Unit in mm


- Low Saturation Voltage : $V_{CE(sat)}(1) = -15\text{mV (Typ.)}$
@ $I_C = -10\text{mA} / I_B = -0.5\text{mA}$
- Large Collector Current : $I_C = -500\text{mA (Max.)}$

MAXIMUM RATINGS ($T_a = 25^\circ\text{C}$)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V_{CBO}	-15	V
Collector-Emitter Voltage	V_{CEO}	-12	V
Emitter-Base Voltage	V_{EBO}	-5	V
Collector Current	I_C	-500	mA
Base Current	I_B	-50	mA
Collector Power Dissipation	P_C	100	mW
Junction Temperature	T_j	125	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-55~125	$^\circ\text{C}$




MARKING



961001EAA2

- TOSHIBA is continually working to improve the quality and the reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to observe standards of safety, and to avoid situations in which a malfunction or failure of a TOSHIBA product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent products specifications. Also, please keep in mind the precautions and conditions set forth in the TOSHIBA Semiconductor Reliability Handbook.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current		I_{CBO}	$V_{CB} = -15V, I_E = 0$	—	—	-0.1	μA
Emitter Cut-off Current		I_{EBO}	$V_{EB} = -5V, I_C = 0$	—	—	-0.1	μA
DC Current Gain		h_{FE} (Note)	$V_{CE} = -2V, I_C = -10mA$	300	—	1000	
Collector-Emitter Saturation Voltage	$V_{CE(sat)} (1)$		$I_C = -10mA, I_B = -0.5mA$	—	-15	-30	mV
	$V_{CE(sat)} (2)$		$I_C = -200mA, I_B = -10mA$	—	-110	-250	
Base-Emitter Saturation Voltage		$V_{BE(sat)}$	$I_C = -200mA, I_B = -10mA$	—	-0.87	-1.2	V
Transition Frequency		f_T	$V_{CE} = -2V, I_C = -10mA$	80	130	—	MHz
Collector Output Capacitance		C_{ob}	$V_{CB} = -10V, I_E = 0, f = 1MHz$	—	4.2	—	pF
Collector-Emitter On Resistance		R_{on}	$I_B = -1mA, V_{in} = -1V_{rms}, f = 1kHz$	—	0.9	—	Ω
Switching Time	Turn-on Time	t_{on}	 INPUT 300Ω OUTPUT 10 μs 50Ω 60Ω $V_{BB} = 3V$ $V_{CC} = -6V$ $I_{B1} = -I_{B2} = 5mA$	—	40	—	ns
	Storage Time	t_{stg}		—	280	—	
	Fall Time	t_f		—	45	—	

(Note) h_{FE} Classification A : 300~600, B : 500~1000

