






Stecklänge / mating length




E = early mate, late break / voreilend
S = standard
L = late mate, early break / nacheilend

Lötanschluß 0.6 x 0.6 mm / solder terminal 0.6 x 0.6 mm



Isolierwerkstoff / housing material : PBT GF30



Bauart 3/ type 3

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions per IEC 60 603-2

Information:				Tolerances		 All Dimensions in mm		Scale		2:1	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.		Designation Messerleiste C 96 Löt Male Connector C 96 Solder					
				a		30.01.2008				www.ERNI.com	
Index		Date		V:00032403.SZA		STVC					

Consider protection memo from DN 34