





PIN NUMBER	DIM. L±0.15
25,26	3.50
ALL OTHER PINS	4.25
1, 13, 38, 50	5.00

NOTES :

1. MATERIAL :

INSULATOR : SUMIKASUPER LCP E6807

FLAMMABILITY RATING: UL94V-0

COLOR: IVORY

CONTACT : BRASS C2680R-H, t=0.30mm.

GROUND MOUNTING EAR: PHOSPHOR BRONZE C5191-H, t=0.20mm.

PICK-UP CAP: LCP E130i

2. PLATING :

CONTACT AREA: SELECTIVE GOLD (SEE P/N DESCRIPTION)

UNDER PLATING: 50u" Min. NICKEL OVERALL

SOLDER TAIL AREA: 100u" Min. TIN/LEAD or 100u" Min. MATTE TIN.


GROUND MOUNTING EAR CONTACT AREA: GOLD FLASH.

GROUND MOUNTING EAR SOLDER AREA: 100u" Min. TIN/LEAD or 100u" Min. MATTE TIN.

3. SOLDER TAILS TO BE WITHIN 0.05 UPWARD AND 0.2 DOWNWARD FROM Z-DATUM PLACE, AND COPLANARITY OF SOLDER TAILS TO BE WITHIN 0.10mm.

4. PRODUCT SPEC: GS-12-240.

5. PACKAGING SPEC: GS-14-980.



mat'l code					tolerance unless otherwise specified		CUSTOMER COPY		FCI	
rev.	ecn	no.	dr	date	linear	.0 ± .30	projection	mm	www.fciconnect.com	
E	ELX-N-16359	J.H	2013/11/25			.00 ± .20				
E	ELX-N-19498	J.H	2014/11/20		angles	.000 ± 0.10	scale	A4	title CF HEADER TYPE II NORMAL S/O=2.0	
					dr	ALLEN CHANG 12/15/05				
					enrg	ALLEN CHANG 12/15/05			product family: PCMCIA	
					chr	STERLING LIN 12/15/05				
					appd	H.C LIU 12/15/05			size dwg no. 10064420	
sheet	revision	F	F							
index	sheet	1	2						code NT	

cage code

6. Part Number Description:

P/N: 10064420-XX50XXX

PLATING ON SOLDER TAIL AREA:

BLANK: 100u" TIN/LEAD.

LF: 100u" MATTE TIN.

PACKAGING OPTION

WITHOUT "R" - TRAY

WITH "R" - TAPE&REEL

1: WITHOUT PICK-UP CAP

2: WITH PICK-UP CAP

PIN COUNT.

KEY TYPE:

0: NORMAL TYPE

GOLD PLATING:

B: 10u" GOLD PLATE


E: 30u" GOLD PLATE

7. THIS PRODUCT (10064420-XXXXLFF) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008.

8. THIS PRODUCT (10064420-XXXXX) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008 EXCEPT FOR Pb.


9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, IR OR VAPOR PHASE REFLOW OVEN.

10. THE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE CRITERIA SHOWN IN THE NOTES 7 AND 9.



General Tolerance +/-0.05mm

Recommended PCB Pattern

mat'l code					tolerance unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com				
rev.	ecn	no.	dr	date	linear	.0 ± .30			projection 	title CF HEADER TYPE II NORMAL S/O=2.0				
F						.00 ± .20								
						.000± 0.10								
					angles	± 2°								
					dr	ALLEN CHANG	12/15/05	unit	product family: PCMCIA				code	
					enr	ALLEN CHANG	12/15/05	mm	size				NT	
					chr	STERLING LIN	12/15/05	scale	dwg no.				sheet	
					appd	H.C LIOU	12/15/05		A4 10064420				2 OF 2	
sheet	revision	F	F											
index	sheet	1	2											

cage code