



LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECR-18-013640	28AUG2018	JT	SH





2227303-1, -2, -3, -7
1-2227303-2




- MATERIAL: 0.25mm THICK STAINLESS STEEL.
- FINISH: 0.00125mm Min. NICKEL OVER ALL , 0.002mm Min.TIN DIPPED ON SOLDER TABS, NON PLATED EDGES PERMISSIBLE.
- MATES WITH SFP MSA COMPLIANT TRANSCEIVERS.
- PADS AND VIAS CHASSIS GROUND.
- DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.50 mm
- REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- REFERENCE APPLICATION SPEC. 114-13120, HOLE C, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- ESD PROTECTION PACKAGE.
- PRELIMINARY PART- NOT RELEASED FOR PRODUCTION
- WITHOUT EMI SPRING
- WITH CUSTOMIZED HEATSINK OPEN



1-2227303-1




2-2227303-2




TRAY	1.25	2-2227303-2
TRAY	3.55	1-2227303-1
TRAY	3.55	2227303-7
REEL	1.80	1-2227303-2
TRAY	1.80	2227303-3
REEL	1.80	2227303-2
TRAY	3.55	2227303-1
PACKAGING	A	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN C. VALENTINE CHK M. SCHMITT APVD M. SCHMITT	19OCT2012 19OCT2012 19OCT2012	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		±0.1 ±0.1 ±0.1 ±0.1 ± -		PRODUCT SPEC 108-1950 APPLICATION SPEC 114-13120 WEIGHT -	
MATERIAL -		-		SIZE A100779	
-		-		CAGE CODE 2227303	
-		-		DRAWING NO 2227303	
-		-		RESTRICTED TO -	
Customer Drawing		SCALE 3:1		SHEET 1 OF 3	
				REV B	



THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		DWN C. VALENTINE 19OCT2012	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK M. SCHMITT 19OCT2012	NAME SFP, 1X1 SINGLE PIECE CAGE, SOLDER PIN	
DIMENSIONS:		APVD W. SCHMITT 19OCT2012	SIZE CAGE CODE DRAWING NO	
mm		PRODUCT SPEC	A100779C=2227303	
0 PLC ±0.1		APPLICATION SPEC	RESTRICTED TO	
1 PLC ±0.1		114-13120	SCALE 3:1 SHEET 2 OF 3 REV B	
2 PLC ±0.1		WEIGHT		
3 PLC ±0.1		Customer Drawing		
4 PLC ±				
ANGLES FINISH				



14.88



Technical drawing of the side profile of the table. The overall width is 47.45. The distance from the right edge to the start of the leg assembly is 15. The height of the table top is 9. The corner radius is R0.25. The drawing shows the table top, legs, and a central support structure.

4805 (3/11)