


CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING


NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 0.3A @ 125 VAC
6. OPERATING FORCE: 500±200 GRAMS
7. OPERATING TEMP: -30°C TO 85°C
- ▲ 8. CIRCUIT DP: 8 POSITION 30° INDEX.
9. DIELECTRIC STRENGTH: 500VAC-60 SEC
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOP RING
11. ▲ DENOTES CRITICAL PARAMETER.

HARDWARE SUPPLIED ON SWITCH



ISOMETRIC



D	15313	ADDED P.C.B LAYOUT	9/22/05	PH
C	15303	MADE CHANGES TO NOTES 5,6,8,9	9/20/05	PH
B	15021	CHANGED/ADDED DIMENSIONS	6/21/05	JB
A	14993	RELEASED FOR PRODUCTION	6/16/05	JB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE KC18D0.001NPS

SCALE 1.5:1

DATE 6/16/2005

DR JB

DWG G510000

REV D