

NOTES:

1.0 ELECTRICAL SPECIFICATIONS:

1.1 FREQUENCY RANGE: DC to 4.0 GHz

1.2 INPUT POWER:

2 WATTS @ +25°C

0.5 WATTS @ +125°C


1.3 OPERATING TEMP RANGE: -55°C TO +125°C

1.4 IMPEDANCE: 50 OHMS

1.5 VSWR: 1.20:1 MAX

2.0 MARKING: (MARK UNIT AS SHOWN)

REF: INK-02638-27-05



REV.	DESCRIPTION	DATE
-	RELEASED	8/8/87
A	ECR 5857	2/17/88
B	ECR 6545(RENUMBER)	8/1/89
C	ECN 10572	5/24/91
C1	REDRAW ON CAD	9/24/91
C2	ADDED TITLEBLOCK	10/26/05

NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Emerson Network Power.	CAGE CODE		34078		MIDWEST MICROWAVE	
	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±2°		 EMERSON Network Power Connectivity Solutions		TITLE TERMINATION OUTLINE DRAWING	
DRAWN/DATE A.BEATTY 9/24/91		ENG./DATE G.KOZAK 9/24/91		DRAWING NUMBER TRM-2048-MC-BNC-10-01		REV. C2
CHECKED/DATE C.RIGGE 9/24/91		APPROVED/DATE		SCALE: 5=1	SHEET 1 of 1	