

# Midget 10x38mm Fuses

## KLK Series

600 V ac/500 V dc • 1/10–30 A • Fast Acting



### Description

The KLK series fast-acting fuses are designed specifically for the protection of control circuits, street lighting, HID lighting, computers, and other applications without high in-rush currents. These midget fuses also have high-interrupting and current-limiting capability. They are intended to supplement the primary branch-circuit fuse or breaker to provide backup overcurrent protection. The KLK fuses are non-indicating and may be used with an indicating fuse block to identify a blown fuse.

### Features & Benefits

| FEATURES                     | BENEFITS                                                                      |
|------------------------------|-------------------------------------------------------------------------------|
| <b>10x38 mm size</b>         | Common dimensions used in a variety of applications                           |
| <b>Fast-acting</b>           | Provides fast, reliable short-circuit response within the interrupting rating |
| <b>POWR-GARD® technology</b> | Ensures quality backup overcurrent protection                                 |

### Applications

- Control circuits
- Street and HID lighting
- Computers

# Midget 10x38mm Fuses

## KLK Series

### Specifications

|                              |                                                                                            |
|------------------------------|--------------------------------------------------------------------------------------------|
| <b>Voltage Rating</b>        | 600 V ac / 500 V dc                                                                        |
| <b>Interrupting Ratings</b>  | AC: 100 kA<br>200 kA Littelfuse self-certified                                             |
| <b>Ampere Range</b>          | 1/10–30 A                                                                                  |
| <b>Applicable Standards</b>  | UL 248-14 Listed (File: E10480)<br>CSA Certified (File: LR29862)<br>QPL (File: F60C)<br>CE |
| <b>Environmental</b>         | RoHS Compliant                                                                             |
| <b>Material</b>              | Body: Melamine<br>Caps: Copper Alloy                                                       |
| <b>Operating Temperature</b> | See Rerating Curve                                                                         |
| <b>Country of Origin</b>     | Mexico                                                                                     |

### Certification & Compliance

|             |                                                      |
|-------------|------------------------------------------------------|
| <b>UL</b>   | UL Listed (File: E10480)                             |
| <b>CSA</b>  | CSA Certified (File: LR29862)                        |
| <b>CE</b>   | EU_DOC-KLK_201218                                    |
| <b>RoHS</b> | RoHS 2 Directive 2011/65/EU; Directive (EU) 2015/863 |

### Accessories

Littelfuse LPSM dead-front series fuse holder  
Littelfuse LEB series fuse holder  
Littelfuse L60030M series fuse holder

### Ordering Information

| AMP RATING | CATALOG NUMBER | ORDERING NUMBER | PRODUCT MARKING | VOLTAGE |     | INTERRUPTING RATING (KA) |    | UPC         | WEIGHT LB (G) | AGENCY APPROVALS |     |
|------------|----------------|-----------------|-----------------|---------|-----|--------------------------|----|-------------|---------------|------------------|-----|
|            |                |                 |                 | AC      | DC  | AC                       | DC |             |               | UL               | CSA |
| 1/10       | KLK.100        | OKLK.100T       | KLK 1/10A       | 600     | 500 | 100                      | 50 | 07945825011 | .013 (5.90)   | •                | •   |
| 1/8        | KLK.125        | OKLK.125T       | KLK 1/8A        | 600     | 500 | 100                      | 50 | 07945825012 | .013 (5.90)   | •                | •   |
| 3/10       | KLK.200        | OKLK.200T       | KLK 2/10A       | 600     | 500 | 100                      | 50 | 07945825018 | .013 (5.90)   | •                | •   |
| 1/4        | KLK.250        | OKLK.250T       | KLK 1/4A        | 600     | 500 | 100                      | 50 | 07945825019 | .013 (5.90)   | •                | •   |
| 3/10       | KLK.300        | OKLK.300T       | KLK 3/10A       | 600     | 500 | 100                      | 50 | 07945825020 | .013 (5.90)   | •                | •   |
| 1/2        | KLK.500        | OKLK.500T       | KLK 1/2A        | 600     | 500 | 100                      | 50 | 07945825024 | .013 (5.90)   | •                | •   |
| 3/4        | KLK.750        | OKLK.750T       | KLK 3/4A        | 600     | 500 | 100                      | 50 | 07945825029 | .013 (5.90)   | •                | •   |
| 1          | KLK001         | OKLK001.T       | KLK 1A          | 600     | 500 | 100                      | 50 | 07945825031 | .013 (5.90)   | •                | •   |
| 1 1/2      | KLK01.5        | OKLK01.5T       | KLK 1-1/2A      | 600     | 500 | 100                      | 50 | 07945825037 | .013 (5.90)   | •                | •   |
| 2          | KLK002         | OKLK002.T       | KLK 2A          | 600     | 500 | 100                      | 50 | 07945825041 | .017 (7.71)   | •                | •   |
| 2 1/2      | KLK02.5        | OKLK02.5T       | KLK 2-1/2A      | 600     | 500 | 100                      | 50 | 07945825043 | .017 (7.71)   | •                | •   |
| 3          | KLK003         | OKLK003.T       | KLK 3A          | 600     | 500 | 100                      | 50 | 07945825047 | .017 (7.71)   | •                | •   |
| 3 1/2      | KLK03.5        | OKLK03.5T       | KLK 3-1/2A      | 600     | 500 | 100                      | 50 | 07945825048 | .017 (7.71)   | •                | •   |

# Midget 10x38mm Fuses

## KLK Series


### Ordering Information

| AMP RATING | CATALOG NUMBER | ORDERING NUMBER | PRODUCT MARKING | VOLTAGE |     | INTERRUPTING RATING (KA) |    | UPC         | WEIGHT LB (G) | AGENCY APPROVALS |     |
|------------|----------------|-----------------|-----------------|---------|-----|--------------------------|----|-------------|---------------|------------------|-----|
|            |                |                 |                 | AC      | DC  | AC                       | DC |             |               | UL               | CSA |
| 4          | KLK004         | OKLK004.T       | KLK 4A          | 600     | 500 | 100                      | 50 | 07945825053 | .017 (7.71)   | •                | •   |
| 5          | KLK005         | OKLK005.T       | KLK 5A          | 600     | 500 | 100                      | 50 | 07945825055 | .017 (7.71)   | •                | •   |
| 6          | KLK006         | OKLK006.T       | KLK 6A          | 600     | 500 | 100                      | 50 | 07945825058 | .017 (7.71)   | •                | •   |
| 7          | KLK007         | OKLK007.T       | KLK 7A          | 600     | 500 | 100                      | 50 | 07945825061 | .017 (7.71)   | •                | •   |
| 8          | KLK008         | OKLK008.T       | KLK 8A          | 600     | 500 | 100                      | 50 | 07945825063 | .017 (7.71)   | •                | •   |
| 9          | KLK009         | OKLK009.T       | KLK 9A          | 600     | 500 | 100                      | 50 | 07945825064 | .017 (7.71)   | •                | •   |
| 10         | KLK010         | OKLK010.T       | KLK 10A         | 600     | 500 | 100                      | 50 | 07945825065 | .017 (7.71)   | •                | •   |
| 12         | KLK012         | OKLK012.T       | KLK 12A         | 600     | 500 | 100                      | 50 | 07945825067 | .017 (7.71)   | •                | •   |
| 15         | KLK015         | OKLK015.T       | KLK 15A         | 600     | 500 | 100                      | 50 | 07945825068 | .017 (7.71)   | •                | •   |
| 20         | KLK020         | OKLK020.T       | KLK 20A         | 600     | 500 | 100                      | 50 | 07945825071 | .017 (7.71)   | •                | •   |
| 25         | KLK025         | OKLK025.T       | KLK 25A         | 600     | 500 | 100                      | 50 | 07945825072 | .017 (7.71)   | •                | •   |
| 30         | KLK030         | OKLK030.T       | KLK 30A         | 600     | 500 | 100                      | 50 | 07945825073 | .017 (7.71)   | •                | •   |

### Electrical Specification - Agency Requirements

| AMPERAGE RATING | OPENING TIME (MINUTES)     |                            |                            |
|-----------------|----------------------------|----------------------------|----------------------------|
|                 | 100 % OF AMP RATING PER UL | 135 % OF AMP RATING PER UL | 200 % OF AMP RATING PER UL |
| 1/10–30         | Temperature Stabilization  | 60 Max                     | 2 Max                      |




### Dimensions Millimeters (inches)



# Midget 10x38mm Fuses

## KLK Series

### Time Current Curves




# Midget 10x38mm Fuses

## KLK Series

### Temperature Derating Curve

Ambient temperature: temperature of air immediately surrounding fuse



**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Littelfuse:

[0KLK010.T](#) [0KLK.200T](#) [0KLK001.T](#) [0KLK007.T](#) [0KLK008.T](#) [0KLK015.T](#) [0KLK.500T](#) [0KLK020.T](#) [0KLK002.T](#)  
[0KLK030.T](#) [0KLK.300T](#) [0KLK025.T](#) [0KLK03.5T](#) [0KLK.750T](#) [0KLK02.5T](#) [0KLK.100T](#) [0KLK.125T](#) [0KLK01.5T](#)  
[0KLK004.T](#) [0KLK009.T](#) [0KLK012.T](#) [0KLK005.T](#) [0KLK.250T](#) [0KLK006.T](#) [0KLK003.T](#) [0KLK015.H](#) [0KLK020.H](#)  
[0KLK.500TS](#) [0KLK007.TS](#) [0KLK02.5TS](#) [0KLK030.TS](#) [0KLK004.TS](#) [0KLK006.TS](#) [0KLK.750TS](#) [0KLK012.TS](#)  
[0KLK005.TS](#) [0KLK020.TS](#) [0KLK003.TS](#) [0KLK015.TS](#) [0KLK002.TS](#) [0KLK010.TS](#) [0KLK008.TS](#) [0KLK009.TS](#)  
[0KLK001.TS](#) [0KLK03.5TS](#) [0KLK01.5TS](#) [0KLK025.TS](#)