

Coaxial Directional Coupler

75Ω

1 to 400 MHz

ZFDC-10-1-75



Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3

Features

- excellent directivity, 44 dB typ.
- up to 4W input power
- rugged shielded case

Applications

- catv
- VHF/HF
- instrumentation

CASE STYLE: K18

Connectors	Model	Price	Qty.
BNC	ZFDC-10-1-75	\$45.95 ea.	(1-9)
BRACKET (OPTION "B")		\$2.50	(1+)

Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS¹						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT (W)	
			L		M		U		L		M		U				
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	L
1-400	10.5±0.5	±0.5	1.0	1.7	1.1	1.5	1.1	1.6	46	30	44	28	34	20	1.3	2.0	4.0


L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]

1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data




Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	In	Return Loss (dB) Out	Cpl
1.00	1.16	10.68	58.99	23.11	17.09	17.35
4.60	0.93	10.48	59.93	33.06	19.71	19.75
8.20	0.90	10.46	57.01	38.55	20.09	20.06
10.00	0.89	10.46	56.81	41.04	20.17	20.11
56.00	0.92	10.48	44.49	39.77	20.01	19.33
128.00	0.94	10.55	36.39	32.77	19.68	17.16
164.00	0.95	10.59	33.96	30.48	19.45	16.03
240.00	0.95	10.70	29.35	26.66	18.97	13.94
320.00	0.96	10.82	25.49	23.65	18.34	12.19
400.00	0.97	10.97	22.28	21.37	17.64	10.84

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.00	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40
J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.75	.07	grams
--	--	3.18	42.88	55.37	19.05	1.78	70.0



electrical schematic

