

Tuija-3 lenses for Sharp GM2BB... (Double Dome) LEDs**SHARP**


- Designed for Sharp GM2BB... (Double Dome) series of LEDs.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F)
- High optical efficiency, >85%
- No lens holder. Fastening to heat sink with droplets of glue. NOTE: legs go into the PCB by 1.2 mm only, do not go thru a normal MCPCB
- Diameter 50 mm (MR16)
- Mechanical CAD models available upon request
- All 3 lens types have the same outer dimensions.

LENS TYPES

NAME	ORDERING CODE	FWHM Angle, with DD-E
Tuija-3 spot	C11192_Tuija-3-SS-DD	±6°
Tuija-3 medium	C11193_Tuija-3-M-DD	±8°
Tuija-3 wide	C11191_Tuija-3-W-DD	±29°



MEASUREMENT DATA

Relative Intensity of C11192_Tuija-3-SS-DD





© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of C11193_Tuija-3-M-DD




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of C11191_Tuija-3-W-DD



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice