Certificate Number: Q10561

Certificate Number: E17276

1N4933G - 1N4937G

GLASS PASSIVATED JUNCTION FAST RECOVERY RECTIFIERS

PRV : 50 - 600 Volts
Io : 1.0 Amperes

FEATURES :

* Glass passivated chip
* High current capability
* High reliability
* Low reverse current
* Low forward voltage drop
* Fast switching for high efficiency

MECHANICAL DATA :

* Case : DO-41 Molded plastic
* Epoxy : UL94V-O rate flame retardant
* Lead : Axial lead solderable per MIL-STD-202, Method 208 guaranteed
* Polarity : Color band denotes cathode end
* Mounting position : Any
* Weight : 0.34 gram

DO - 41



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified.
Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

RATING	SYMBOL	1N4933G	1N4934G	1N4935G	1N4936G	1N4937G	UNIT
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	V
Maximum Average Forward Current 0.375"(9.5mm) Lead Length Ta = 50 °C	$I_{F(AV)}$	1.0					A
Peak Forward Surge Current, 8.3ms Single half sine wave superimposed on rated load (JEDEC Method)	I_{FSM}	30					A
Maximum Peak Forward Voltage at I_F = 1.0 A	V_F	1.2					V
Maximum DC Reverse Current Ta = 25 °C	I_R	5.0					µA
at Rated DC Blocking Voltage Ta = 100 °C	$I_{R(H)}$	100					µA
Maximum Reverse Recovery Time (Note 1)	Trr	150					ns
Typical Junction Capacitance (Note 2)	C_J	15					pf
Junction Temperature Range	T_J	- 65 to + 150					°C
Storage Temperature Range	T_{STG}	- 65 to + 150					°C

Notes :

(1) Reverse Recovery Test Conditions : I_F = 0.5 A, I_R = 1.0 A, Irr = 0.25 A.

(2) Measured at 1.0 MHz and applied reverse voltage of 4.0 V_{DC}

RATING AND CHARACTERISTIC CURVES (1N4933G - 1N4937G)

FIG.1 - REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM



NOTES : 1. Rise Time = 7 ns max., Input Impedance = 1 megaohm, 22 pF.
2. Rise time = 10 ns max., Source Impedance = 50 ohms.
3. All Resistors = Non-inductive Types.

FIG.2 - DERATING CURVE FOR OUTPUT RECTIFIED CURRENT



FIG.3 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT



FIG.4 - TYPICAL FORWARD CHARACTERISTICS



FIG.5 - TYPICAL REVERSE CHARACTERISTICS